

Product data sheet

Specifications



Complete body for pilot lights,
Harmony XB6, orange light block,
with body/fixing collar, integral LED,
230...240V AC

ZB6EM8B

Product availability: Non-Stock - Not normally stocked in
distribution facility

Main

Range of Product	Harmony XB6
Product or Component Type	Complete body for pilot lights
Device short name	ZB6
Sale per indivisible quantity	5
Connections - terminals	Faston connectors 2.8 x 0.5 mm
Light source	LED
Bulb base	Integral LED
Light block supply	Direct
Light source colour	Orange
[Us] Rated Supply Voltage	230...240 V AC

Complementary

CAD overall height	0.6 in (14 mm)
CAD overall depth	2.3 in (58 mm)
Terminals description ISO n°1	(X1-X2)PL
Product Weight	0.007 lb(US) (0.003 kg)
Operating position	Any position
[Ui] rated insulation voltage	250 V 3)IEC 60947-1
[Uimp] rated impulse withstand voltage	4 kV IEC 60947-1
Signalling type	Steady
Supply voltage limits	195...264 V AC
Surge withstand	1 kV in contact IEC 61000-4-5 2 kV in free air IEC 61000-4-5

Environment

Protective treatment	TC
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Electrical shock protection class	Class II conforming to IEC 61140

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	JIS C 4520 UL 508 IEC 60947-5-5 IEC 60947-1 JIS C 852 IEC 60947-5-1 CSA C22.2 No 14
Product Certifications	CSA CCC UL GOST
Vibration resistance	+/- 3 mm (f= 2...500 Hz) conforming to IEC 60068-2-6 5 gn (f= 2...500 Hz) conforming to IEC 60068-2-6
Shock resistance	30 gn 18 ms) half sine wave acceleration IEC 60068-2-27 50 gn 11 ms) half sine wave acceleration IEC 60068-2-27
Resistance to fast transients	2 kV IEC 61000-4-4
Resistance to electromagnetic fields	9.1 V/m (10 V/m) IEC 61000-4-3
Resistance to electrostatic discharge	6 kV on contact (on metal parts) IEC 61000-2-6 8 kV in free air (in insulating parts) IEC 61000-2-6
Electromagnetic emission	Class B IEC 55011

Ordering and shipping details

Category	US10CS222459
Discount Schedule	0CS2
GTIN	3389110274868
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	0.87 in (2.2 cm)
Package 1 Width	1.26 in (3.2 cm)
Package 1 Length	2.56 in (6.5 cm)
Package weight(Lbs)	0.1 oz (3.0 g)
Unit Type of Package 2	CAR
Number of Units in Package 2	5
Package 2 Height	0.87 in (2.2 cm)
Package 2 Width	1.26 in (3.2 cm)
Package 2 Length	2.56 in (6.5 cm)
Package 2 Weight	0.6 oz (17 g)

Contractual warranty

Warranty	18 months
----------	-----------

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	7e93e493-8304-40e7-9b39-3ac9fc039df4
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


Use Again

 Repack and remanufacture	
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Dimensions Drawings

Body for Pilot Light

Dimensions



b 13.5 mm/0.53 in.

Technical Illustration

Dimensions

mm
in.

