

LC1DPKF7

Capacitor contactor, TeSys Deca, 30 kVAR at
400 V/50 Hz, coil 110 V AC 50/60 Hz





Main

Range	TeSys TeSys Deca
Product name	TeSys LC1D.K TeSys Deca
Product or Component Type	Capacitor duty contactor
Device short name	LC1DPK
Device Application	Control
Contactors application	Power factor correction
Utilisation category	AC-6b
Poles description	3P
Power pole contact composition	3 NO
Device location in system	Inside delta interruption Line interruption
[Ue] rated operational voltage	Power circuit 690 V AC 50/60 Hz
Reactive power rating	17 Kvar 230 V AC 50 Hz 140 °F (60 °C) 30 Kvar 400 V AC 50 Hz 140 °F (60 °C) 32 Kvar 440 V AC 50 Hz 140 °F (60 °C) 50 Kvar 690 V AC 50 Hz 140 °F (60 °C) 16.5 Kvar 230 V AC 60 Hz 140 °F (60 °C) 33.3 Kvar 460 V AC 60 Hz 140 °F (60 °C) 40 kvar 575 V AC 60 Hz 140 °F (60 °C)
Control circuit type	AC 50/60 Hz
[Uc] control circuit voltage	110 V AC 50/60 Hz
Auxiliary contact composition	1 NO + 2 NC instantaneous
Electrical durability	300000 Cycles 400 V 200000 cycles 690 V
Mounting Support	DIN rail Plate
Standards	EN/IEC 60947-1 EN/IEC 60947-4-1 UL 60947-4-1 CSA C22.2 No 60947-4-1 IEC 60335-1
Product Certifications	IECEE CB Scheme UL CSA UKCA
Connections - terminals	Control circuit screw clamp terminals 1 0.00... 0.01 in ² (1...4 mm ²) solid Control circuit screw clamp terminals 2 0.00... 0.01 in ² (1...4 mm ²) solid Control circuit screw clamp terminals 1 0.00... 0.01 in ² (1...4 mm ²) flexible without cable end Control circuit screw clamp terminals 2 0.00... 0.01 in ² (1...4 mm ²) flexible without cable end Control circuit screw clamp terminals 1 0.00... 0.01 in ² (1...4 mm ²) flexible with cable end Control circuit screw clamp terminals 2 0.00... 0.00 in ² (1...2.5 mm ²) flexible with cable end Power circuit EverLink BTR screw connectors 1 0.00...0.05 in ² (1...35 mm ²) solid Power circuit EverLink BTR screw connectors 2 0.00...0.04 in ² (1...25 mm ²) solid Power circuit EverLink BTR screw connectors 1 0.00...0.05 in ² (1...35 mm ²) flexible with or without cable end Power circuit EverLink BTR screw connectors 2 0.00...0.04 in ² (1...25 mm ²) flexible with or without cable end

Tightening torque	Control circuit 15.05 lbf.in (1.7 N.m) screw clamp terminals Power circuit 44.25 lbf.in (5 N.m) EverLink BTR screw connectors 0.00...0.04 in ² (1...25 mm ²) Power circuit 70.81 lbf.in (8 N.m) EverLink BTR screw connectors 0.05 in ² (35 mm ²)
Maximum operating rate	240 cyc/h

Complementary

Auxiliary contacts type	Mechanically linked 1 NO + 2 NC IEC 60947-5-1
-------------------------	---

Environment

IP degree of protection	IP20 front face IEC 60529
Ambient Air Temperature for Operation	23...140 °F (-5...60 °C)
Ambient Air Temperature for Storage	-76...176 °F (-60...80 °C)
Operating altitude	0...9842.52 ft (0...3000 m)
Height	6.54 in (166 mm)
Width	2.17 in (55 mm)
Depth	6.14 in (156 mm)
Net Weight	2.87 lb(US) (1.3 kg)

Ordering and shipping details

Category	22357-CTR, TESYS D, OPEN, 40-65A AC
Discount Schedule	I12
GTIN	3606480401251
Returnability	No
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.76 in (7 cm)
Package 1 Width	7.87 in (20 cm)
Package 1 Length	9.06 in (23 cm)
Package 1 Weight	2.44 lb(US) (1.108 kg)
Unit Type of Package 2	S03
Number of Units in Package 2	6
Package 2 Height	11.81 in (30 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	16.23 lb(US) (7.361 kg)
Unit Type of Package 3	P06
Number of Units in Package 3	48
Package 3 Height	31.50 in (80 cm)
Package 3 Width	31.50 in (80 cm)
Package 3 Length	23.62 in (60 cm)
Package 3 Weight	148.57 lb(US) (67.388 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration

Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------