

Product data sheet

Specifications



Miniature circuit breaker (MCB), Multi9 C60SP, 1P, 3A, B curve, 10kA (UL1077), 10kA (IEC/EN 60947-2)

M9F21103

Product availability: Stock - Normally stocked in distribution facility

Main

Range	Multi9
Product name	Multi9 C60
Product or Component Type	Miniature circuit-breaker
Device short name	C60SP
Device Application	Distribution
Poles description	1P
Number of protected poles	1
Line Rated Current	3 A 77 °F (25 °C) EN/IEC 60947-2
Network type	AC DC
Trip unit technology	Thermal-magnetic
Curve code	B
Breaking capacity	10 kA AIR 277 V AC UL 1077 14 kA AIR 240 V AC UL 1077 14 kA AIR 120 V AC UL 1077 10 kA AIR 65 V DC UL 1077 10 kA AIR 277 V AC CSA C22.2 No 235 14 kA AIR 240 V AC CSA C22.2 No 235 14 kA AIR 120 V AC CSA C22.2 No 235 10 kA AIR 65 V DC CSA C22.2 No 235 3 kA Icu 415 V AC EN/IEC 60947-2 10 kA Icu 240 V AC EN/IEC 60947-2 20 kA Icu 60 V DC EN/IEC 60947-2 3 kA Icu 415 V AC GB 14048.2 10 kA Icu 240 V AC GB 14048.2 20 kA Icu 60 V DC GB 14048.2
Standards	EN/IEC 60947-2 GB 14048.2 UL 1077 CSA C22.2 No 235
Product certifications	IEC CCC UR CSA

Complementary

[Ue] rated operational voltage	240 V AC 50/60 Hz 415 V AC 50/60 Hz 60 V DC
Magnetic tripping limit	4 x In +/- 20 % AC 5.7 x In +/- 20 % DC

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Ics] rated service breaking capacity	2.25 kA 75 % EN/IEC 60947-2 - 415 V AC 7.5 kA 75 % EN/IEC 60947-2 - 240 V AC 20 kA 100 % EN/IEC 60947-2 - 60 V DC 2.25 kA 75 % GB 14048.2 - 415 V AC 7.5 kA 75 % GB 14048.2 - 240 V AC 20 kA 100 % GB 14048.2 - 60 V DC
[Ui] rated insulation voltage	500 V AC EN/IEC 60947-2
[Uimp] rated impulse withstand voltage	6 kVEN/IEC 60947-2
Suitability for isolation	Yes EN/IEC 60947-2
Contact position indicator	Yes
Control Type	Toggle
Local signalling	ON/OFF indication
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 mm pitches	2
Height	3.2 in (81 mm)
Width	0.7 in (18 mm)
Depth	2.8 in (72 mm)
color	Gray
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Provision for padlocking	Padlockable
Connections - terminals	Tunnel type terminal top or bottom) 0.002...0.04 in² (1...25 mm²) AWG 18...AWG 8) - rigid Tunnel type terminal top or bottom) 0.002...0.02 in² (1...16 mm²) AWG 18...AWG 8) - flexible with ferrule Tunnel type terminal top or bottom) 0.002...0.02 in² (1...16 mm²) AWG 18...AWG 8) - flexible
Wire stripping length	0.6 in (14 mm) for top or bottom connection
Tightening torque	22.1 lbf.in (2.5 N.m) top or bottom
Earth-leakage protection	Without

Environment

IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution degree	3 EN/IEC 60947-2
Tropicalisation	2 IEC 60068-1
Relative humidity	95 % 131 °F (55 °C)
Operating altitude	0...6561.68 ft (0...2000 m)
Ambient air temperature for operation	-22...158 °F (-30...70 °C)
Ambient Air Temperature for Storage	-40...176 °F (-40...80 °C)

Ordering and shipping details

Category	US10DE200948
Discount Schedule	0DE2
GTIN	3606481167644

Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	2.95 in (7.500 cm)
Package 1 Width	0.71 in (1.800 cm)
Package 1 Length	3.35 in (8.500 cm)
Package weight(Lbs)	4.021 oz (114.000 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	12
Package 2 Height	3.07 in (7.800 cm)
Package 2 Width	3.46 in (8.800 cm)
Package 2 Length	8.86 in (22.500 cm)
Package 2 Weight	3.122 lb(US) (1.416 kg)
Unit Type of Package 3	S03
Number of Units in Package 3	144
Package 3 Height	11.81 in (30.000 cm)
Package 3 Width	11.81 in (30.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	38.588 lb(US) (17.503 kg)

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

 Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	11
Environmental Disclosure	Product Environmental Profile

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant
SCIP Number	40a4e715-7fff-45ff-88bf-38212f6a80a5
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

 Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.