

# Product data sheet

Specifications



Head for illuminated selector switch, Harmony XB4, metal, green handle, 30mm, universal LED, 3 positions, left to center

ZB4FK1733

**Important message:** A change in appearance may be noted on the product but does not affect its use in terms of function and safety. This makes it compatible with our Universal LED blocks

## Main

|                               |                                      |
|-------------------------------|--------------------------------------|
| Range of product              | Harmony XB4                          |
| Product or component type     | Head for illuminated selector switch |
| Product compatibility         | Universal LED                        |
| Device short name             | ZB4F                                 |
| Bezel material                | Chromium plated metal                |
| Head type                     | Built-in-flush                       |
| Mounting diameter             | 30.5 mm                              |
| Sale per indivisible quantity | 1                                    |
| Shape of signaling unit head  | Round                                |
| Type of operator              | Left to centre spring return         |
| Operator profile              | Green standard handle                |
| Operator position information | 3 positions +/- 45°                  |
| Cap/operator or lens colour   | Green                                |

## Complementary

|                                    |                                                                                                                                                                                                                                                                                                                                                  |
|------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| CAD overall width                  | 36.6 mm                                                                                                                                                                                                                                                                                                                                          |
| CAD overall height                 | 36.6 mm                                                                                                                                                                                                                                                                                                                                          |
| CAD overall depth                  | 47 mm                                                                                                                                                                                                                                                                                                                                            |
| Product weight                     | 0.078 kg                                                                                                                                                                                                                                                                                                                                         |
| Resistance to high pressure washer | 7000000 Pa at 55 °C, distance : 0.1 m                                                                                                                                                                                                                                                                                                            |
| Mechanical durability              | 500000 cycles                                                                                                                                                                                                                                                                                                                                    |
| Electrical composition code        | M3 for <4 contacts using single blocks in front mounting with integral LED<br>M6 for <2 contacts using single blocks in front mounting with integral LED and transformer<br>M10 for <2 contacts using single blocks in front mounting with integral LED<br>M4 for <4 contacts using single and double blocks in front mounting with integral LED |
| Device presentation                | Basic element                                                                                                                                                                                                                                                                                                                                    |

## Environment

|                                     |             |
|-------------------------------------|-------------|
| Protective treatment                | TH          |
| Ambient air temperature for storage | -40...70 °C |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                                       |                                                                                                                                                                                                                                                                     |
|---------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Ambient air temperature for operation | -40...70 °C                                                                                                                                                                                                                                                         |
| Overvoltage category                  | Class I conforming to IEC 60536                                                                                                                                                                                                                                     |
| IP degree of protection               | IP66 conforming to IEC 60529<br>IP67 conforming to IEC 60529<br>IP69 conforming to IEC 60529<br>IP69K conforming to ISO 20653<br>Type 13 conforming to UL 50 E<br>Type 12 conforming to UL 50 E<br>Type 4 conforming to UL 50 E<br>Type 4X conforming to UL 50 E    |
| IK degree of protection               | IK04 conforming to IEC 50102                                                                                                                                                                                                                                        |
| Standards                             | CSA C22.2 No 14<br>IEC 60947-5-1<br>IEC 60947-5-4<br>UL 508<br>IEC 60947-1<br>JIS C8201-5-1<br>CE<br>JIS C8201-1                                                                                                                                                    |
| Product certifications                | UL listed<br>CSA<br>CCC<br>EAC                                                                                                                                                                                                                                      |
| Vibration resistance                  | 5 gn (f= 10...500 Hz) conforming to IEC 60068-2-6<br>2 mm peak to peak (f= 2...10 Hz) conforming to IEC 60068-2-6                                                                                                                                                   |
| Shock resistance                      | 30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27<br>50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27<br>25 gn (duration = 6 ms) for 1000 shocks on each axis conforming to IEC 60068-2-27 |

## Packing Units

|                              |        |
|------------------------------|--------|
| Unit Type of Package 1       | PCE    |
| Number of Units in Package 1 | 1      |
| Package 1 Height             | 4.3 cm |
| Package 1 Width              | 5.2 cm |
| Package 1 Length             | 5.5 cm |
| Package 1 Weight             | 78.0 g |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

| Environmental footprint          |                                               |
|----------------------------------|-----------------------------------------------|
| Total lifecycle Carbon footprint | 1                                             |
| Environmental Disclosure         | <a href="#">Product Environmental Profile</a> |

Use Better


| Materials and Substances               |                                                                                                                                                                                                                                                                                       |
|----------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Packaging made with recycled cardboard | Yes                                                                                                                                                                                                                                                                                   |
| Packaging without single use plastic   | Yes                                                                                                                                                                                                                                                                                   |
| <a href="#">EU RoHS Directive</a>      | Pro-active compliance (Product out of EU RoHS legal scope)                                                                                                                                                                                                                            |
| REACH Regulation                       | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                     |
| California proposition 65              | WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |

Use Again

| Repack and remanufacture        |                                         |
|---------------------------------|-----------------------------------------|
| End of life manual availability | <a href="#">End of Life Information</a> |
| Take-back                       | No                                      |

Dimensions Drawings

Dimensions




e : clamping thickness: 1 to 6 mm / 0.04 to 0.24 in.  
(1) : Additional row of contacts

Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

Connection by Screw Clamp Terminals or Plug-in Connectors




- (1) : Diameter on finished panel or support  
(2) : Ø30.75 mm recommended ( $\text{Ø}30.5 \begin{smallmatrix} +0.5 \\ 0 \end{smallmatrix}$ ) / Ø1.21 in. recommended ( $\text{Ø}1.20 \text{ in.} \begin{smallmatrix} +0.0196 \\ 0 \end{smallmatrix}$ )

| Connections                                 | a in mm | a in in. | b in mm | b in in. |
|---------------------------------------------|---------|----------|---------|----------|
| By connectors                               | 50      | 1.97     | 40      | 1.57     |
| By connectors and with legend holder ZBZF32 | 50      | 1.97     | 40      | 1.57     |
| By connectors and with legend holder ZBZF33 | 60      | 2.36     | 40      | 1.57     |

Technical Description

Electrical Composition Corresponding to Code M3

---



Electrical Composition Corresponding to Code M4

---



Electrical Composition Corresponding to Codes M6 and P2

---





Electrical Composition Corresponding to Codes M5, M10, MF1, MR1 and MF2



Legend

---

Single contact



Double contact



Light block



Possible location



Sequence of Contacts Fitted to 3-position Selector Switch Body

Position 315°



|          |          |        |        |  |        |
|----------|----------|--------|--------|--|--------|
| Push     | Position | Top    |        |  |        |
|          |          | Bottom |        |  |        |
|          | Location |        | Left   |  | Right  |
|          | State    |        | 1      |  | 0      |
|          |          |        |        |  |        |
| Contacts | N/O      |        | closed |  | open   |
|          | N/C      |        | open   |  | closed |

Position 0°



|          |          |        |        |  |        |
|----------|----------|--------|--------|--|--------|
| Push     | Position | Top    |        |  |        |
|          |          | Bottom |        |  |        |
|          | Location |        | Left   |  | Right  |
|          | State    |        | 0      |  | 0      |
|          |          |        |        |  |        |
| Contacts | N/O      |        | open   |  | open   |
|          | N/C      |        | closed |  | closed |

Position 45°



|          |          |        |                                                                                   |                                                                                   |                                                                                   |
|----------|----------|--------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|-----------------------------------------------------------------------------------|
| Push     | Position | Top    |  |  |                                                                                   |
|          |          | Bottom |  |                                                                                   |  |
|          | Location |        | Left                                                                              |                                                                                   | Right                                                                             |
|          | State    |        | 0                                                                                 |                                                                                   | 1                                                                                 |
|          |          |        |                                                                                   |                                                                                   |                                                                                   |
| Contacts | N/O      |        | open                                                                              |                                                                                   | closed                                                                            |
|          | N/C      |        | closed                                                                            |                                                                                   | open                                                                              |

Technical Illustration

Dimensions




Image of product / Alternate images

Alternative

---

