

Product data sheet

Specifications

TeSys Deca - auxiliary contact block - 2 NO



GVAE203

Product availability: Stock - Normally stocked in distribution facility

Main

Range	TeSys TeSys Deca
Device short name	GVAE
Product or Component Type	Auxiliary contact block
Product Compatibility	GV2L GV2P GV2RT GV3P GV2LE GV3L LS1D323 GV2ME
Mounting Location	Front side
Pole contact composition	2 NO
Quantity per Set	Set of 10

Complementary

[Ui] rated insulation voltage	300 V UL 508 300 V CSA C22.2 No 14 250 V IEC 60947-1
[Ue] rated operational voltage	24...240 V AC 24...60 V DC
[Ith] conventional free air thermal current	2.5 A
Mechanical durability	100000 cycles
Minimum switching current	5 mA
Minimum switching voltage	17 V
Protection type	GG fuse 10 A GB2CB06 circuit breaker 10 A
Rated operational power in VA	120 VA 110...120 V AC-15 100000 cycles 120 VA 230...240 V AC-15 100000 cycles 48 VA 24 V AC-15 100000 cycles 60 VA 48 V AC-15 100000 cycles
Rated operational power in W	15 W 48 V DC-13 100000 cycles 24 W 24 V DC-13 100000 cycles 9 W 60 V DC-13 100000 cycles
Height	0.5 in (13 mm)
Width	1.8 in (44.5 mm)
Depth	1.2 in (31.5 mm)
Product Weight	0.11 lb(US) (0.05 kg)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

color	Dark grey
-------	-----------

Environment

Environmental characteristic	Normal environment
Product Certifications	UKCA

Ordering and shipping details

Category	US10I1122367
Discount Schedule	0I11
GTIN	3389110346657
Returnability	Yes
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	0.55 in (1.400 cm)
Package 1 Width	1.26 in (3.200 cm)
Package 1 Length	1.81 in (4.600 cm)
Package weight(Lbs)	0.564 oz (16.000 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	0.98 in (2.500 cm)
Package 2 Width	6.30 in (16.000 cm)
Package 2 Length	6.30 in (16.000 cm)
Package 2 Weight	5.926 oz (168.000 g)
Unit Type of Package 3	S01
Number of Units in Package 3	100
Package 3 Height	5.91 in (15.000 cm)
Package 3 Width	5.91 in (15.000 cm)
Package 3 Length	15.75 in (40.000 cm)
Package 3 Weight	4.098 lb(US) (1.859 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	1
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Technical Illustration

Assembly's dimensions

