

Product data sheet

Specifications



IEC contactor, TeSys Deca,
nonreversing, 200A resistive, 4 pole,
4 NO, 440VDC coil, open style

LC1D115004RD

 To be discontinued on: Dec 31, 2026

 To be discontinued

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Range	TeSys
Range of Product	TeSys Deca
Product or Component Type	Contactors
Device short name	LC1D
Contactors application	Resistive load
Utilisation category	AC-1 AC-3 AC-3e AC-4
Poles description	4P
[Ue] rated operational voltage	Power circuit <= 1000 V AC 25...400 Hz Power circuit <= 460 V DC
[Ie] rated operational current	200 A (at <140 °F (60 °C)) at <= 440 V AC AC-1 for power circuit
[Uc] control circuit voltage	440 V DC

Complementary

Compatibility code	LC1D
Pole contact composition	4 NO
Protective cover	With
[Ith] conventional free air thermal current	200 A (at 140 °F (60 °C)) for power circuit
Irms rated making capacity	1260 A at 440 V for power circuit conforming to IEC 60947
Rated breaking capacity	1100 A at 440 V for power circuit conforming to IEC 60947
[Icw] rated short-time withstand current	250 A 104 °F (40 °C) - 10 min for power circuit 550 A 104 °F (40 °C) - 1 min for power circuit 950 A 104 °F (40 °C) - 10 s for power circuit 1100 A 104 °F (40 °C) - 1 s for power circuit
Associated fuse rating	250 A gG at <= 690 V coordination type 1 for power circuit 200 A gG at <= 690 V coordination type 2 for power circuit
Average impedance	0.6 mOhm - Ith 200 A 50 Hz for power circuit
Power dissipation per pole	24 W AC-1
[Ui] rated insulation voltage	Power circuit 600 V CSA Power circuit 600 V UL Power circuit 1000 V IEC 60947-4-1
Overvoltage category	III

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Pollution degree	3
[Uimp] rated impulse withstand voltage	8 kV IEC 60947
Safety reliability level	B10d = 684932 cycles contactor with nominal load EN/ISO 13849-1 B10d = 10000000 cycles contactor with mechanical load EN/ISO 13849-1
Mechanical durability	8 Mcycles
Electrical durability	0.8 Mcycles 200 A AC-1 <= 440 V
Control circuit type	DC standard
Coil technology	With integral suppression device
Control circuit voltage limits	0.75...1.2 Uc (-40...131 °F (-40...55 °C)):operational DC 0.15...0.4 Uc (-40...158 °F (-40...70 °C)):drop-out DC 1...1.2 Uc (131...158 °F (55...70 °C)):operational DC
Inrush power in W	270...365 W 68 °F (20 °C))
Hold-in power consumption in W	2.4...5.1 W 68 °F (20 °C)
Operating time	20...35 ms closing 40...75 ms opening
Time constant	25 ms
Maximum operating rate	1200 cyc/h at 60 °C
Connections - terminals	Control circuit: screw clamp terminals 2 0.002...0.004 in ² (1...2.5 mm ²) - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 0.002...0.004 in ² (1...2.5 mm ²) - cable stiffness: flexible with cable end Control circuit: screw clamp terminals 1 0.002...0.004 in ² (1...2.5 mm ²) - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 2 0.002...0.004 in ² (1...2.5 mm ²) - cable stiffness: flexible without cable end Control circuit: screw clamp terminals 1 0.002...0.004 in ² (1...2.5 mm ²) - cable stiffness: solid without cable end Control circuit: screw clamp terminals 2 0.002...0.004 in ² (1...2.5 mm ²) - cable stiffness: solid without cable end Power circuit: connector 1 0.02...0.2 in ² (10...120 mm ²) - cable stiffness: flexible without cable end Power circuit: connector 2 0.02...0.08 in ² (10...50 mm ²) - cable stiffness: flexible without cable end Power circuit: connector 1 0.02...0.2 in ² (10...120 mm ²) - cable stiffness: flexible with cable end Power circuit: connector 2 0.02...0.08 in ² (10...50 mm ²) - cable stiffness: flexible with cable end Power circuit: connector 1 0.02...0.2 in ² (10...120 mm ²) - cable stiffness: solid without cable end Power circuit: connector 2 0.02...0.08 in ² (10...50 mm ²) - cable stiffness: solid without cable end
Tightening torque	Control circuit 10.6 lbf.in (1.2 N.m) screw clamp terminals flat Ø 6 mm Control circuit 10.6 lbf.in (1.2 N.m) screw clamp terminals Philips No 2 Power circuit 106.2 lbf.in (12 N.m) connector hexagonal 0.2 in (4 mm) Control circuit 10.6 lbf.in (1.2 N.m) screw clamp terminals pozidriv No 2
Mounting Support	Rail Plate

Environment

Standards	CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508
-----------	---

Product Certifications	GL LROS (Lloyds register of shipping) GOST UL CCC DNV CSA RINA BV UKCA
IP degree of protection	IP20 front face IEC 60529
Protective treatment	THIEC 60068-2-30
Climatic withstand	IACS E10 exposure to damp heat IEC 60947-1 Annex Q category D exposure to damp heat
Permissible ambient air temperature around the device	-40...140 °F (-40...60 °C) 140...158 °F (60...70 °C) with derating
Operating altitude	0...9842.52 ft (0...3000 m)
Fire resistance	1562 °F (850 °C) IEC 60695-2-1
Flame retardance	V1 conforming to UL 94
Mechanical robustness	Vibrations contactor open 2 Gn, 5...300 Hz) Vibrations contactor closed 4 Gn, 5...300 Hz) Shocks contactor closed 15 Gn for 11 ms) Shocks contactor open 6 Gn for 11 ms)
Height	6.2 in (158 mm)
Width	5.9 in (150 mm)
Depth	5.2 in (132 mm)
Product Weight	6.31 lb(US) (2.86 kg)

Ordering and shipping details

Category	US10I1222359
Discount Schedule	0I12
GTIN	3389118075634
Returnability	No
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	7.72 in (19.600 cm)
Package 1 Width	8.31 in (21.100 cm)
Package 1 Length	8.31 in (21.100 cm)
Package weight(Lbs)	6.632 lb(US) (3.008 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	202
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Compliant with Exemptions
SCIP Number	A530c666-91dd-4119-8d61-f1c22a361ecb
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
PVC free	Yes

Use Again

Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.