

# Product data sheet

Specifications



variable speed drive, Altivar  
Machine ATV340, 4kW, heavy duty,  
400V, 3 phases

ATV340U40N4

**Product availability: Stock - Normally stocked in distribution facility**

## Main

|                              |                                                                                                                                                                              |
|------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Range of Product             | Altivar Machine ATV340                                                                                                                                                       |
| Product or Component Type    | Variable speed drive                                                                                                                                                         |
| Product Specific Application | Machine                                                                                                                                                                      |
| Mounting Mode                | Cabinet mount                                                                                                                                                                |
| Variant                      | Standard version                                                                                                                                                             |
| Communication Port Protocol  | Modbus serial                                                                                                                                                                |
| Option card                  | communication module, Profibus DP V1<br>communication module, PROFINET<br>communication module, DeviceNet<br>communication module, CANopen<br>communication module, EtherCAT |
| Phase                        | 3 phase                                                                                                                                                                      |
| Supply frequency             | 50...60 Hz +/- 5 %                                                                                                                                                           |
| [Us] rated supply voltage    | 380...480 V - 15...10 %                                                                                                                                                      |
| nominal output current       | 9.3 A                                                                                                                                                                        |
| Motor power kW               | 5.5 kW normal duty<br>4 kW heavy duty                                                                                                                                        |
| Maximum Horse Power Rating   | 7 hp normal duty<br>5 hp heavy duty                                                                                                                                          |
| EMC filter                   | Class C3 EMC filter integrated                                                                                                                                               |
| IP degree of protection      | IP20                                                                                                                                                                         |

## Complementary

|                         |                                                                                                                                                                                                                                                                           |
|-------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Discrete input number   | 5                                                                                                                                                                                                                                                                         |
| Discrete input type     | PT1 programmable as pulse input 0...30 kHz, 24 V DC 30 V)<br>DI1...DI5 safe torque off, 24 V DC 30 V)3.5 kOhm<br>programmable                                                                                                                                             |
| number of preset speeds | 16 preset speeds                                                                                                                                                                                                                                                          |
| Discrete output number  | 2.0                                                                                                                                                                                                                                                                       |
| Discrete output type    | Programmable output DQ1, DQ2 30 V DC 100 mA                                                                                                                                                                                                                               |
| Analogue input number   | 2                                                                                                                                                                                                                                                                         |
| Analogue input type     | AI1 software-configurable current 0...20 mA 250 Ohm 12 bits<br>AI1 software-configurable temperature probe or water level sensor<br>AI1 software-configurable voltage 0...10 V DC 31.5 kOhm 12 bits<br>AI2 software-configurable voltage - 10...10 V DC 31.5 kOhm 12 bits |
| Analogue output number  | 1                                                                                                                                                                                                                                                                         |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                                     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
|-------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Analogue output type                | Software-configurable voltage AQ1 0...10 V DC 470 Ohm 10 bits<br>Software-configurable current AQ1 0...20 mA 500 Ohm 10 bits                                                                                                                                                                                                                                                                                                                                                         |
| Relay output number                 | 2                                                                                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Output voltage                      | <= power supply voltage                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| Relay output type                   | Relay outputs R1A<br>Relay outputs R1C 100000 cycles<br>Relay outputs R2A<br>Relay outputs R2C 100000 cycles                                                                                                                                                                                                                                                                                                                                                                         |
| Maximum switching current           | Relay output R1C resistive, cos phi = 1 3 A 250 V AC<br>Relay output R1C resistive, cos phi = 1 3 A 30 V DC<br>Relay output R1C inductive, cos phi = 0.4 7 ms 2 A 250 V AC<br>Relay output R1C inductive, cos phi = 0.4 7 ms 2 A 30 V DC<br>Relay output R2C resistive, cos phi = 1 5 A 250 V AC<br>Relay output R2C resistive, cos phi = 1 5 A 30 V DC<br>Relay output R2C inductive, cos phi = 0.4 7 ms 2 A 250 V AC<br>Relay output R2C inductive, cos phi = 0.4 7 ms 2 A 30 V DC |
| Minimum switching current           | Relay output R1B 5 mA 24 V DC<br>Relay output R2C 5 mA 24 V DC                                                                                                                                                                                                                                                                                                                                                                                                                       |
| Physical interface                  | 2-wire RS 485                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| Connector Type                      | 1 RJ45                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| Method of access                    | Slave Modbus RTU                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| Transmission Rate                   | 4.8 kbit/s<br>9.6 kbit/s<br>19.2 kbit/s<br>38.4 kbit/s                                                                                                                                                                                                                                                                                                                                                                                                                               |
| Transmission frame                  | RTU                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |
| Number of addresses                 | 1...247                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| Data format                         | 8 bits, configurable odd, even or no parity                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| Type of polarization                | No impedance                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
| 4 quadrant operation possible       | True                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Asynchronous motor control profile  | Constant torque standard<br>Variable torque standard<br>Optimized torque mode                                                                                                                                                                                                                                                                                                                                                                                                        |
| Synchronous motor control profile   | Permanent magnet motor<br>Reluctance motor                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| Pollution degree                    | 2 IEC 61800-5-1                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| Maximum output frequency            | 0.599 kHz                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| Acceleration and deceleration ramps | Linear adjustable separately from 0.01...9999 s<br>S, U or customized                                                                                                                                                                                                                                                                                                                                                                                                                |
| Motor slip compensation             | Automatic whatever the load<br>Not available in permanent magnet motor law<br>Adjustable<br>Can be suppressed                                                                                                                                                                                                                                                                                                                                                                        |
| Switching frequency                 | 2...16 kHz adjustable<br>4...16 kHz with derating factor                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Nominal switching frequency         | 4 kHz                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
| Braking to standstill               | By DC injection                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| Brake chopper integrated            | True                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Line current                        | 11.4 A 380 V normal duty)<br>9.0 A 480 V normal duty)<br>13.4 A 380 V heavy duty)<br>10.6 A 480 V heavy duty)                                                                                                                                                                                                                                                                                                                                                                        |

|                                                             |                                                                                                                                                                                                                                                                                                             |
|-------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Line current</b>                                         | 13.4 A 380 V without line choke heavy duty)<br>10.6 A 480 V without line choke heavy duty)<br>11.4 A 380 V with external line choke normal duty)<br>9 A 480 V with external line choke normal duty)<br>8.5 A 380 V with external line choke heavy duty)<br>6.8 A 480 V with external line choke heavy duty) |
| <b>Maximum Input Current per Phase</b>                      | 13.4 A                                                                                                                                                                                                                                                                                                      |
| <b>Maximum output voltage</b>                               | 480 V                                                                                                                                                                                                                                                                                                       |
| <b>Apparent power</b>                                       | 9 kVA 480 V normal duty)<br>8.8 kVA 480 V heavy duty)                                                                                                                                                                                                                                                       |
| <b>Maximum transient current</b>                            | 14 A 60 s normal duty)<br>14 A 60 s heavy duty)<br>17.1 A 2 s normal duty)<br>16.7 A 2 s heavy duty)                                                                                                                                                                                                        |
| <b>Electrical connection</b>                                | Screw terminal 1.5...4 mm <sup>2</sup> line side<br>Screw terminal 4...6 mm <sup>2</sup> DC bus<br>Screw terminal 1.5...4 mm <sup>2</sup> motor<br>Screw terminal 0.2...2.5 mm <sup>2</sup> control                                                                                                         |
| <b>Prospective line Isc</b>                                 | 5 kA                                                                                                                                                                                                                                                                                                        |
| <b>Base load current at high overload</b>                   | 9.3 A                                                                                                                                                                                                                                                                                                       |
| <b>Base load current at low overload</b>                    | 12.7 A                                                                                                                                                                                                                                                                                                      |
| <b>Power dissipation in W</b>                               | Natural convection 99 W 380 V 4 kHz heavy duty)<br>Forced convection 99 W 380 V 4 kHz heavy duty)<br>Natural convection 130 W 380 V 4 kHz normal duty)<br>Forced convection 130 W 380 V 4 kHz normal duty)                                                                                                  |
| <b>Electrical connection</b>                                | Line side screw terminal 1.5...4 mm <sup>2</sup> AWG 14...AWG 12<br>DC bus screw terminal 4...6 mm <sup>2</sup> AWG 12...AWG 10<br>Motor screw terminal 1.5...4 mm <sup>2</sup> AWG 14...AWG 12<br>Control screw terminal 0.2...2.5 mm <sup>2</sup> AWG 24...AWG 12                                         |
| <b>With safety function Safely Limited Speed (SLS)</b>      | True                                                                                                                                                                                                                                                                                                        |
| <b>With safety function Safe brake management (SBC/SBT)</b> | True                                                                                                                                                                                                                                                                                                        |
| <b>With safety function Safe Operating Stop (SOS)</b>       | False                                                                                                                                                                                                                                                                                                       |
| <b>With safety function Safe Position (SP)</b>              | False                                                                                                                                                                                                                                                                                                       |
| <b>With safety function Safe programmable logic</b>         | False                                                                                                                                                                                                                                                                                                       |
| <b>With safety function Safe Speed Monitor (SSM)</b>        | False                                                                                                                                                                                                                                                                                                       |
| <b>With safety function Safe Stop 1 (SS1)</b>               | True                                                                                                                                                                                                                                                                                                        |
| <b>With sft fct Safe Stop 2 (SS2)</b>                       | False                                                                                                                                                                                                                                                                                                       |
| <b>With safety function Safe torque off (STO)</b>           | True                                                                                                                                                                                                                                                                                                        |
| <b>With safety function Safely Limited Position (SLP)</b>   | False                                                                                                                                                                                                                                                                                                       |
| <b>With safety function Safe Direction (SDI)</b>            | False                                                                                                                                                                                                                                                                                                       |

|                           |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                 |
|---------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Protection type           | Thermal protection motor<br>Safe torque off motor<br>Motor phase loss motor<br>Thermal protection drive<br>Safe torque off drive<br>Overheating drive<br>Overcurrent drive<br>Output overcurrent between motor phase and earth drive<br>Output overcurrent between motor phases drive<br>Short-circuit between motor phase and earth drive<br>Short-circuit between motor phases drive<br>Motor phase loss drive<br>DC Bus overvoltage drive<br>Line supply overvoltage drive<br>Line supply undervoltage drive<br>Input supply loss drive<br>Exceeding limit speed drive<br>Break on the control circuit drive |
| Width                     | 3.3 in (85.0 mm)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
| Height                    | 10.6 in (270.0 mm)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |
| Depth                     | 9.2 in (232.5 mm)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
| Product Weight            | 4.9 lb(US) (2.2 kg)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| Continuous output current | 12.7 A 4 kHz normal duty<br>9.3 A 4 kHz heavy duty                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                              |

## Environment

|                                                                  |                                                                                                                                                                                                                                                                                                                                                                                                                                  |
|------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Operating altitude                                               | <= 9842.52 ft (3000 m) with current derating above 1000m                                                                                                                                                                                                                                                                                                                                                                         |
| Operating position                                               | Vertical +/- 10 degree                                                                                                                                                                                                                                                                                                                                                                                                           |
| Product Certifications                                           | UL<br>CSA<br>TÜV<br>EAC<br>CTick                                                                                                                                                                                                                                                                                                                                                                                                 |
| Marking                                                          | CE                                                                                                                                                                                                                                                                                                                                                                                                                               |
| Standards                                                        | IEC 61800-3<br>IEC 61800-5-1<br>IEC 60721-3<br>IEC 61508<br>IEC 13849-1<br>UL 618000-5-1<br>UL 508C                                                                                                                                                                                                                                                                                                                              |
| Assembly style                                                   | With heat sink                                                                                                                                                                                                                                                                                                                                                                                                                   |
| Electromagnetic compatibility                                    | Electrostatic discharge immunity test level 3 conforming to IEC 61000-4-2<br>Radiated radio-frequency electromagnetic field immunity test level 3 conforming to IEC 61000-4-3<br>Electrical fast transient/burst immunity test level 4 conforming to IEC 61000-4-4<br>1.2/50 µs - 8/20 µs surge immunity test level 3 conforming to IEC 61000-4-5<br>Conducted radio-frequency immunity test level 3 conforming to IEC 61000-4-6 |
| Environmental class (during operation)                           | Class 3C3 according to IEC 60721-3-3<br>Class 3S3 according to IEC 60721-3-3                                                                                                                                                                                                                                                                                                                                                     |
| Maximum acceleration under shock impact (during operation)       | 70 m/s² at 22 ms                                                                                                                                                                                                                                                                                                                                                                                                                 |
| Maximum acceleration under vibrational stress (during operation) | 5 m/s² at 9...200 Hz                                                                                                                                                                                                                                                                                                                                                                                                             |
| Maximum deflection under vibratory load (during operation)       | 1.5 mm at 2...9 Hz                                                                                                                                                                                                                                                                                                                                                                                                               |
| Permitted relative humidity (during operation)                   | Class 3K5 according to EN 60721-3                                                                                                                                                                                                                                                                                                                                                                                                |
| Volume of cooling air                                            | 5019.4 Gal/hr(US) (19.0 m3/h)                                                                                                                                                                                                                                                                                                                                                                                                    |
| Type of cooling                                                  | Forced convection                                                                                                                                                                                                                                                                                                                                                                                                                |
| Overvoltage category                                             | Class III                                                                                                                                                                                                                                                                                                                                                                                                                        |

|                                       |                                                                                                                                  |
|---------------------------------------|----------------------------------------------------------------------------------------------------------------------------------|
| Regulation loop                       | Adjustable PID regulator                                                                                                         |
| Noise level                           | 49.5 dB                                                                                                                          |
| Pollution degree                      | 2                                                                                                                                |
| Ambient air transport temperature     | -40...158 °F (-40...70 °C)                                                                                                       |
| Ambient air temperature for operation | 5...122 °F (-15...50 °C) without derating vertical position<br>122...140 °F (50...60 °C) with derating factor vertical position) |
| Ambient Air Temperature for Storage   | -40...158 °F (-40...70 °C)                                                                                                       |
| Isolation                             | Between power and control terminals                                                                                              |

## Ordering and shipping details

|                   |               |
|-------------------|---------------|
| Category          | US1CP4B22182  |
| Discount Schedule | CP4B          |
| GTIN              | 3606480966910 |
| Returnability     | Yes           |
| Country of origin | ID            |

## Packing Units

|                              |                            |
|------------------------------|----------------------------|
| Unit Type of Package 1       | PCE                        |
| Nbr. of units in pkg.        | 1                          |
| Package 1 Height             | 4.33 in (11.000 cm)        |
| Package 1 Width              | 14.57 in (37.000 cm)       |
| Package 1 Length             | 12.60 in (32.000 cm)       |
| Package weight(Lbs)          | 6.504 lb(US) (2.950 kg)    |
| Unit Type of Package 2       | S06                        |
| Number of Units in Package 2 | 12                         |
| Package 2 Height             | 29.53 in (75.000 cm)       |
| Package 2 Width              | 23.62 in (60.000 cm)       |
| Package 2 Length             | 31.50 in (80.000 cm)       |
| Package 2 Weight             | 103.617 lb(US) (47.000 kg) |

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

| Environmental footprint                        |                                               |
|------------------------------------------------|-----------------------------------------------|
| Carbon footprint (kg CO2 eq, Total Life cycle) | 3159                                          |
| Environmental Disclosure                       | <a href="#">Product Environmental Profile</a> |

Use Better

| Materials and Substances               |                                                                                                                                                                                                                                                                                             |
|----------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Packaging made with recycled cardboard | Yes                                                                                                                                                                                                                                                                                         |
| Packaging without single use plastic   | Yes                                                                                                                                                                                                                                                                                         |
| <a href="#">EU RoHS Directive</a>      | Pro-active compliance (Product out of EU RoHS legal scope)                                                                                                                                                                                                                                  |
| SCIP Number                            | 81d6792e-d307-4115-9475-2db3f34c93af                                                                                                                                                                                                                                                        |
| REACH Regulation                       | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                                                           |
| California proposition 65              | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |


| Energy efficiency                                  |     |
|----------------------------------------------------|-----|
| Product contributes to saved and avoided emissions | Yes |

Use Again

| Repack and remanufacture |                                                                                                                                                                                                                  |
|--------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Circularity Profile      | <a href="#">End of Life Information</a>                                                                                                                                                                          |
| Take-back                | No                                                                                                                                                                                                               |
| WEEE Label               |  The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |


### Dimensions

**Views: Front - Left - Rear**



Mounting and Clearance


Clearance



| X1    | X2     | X3    |        |      |        |
|-------|--------|-------|--------|------|--------|
| mm    | in.    | mm    | in.    | mm   | in.    |
| ≥ 100 | ≥ 3.94 | ≥ 100 | ≥ 3.94 | ≥ 60 | ≥ 2.36 |


Mounting Types

Mounting Type A: Side by Side IP20



Possible, at ambient temperature  $\leq 50\text{ }^{\circ}\text{C}$  (122  $^{\circ}\text{F}$ )

Mounting Type B: Individual IP20




$a \geq 50\text{ mm}$  (1.97 in.) from 50...60 $^{\circ}\text{C}$ , no restriction below 50 $^{\circ}\text{C}$

Connections and Schema

Connections and Schema

Three-phase Power Supply - Diagram With Line Contactor




(1) : Use relay output R1 set to operating state Fault to switch Off the product once an error is detected.

NOTE :

- Press S1 until the initialization of the drive is finished.
- An external 24V power supply can be connected so that the control part of the drive is always power supplied.

Three-phase Power Supply - Diagram With Downstream Contactor




- (1) : Use relay output R1 set to operating state Fault to switch Off the product once an error is detected.
- (2) : Command of KM2 can be done by using the **[Output contactor cmd]** OCC function. For more information, refer to the programming manual.


**NOTE :**

- Close upstream contactor, then press S1 after the initialization of the drive is finished.
- An external 24V power supply can be connected so that the control part of the drive is always power supplied.

**Sensor Connection**




Control Block Wiring Diagram



- (1) : 24V In, Out, maximum supply current 200 mA is provided,
- (2) : STO - Safe Torque Off, see ATV340 Embedded safety function manual NVE64143
- (3) : PTI - Pulse Train In, from external source (eg.PLC) Pulse - Direction or A-B signals can be connected
- (4) : PTO - Pulse Train Out, can be used to connect to a 2nd ATV340 PTI
- (5) : To connect a motor position feedback encoder
- (6) : Digital output, e.g. to connect a contactor, also usable as DI
- (7) : Digital inputs
- (8) : Analog output, e.g. to connect a meter
- (9) : Analog input, e.g. from potentiometer
- (10) : Differential analog input, e.g. as speed reference from external PLC differential, +/- 10 V
- (11) : 2 advanced Ethernet ports ETH1, ETH2 (ATV340.....E) or 2 Sercos III ports S3P1, S3P2 (ATV340.....S)


Digital Inputs Wiring

Digital Inputs: Internal Supply  
Using DISUP Signal




In SRC position DISUP outputs 24 V. In SK position DISUP is connected to 0 V.


Digital Inputs: External Supply  
Positive Logic, Source, European Style



Negative Logic, Sink, Asian Style




Digital Inputs: Internal supply  
Negative Logic, Sink, Asian Style



Digital Outputs Wiring


Digital Outputs: Internal Supply

Positive Logic, Source, European Style, DQCOM to +24V



(1) Relay or valve


Negative Logic, Sink, Asian Style, DQCOM to 0V



(1) Relay or valve


Digital Outputs: External Supply

Positive Logic, Source, European Style, DQCOM to +24V



(1) Relay or valve


Negative Logic, Sink, Asian Style, DQCOM to 0V



(1) Relay or valve

Performance Curves

Derating Curves



— 40 °C (104 °F) - Mounting type A and B  
- - - 50 °C (122 °F) - Mounting type A and B  
**In** : Nominal Drive Current  
**SF** : Switching Frequency

Technical Illustration

Dimensions

