

Product data sheet

Specifications



Motion controller LMC802 130 axis - Acc kit - Profibus DP + OM RT- Ethernet

LMC802CBL10000

**Product availability: Non-Stock - Not normally stocked in
distribution facility**

Main

Range of Product	PacDrive 3
Product or Component Type	Motion controller

Complementary

Product Compatibility	LMC802
Number of axis	130
Discrete input number	20 digital input IEC 61131-2 Type 1 4 interrupt input IEC 61131-2 Type 1 16 touch probe input IEC 61131-2 Type 1
Discrete input voltage	20...33 V 0...6 V
Discrete input voltage type	DC
Analogue input number	2
Analogue input type	Voltage analog input - 10...10 V Current analog input - 20...20 mA
Analogue input resolution	12 bits
Discrete input current	5 mA digital input 5 mA interrupt input 5 mA touch probe input
Input impedance	100000 Ohm analog input 500 Ohm
Anti bounce filtering	1 ms or 5 ms configurable digital input 100 µs touch probe input 0.1 ms or 1 ms configurable interrupt input
Discrete output number	16 digital output 2 analog output
Discrete output current	250 mA digital output
Maximum leakage current	0.4 mA
Maximum Number of I/O Expansion Module	2
[Us] rated supply voltage	24 V DC
Power consumption in W	36 W
Memory Type	256 kB NVRAM 1 GB RAM DDR3L
Programming language	FBD (function block diagram) CFC (continuous function chart) SFC (sequential function chart) ST (structured text) LD (ladder) IL (instruction list)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Integrated connection type	2 Ethernet port RJ45 Sercos 1 CAN port SUB-D 9 CANopen 1 USB port USB type A 2 Ethernet port RJ45 RT-Ethernet (real-time) 1 Ethernet port RJ45 PacNet 1 port SUB-D 9 Profibus DP 1 COM1 serial link SUB-D 9 RS232 1 COM2 serial link SUB-D 9 RS422/RS485 1 port SUB-D 9 master encoder 1 Ethernet port RJ45 Ethernet 10/100/1000BASE-T, FTP/HTTP
Supply	Power supply 24 VDC, <1 A
Width	3.9 in (100 mm)
Height	12.2 in (310 mm)
Depth	9.6 in (243 mm)
Product Weight	7.7 lb(US) (3.5 kg)

Environment

Standards	CSA C22.2 No 14 UL 508C CSA C22.2 No 274 EN/IEC 61131-2
Product Certifications	CSA EAC CE cULus
Ambient air temperature for operation	41...131 °F (5...55 °C)
Relative humidity	5...95 % without condensation
IP degree of protection	IP20EN/IEC 60529
Pollution degree	2 IEC 61131-2
Vibration resistance	3.5 mm 5...8.4 Hz 10 m/s² 8.4...150 Hz
Shock resistance	150 m/s² 6 ms operation)EN/IEC 60721-3-3

Ordering and shipping details

Category	US1PC5218354
Discount Schedule	PC52
GTIN	3606485458502
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	6.77 in (17.2 cm)
Package 1 Width	12.80 in (32.5 cm)
Package 1 Length	16.73 in (42.5 cm)
Package weight(Lbs)	10.74 lb(US) (4.87 kg)

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

 Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	2188
Environmental Disclosure	Product Environmental Profile

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
PVC free	Yes

Use Again

 Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No