

Product data sheet

Specifications



redundant power supply module, Modicon X80, 24 to 48V DC, safety

BMXCPS4022S

Main

Range of product	Modicon X80
Product or component type	Power supply module
backplane compatibility	All backplane
advanced diagnostics available via network	Redundancy information Redundancy test Remaining lifetime Temperature sensing Uptime duration
Primary voltage	24...48 V
Supply circuit type	DC
Secondary power	18 W 3.3 V DC at -25...60 °C I/O module logic power supply 40 W 24 V DC at -25...60 °C I/O module power supply and processor if 3.3 V not loaded

Complementary

Primary voltage limit	18...62.4 V
Input current	1.9 A 24 V 1 A 48 V
Inrush current	60 A 24 V 60 A 48 V
I²t on activation	1 A².s 24 V 3 A².s 48 V
It on activation	0.3 A.s 24 V 0.4 A.s 48 V
MTBF reliability	721000 H
Protection type	Internal fuse not accessible for primary circuit Overload protection for secondary circuit Overvoltage protection for secondary circuit Short-circuit protection for secondary circuit
Current at secondary voltage	1.67 A 24 V DC I/O module logic power supply 5 A 3.3 V DC I/O module power supply and processor
Maximum power dissipation in W	8.5 W
Status LED	1 LED (green) presence of voltages (OK) 1 LED (green) redundancy OK 1 LED (green) power supply status
Control type	RESET push-button cold restart
Electrical connection	1 connector 2 pin(s) alarm relay 1 connector 5 pin(s) line supply, protective earth
Maximum cable distance between devices	10 m 15 m

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Insulation resistance	>= 100 MOhm primary/ground >= 100 MOhm primary/secondary
Product weight	0.81 kg
Environment	
Immunity to microbreaks	1 ms
Dielectric strength	1500 V primary/ground 1500 V primary/secondary
Vibration resistance	3 gn
Shock resistance	15 gn
IP degree of protection	IP20
Directives	2014/30/EU - electromagnetic compatibility 2006/42/EC - machinery 2014/34/EU - ATEX directive
Product certifications	CE UL CSA RCM EAC Merchant Navy ATEX zone 2/22 IECEx zone 2/22 TÜV
Standards	IEC 61131-2 IEC 61010-2-201 UL 61010-2-201 CSA C22.2 No 61010-2-201 IACS E10 EN/IEC 61000-6-5, interface type 1 and type 2 EN/IEC 61850-3, location G IEC 60079-0
Environmental characteristic	Hazardous location class I division 2 Gas resistant class Gx conforming to ISA S71.04 Gas resistant class 3C4 conforming to IEC 60721-3-3 Dust resistant class 3S4 conforming to IEC 60721-3-3 Sand resistant class 3S4 conforming to IEC 60721-3-3 Salt resistant level 2 conforming to IEC 68252 Mold growth resistant class 3B2 conforming to IEC 60721-3-3 Fungal spore resistant class 3B2 conforming to IEC 60721-3-3
Ambient air temperature for storage	-40...85 °C
Ambient air temperature for operation	-25...60 °C
Relative humidity	5...95 % at 55 °C without condensation
Protective treatment	Conformal coating
Operating altitude	0...2000 m 2000...5000 m with derating factor
Packing Units	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	9.000 cm
Package 1 Width	18.000 cm
Package 1 Length	25.000 cm
Package 1 Weight	679.000 g
Unit Type of Package 2	S03

Number of Units in Package 2	6
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.790 kg

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

 Environmental footprint	
Total lifecycle Carbon footprint	497
Environmental Disclosure	Product Environmental Profile

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	41745a42-b2d7-4938-80f8-0738cea8ed1d
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

 Repack and remanufacture	
End of life manual availability	End of Life Information
Take-back	No

Image of product / Alternate images

Alternative





