

Product data sheet

Specifications



APC Smart-UPS C, Line Interactive, 1440VA, Tower, 120V, 8x NEMA 5-15R outlets, SmartConnect port, USB and Serial communication, AVR, Graphic LCD

SMC1500C

Overview

Lead time Usually Ships within 2 Weeks

Main

Product or component type Uninterruptible power supply (UPS)

Complementary

Communication port type SmartConnect Ethernet port

Software package SmartConnect software for remote power monitoring feature availability varies by terms of use

Batteries & Runtime

Run Time [View Runtime Graph](#)

Efficiency [View Efficiency Graph](#)

Battery type Lead-acid battery

Extended runtime 0

Number of battery filled slots 0

Number of battery free slots 0

Battery recharge time 3 h

Number of battery replacement quantity 1

Battery life 3...5 year(s)

Replacement battery [RBC6](#)

Battery charger power 96 W rated

General

Provided equipment USB cable

Number of power module 0

Number of power module filled slots 0

Number of power module free slots 0

product web sub-family Cloud-enabled monitoring

Redundant No

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Physical

Cable length	1.8 m
Number of cables	1
Colour	Black
Height	21.9 cm
Width	17.1 cm
Depth	43.9 cm
Product weight	20.1 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	Yes

Input

Main Input Voltage	120 V
Other Input Voltage	110 V 125 V
Input Connection Type	NEMA 5-15P
Input voltage limits	85...136 V adjustable 93...130 V
Network frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Main Output Voltage	120 V
Other Output Voltage	110 V 125 V
Rated power in W	900 W
rated power in VA	1440 VA
output connection type	8 NEMA 5-15R
Harmonic distortion	Less than 5 %
Maximum configurable power in VA	1440 VA
Maximum configurable power in W	900 W
Transfer time	6 ms typical : 10 ms maximum
UPS type	Line interactive
Wave type	Sine wave
Output frequency	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product certifications	cULus ENERGY STAR V2.0 (USA)
Equipment protection policy	Lifetime : \$150000

Environmental

Acoustic level	45 dBA
Heat dissipation	225 Btu/h
Operating altitude	0...10000 ft
Ambient air temperature for operation	0...40 °C
Ambient air temperature for storage	-15...45 °C
Storage altitude	0...15240 m
Relative humidity	0...95 %
Storage Relative Humidity	0...95 %

Communications & Management

Control panel	Multifunction LCD status and control console
Free slots	0
Communication port support	SmartConnect Ethernet port: for cloud monitoring feature availability varies by terms of use
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays

Surge Protection and Filtering

Surge energy rate	680 J
Noise suppression	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	33 cm
Package 1 Width	59 cm
Package 1 Length	33 cm
Package 1 Weight	22.64 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Total lifecycle Carbon footprint	1093
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant with Exemptions
SCIP Number	B2b22a56-41f2-497e-9ea6-cf093b3b8bd3
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Energy efficiency	
Energy Efficiency Optimized	Energy efficient product
 ENERGY STAR®	ENERGY STAR UPS V2.0 (USA)

Use Again

Repack and remanufacture	
End of life manual availability	End of Life Information
Removable battery	User replaceable
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Technical Illustration

Dimensions



Image of product / Alternate images

Alternative

