



### Overview

|              |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                         |
|--------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Presentation | APC Metered by Outlet with Switching Rack Power Distribution Units (PDUs) enable advanced, user-customizable power control and individual outlet power metering. Remote outlet level controls allow power on/off functionality for power recycling to reboot locked-up equipment and to avoid unauthorized use of individual outlets. Power sequencing delays allow users to define the order in which to power up or down attached equipment. Avoid circuit overload during power recovery and extend uptime of critical equipment by prioritizing the load shedding. Current metering provides real-time remote monitoring of connected loads. Switched Rack PDUs include real power monitoring, a temperature/humidity sensor port, and locking IEC receptacles. User-defined alarms warn of potential circuit overloads before critical IT failures occur. Users can access, configure, and control Switched rack PDUs through secure Web, SNMP, or Telnet Interfaces and is complimented by APC Centralized Management platforms using InfraStruxure Central, Capacity Manager and Change Manager. |
| Lead time    | Usually in Stock                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |

### Main

|                     |                                                                                                                   |
|---------------------|-------------------------------------------------------------------------------------------------------------------|
| Main Input Voltage  | 3 phase                                                                                                           |
| Main Output Voltage | 208 V                                                                                                             |
| Plug standard       | NEMA L21-20P                                                                                                      |
| Number of rack unit | 0U                                                                                                                |
| Cable length        | 6 ft (1.83 m)                                                                                                     |
| Number of cables    | 1                                                                                                                 |
| Provided Equipment  | CAN Port Terminator<br>Installation guide<br>Rack Mounting brackets<br>Safety guide<br>Serial configuration cable |

### Physical

|                     |                        |
|---------------------|------------------------|
| Color               | Black                  |
| Height              | 72.01 in (182.9 cm)    |
| Width               | 2.20 in (5.6 cm)       |
| Depth               | 2.01 in (5.1 cm)       |
| Net Weight          | 15.74 lb(US) (7.14 kg) |
| Mounting Location   | Side                   |
| Mounting preference | No preference          |
| Mounting Mode       | Rack-mounted           |
| USB compatible      | No                     |

## Input

|                      |          |
|----------------------|----------|
| Line Rated Current   | 16 A     |
| Max line current     | 20 A     |
| Input current limits | 20 A     |
| Load Capacity        | 5700 VA  |
| Input Frequency      | 50/60 Hz |

## Output

|                                |                                     |
|--------------------------------|-------------------------------------|
| Number of power socket outlets | 21 IEC 60320 C13<br>3 IEC 60320 C19 |
|--------------------------------|-------------------------------------|

## Conformance

|                        |                                         |
|------------------------|-----------------------------------------|
| Product Certifications | CUL Listed<br>UL Listed<br>VCCI Class A |
| Standards              | FCC Part 15 class A<br>ICES-003         |

## Environmental

|                                       |                                  |
|---------------------------------------|----------------------------------|
| Ambient Air Temperature for Operation | 23...140 °F (-5...60 °C)         |
| Relative Humidity                     | 5...95 %                         |
| Operating altitude                    | 0...10000 ft                     |
| Ambient Air Temperature for Storage   | -13...149 °F (-25...65 °C)       |
| Storage Relative Humidity             | 5...95 %                         |
| Storage altitude                      | 0...50000 ft (0.00...15240.00 m) |

## Ordering and shipping details

|                     |                        |
|---------------------|------------------------|
| GTIN                | 731304276999           |
| Package weight(Lbs) | 20.75 lb(US) (9.41 kg) |

## Packing Units

|                              |                     |
|------------------------------|---------------------|
| Package 1 Height             | 80.24 in (203.8 cm) |
| Package 1 width              | 6.38 in (16.2 cm)   |
| Package 1 Length             | 4.65 in (11.8 cm)   |
| Number of Units in Package 3 | 48                  |

## Offer Sustainability

|                             |                                                                                                                                   |
|-----------------------------|-----------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status    | Green Premium product                                                                                                             |
| REACH Regulation            |  <a href="#">REACH Declaration</a>             |
| EU RoHS Directive           | Compliant  <a href="#">EU RoHS Declaration</a> |
| Lead free                   | Yes                                                                                                                               |
| Mercury free                | Yes                                                                                                                               |
| RoHS exemption information  |  <a href="#">Yes</a>                           |
| Environmental Disclosure    |  <a href="#">Product Environmental Profile</a> |
| Circularity Profile         |  <a href="#">End Of Life Information</a>       |
| Optimized Energy Efficiency | Energy efficient product                                                                                                          |
| Take-back                   | Take-back program available                                                                                                       |

## Contractual warranty

|          |                           |
|----------|---------------------------|
| Warranty | 2 years repair or replace |
|----------|---------------------------|