

SMT1500CUS

APC Smart-UPS, Line Interactive, 1500VA,
Tower, 120V, 8x NEMA 5-15R outlets,
SmartConnect Port+SmartSlot, AVR, LCD,
TAA



Overview

Lead time	Usually Ships within 2 Weeks
-----------	------------------------------

Main

Main Input Voltage	120 V
Other Input Voltage	110 V 125 V
Main Output Voltage	120 V
Other Output Voltage	110 V 125 V
Rated power in W	1000 W
Rated power in VA	1440 VA
Input Connection Type	NEMA 5-15P
Output connection type	8 NEMA 5-15R
Cable length	6 ft (1.83 m)
Number of cables	1
Battery Type	Lead-Acid battery
Provided equipment	CD with software USB cable

General

Number of power module filled slots	0
Number of power module free slots	0
Product web sub-family	Cloud-enabled monitoring
Redundant	No

Physical

Color	Black
Height	8.62 in (21.9 cm)
Width	6.73 in (17.1 cm)
Depth	17.28 in (43.9 cm)
Net Weight	54.23 lb(US) (24.6 kg)
Mounting Location	Front
Mounting preference	No preference

Mounting Mode	Not rack-mountable
Two post mountable	0
USB compatible	Yes

Input

Efficiency at full load	75...154 V adjustable 82...144 V
Input Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic distortion	Less than 5%
Maximum configurable power in VA	1440 VA
Max Configurable Power (Watts)	1000 W
Transfer Time	6ms typical : 10ms maximum
Topology	Line Interactive
Waveform Type	Sine wave
Output Frequency (sync to mains)	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	CULus ENERGY STAR V2.0 (USA)
Equipment protection policy	Lifetime : \$150000

Environmental

Acoustic level	45 dBA
Heat dissipation	225 Btu/h
Operating altitude	0...10000 ft
Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage altitude	0...50000 ft (0.00...15240.00 m)
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %

Batteries & Runtime

Extendable Run Time	0
Included Battery Modules	0
Battery Slots Empty	0
Typical recharge time	3 h
RBC Quantity	1
Battery Life	3...5 year(s)
Battery power in VAh	408 VAh runtime
Battery Charge Power (Watts)	136 W rated

Communications & Management

Control panel	Multi-function LCD status and control console
Free slots	1

Surge Protection and Filtering

Surge energy rating	680 J
Filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : m

Ordering and shipping details

GTIN	731304424413
------	--------------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Offer Sustainability

EU RoHS Directive	Under investigation
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	3 Years
----------	---------