

# LC1D183P7

IEC contactor, TeSys Deca, nonreversing,  
18A, 10HP at 480VAC, 3 phase, 3 pole, 3 NO,  
230VAC 50/60Hz coil, open style



## Main

|                                |                                                                                                                                                                    |
|--------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Range of Product               | TeSys Deca                                                                                                                                                         |
| Product or Component Type      | Contacteur                                                                                                                                                         |
| Device short name              | LC1D                                                                                                                                                               |
| Contacteur application         | Motor control<br>Resistive load                                                                                                                                    |
| Utilisation category           | AC-3<br>AC-1<br>AC-4<br>AC-3e                                                                                                                                      |
| Poles description              | 3P                                                                                                                                                                 |
| [Ue] rated operational voltage | Power circuit <= 690 V AC 25...400 Hz<br>Power circuit <= 300 V DC                                                                                                 |
| [Ie] rated operational current | 18 A 140 °F (60 °C)) <= 440 V AC AC-3 power circuit<br>32 A 140 °F (60 °C)) <= 440 V AC AC-1 power circuit<br>18 A 140 °F (60 °C)) <= 440 V AC AC-3e power circuit |
| [Uc] control circuit voltage   | 230 V AC 50/60 Hz                                                                                                                                                  |

## Complementary

|                                             |                                                                                                                                                                                                                                                                                                                                                                                                                           |
|---------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Motor power kW                              | 4 KW 220...230 V AC 50/60 Hz AC-3)<br>7.5 KW 380...400 V AC 50/60 Hz AC-3)<br>9 KW 415...440 V AC 50/60 Hz AC-3)<br>10 KW 500 V AC 50/60 Hz AC-3)<br>10 KW 660...690 V AC 50/60 Hz AC-3)<br>4 KW 400 V AC 50/60 Hz AC-4)<br>4 KW 220...230 V AC 50/60 Hz AC-3e)<br>7.5 KW 380...400 V AC 50/60 Hz AC-3e)<br>9 KW 415...440 V AC 50/60 Hz AC-3e)<br>10 KW 500 V AC 50/60 Hz AC-3e)<br>10 kW 660...690 V AC 50/60 Hz AC-3e) |
| Maximum Horse Power Rating                  | 1 Hp 115 V at AC 50/60 Hz for 1 phase<br>3 Hp 230/240 V at AC 50/60 Hz for 1 phase<br>5 Hp 200/208 V at AC 50/60 Hz for 3 phase<br>5 Hp 230/240 V at AC 50/60 Hz for 3 phase<br>10 Hp 460/480 V at AC 50/60 Hz for 3 phase<br>15 hp 575/600 V at AC 50/60 Hz for 3 phase                                                                                                                                                  |
| Compatibility code                          | LC1D                                                                                                                                                                                                                                                                                                                                                                                                                      |
| Pole contact composition                    | 3 NO                                                                                                                                                                                                                                                                                                                                                                                                                      |
| Contact compatibility                       | M2                                                                                                                                                                                                                                                                                                                                                                                                                        |
| Protective cover                            | With                                                                                                                                                                                                                                                                                                                                                                                                                      |
| [Ith] conventional free air thermal current | 25 A 140 °F (60 °C) power circuit<br>10 A 140 °F (60 °C) signalling circuit                                                                                                                                                                                                                                                                                                                                               |
| Irms rated making capacity                  | 140 A AC signalling circuit IEC 60947-5-1<br>250 A DC signalling circuit IEC 60947-5-1<br>300 A 440 V power circuit IEC 60947                                                                                                                                                                                                                                                                                             |
| Rated breaking capacity                     | 300 A 440 V power circuit IEC 60947                                                                                                                                                                                                                                                                                                                                                                                       |

|                                          |                                                                                                                                                                                                                                                                                                                                                                                                                                          |
|------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| [Icw] rated short-time withstand current | 145 A 104 °F (40 °C) - 10 s power circuit<br>240 A 104 °F (40 °C) - 1 s power circuit<br>40 A 104 °F (40 °C) - 10 min power circuit<br>84 A 104 °F (40 °C) - 1 min power circuit<br>100 A - 1 s signalling circuit<br>120 A - 500 ms signalling circuit<br>140 A - 100 ms signalling circuit                                                                                                                                             |
| Associated fuse rating                   | 10 A gG signalling circuit IEC 60947-5-1<br>50 A gG ≤ 690 V type 1 power circuit<br>35 A gG ≤ 690 V type 2 power circuit                                                                                                                                                                                                                                                                                                                 |
| Average impedance                        | 2.5 mOhm - Ith 25 A 50 Hz power circuit                                                                                                                                                                                                                                                                                                                                                                                                  |
| Power dissipation per pole               | 2.5 W AC-1<br>0.8 W AC-3<br>0.8 W AC-3e                                                                                                                                                                                                                                                                                                                                                                                                  |
| [Ui] rated insulation voltage            | Power circuit 690 V IEC 60947-4-1<br>Power circuit 600 V CSA<br>Power circuit 600 V UL<br>Signalling circuit 690 V IEC 60947-1<br>Signalling circuit 600 V CSA<br>Signalling circuit 600 V UL                                                                                                                                                                                                                                            |
| Overvoltage category                     | III                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| Pollution degree                         | 3                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| [Uimp] rated impulse withstand voltage   | 6 kV IEC 60947                                                                                                                                                                                                                                                                                                                                                                                                                           |
| Safety reliability level                 | B10d = 1369863 cycles contactor with nominal load EN/ISO 13849-1<br>B10d = 2000000 cycles contactor with mechanical load EN/ISO 13849-1                                                                                                                                                                                                                                                                                                  |
| Mechanical durability                    | 15 Mcycles                                                                                                                                                                                                                                                                                                                                                                                                                               |
| Electrical durability                    | 1.65 Mcycles 18 A AC-3 ≤ 440 V<br>1 Mcycles 32 A AC-1 ≤ 440 V<br>1.65 Mcycles 25 A AC-3e ≤ 440 V                                                                                                                                                                                                                                                                                                                                         |
| Control circuit type                     | AC 50/60 Hz                                                                                                                                                                                                                                                                                                                                                                                                                              |
| Coil technology                          | Without built-in suppressor module                                                                                                                                                                                                                                                                                                                                                                                                       |
| Control circuit voltage limits           | 0.3...0.6 Uc -40...158 °F (-40...70 °C) drop-out AC 50/60 Hz<br>0.8...1.1 Uc -40...140 °F (-40...60 °C) operational AC 50 Hz<br>0.85...1.1 Uc -40...140 °F (-40...60 °C) operational AC 60 Hz<br>1...1.1 Uc 140...158 °F (60...70 °C) operational AC 50/60 Hz                                                                                                                                                                            |
| Inrush power in VA                       | 70 VA 60 Hz 0.75 68 °F (20 °C))<br>70 VA 50 Hz 0.75 68 °F (20 °C))                                                                                                                                                                                                                                                                                                                                                                       |
| Hold-in power consumption in VA          | 7.5 VA 60 Hz 0.3 68 °F (20 °C))<br>7 VA 50 Hz 0.3 68 °F (20 °C))                                                                                                                                                                                                                                                                                                                                                                         |
| Heat dissipation                         | 2...3 W 50/60 Hz                                                                                                                                                                                                                                                                                                                                                                                                                         |
| Operating time                           | 12...22 ms closing<br>4...19 ms opening                                                                                                                                                                                                                                                                                                                                                                                                  |
| Maximum operating rate                   | 3600 cyc/h 140 °F (60 °C)                                                                                                                                                                                                                                                                                                                                                                                                                |
| Connections - terminals                  | Control circuit spring terminals 1 0.00 in <sup>2</sup> (2.5 mm <sup>2</sup> ) flexible without cable end<br>Control circuit spring terminals 2 0.00 in <sup>2</sup> (2.5 mm <sup>2</sup> ) flexible without cable end<br>Power circuit spring terminals 1 0.01 in <sup>2</sup> (4 mm <sup>2</sup> ) flexible without cable end<br>Power circuit spring terminals 2 0.01 in <sup>2</sup> (4 mm <sup>2</sup> ) flexible without cable end |
| Auxiliary contact composition            | 1 NO + 1 NC                                                                                                                                                                                                                                                                                                                                                                                                                              |
| Auxiliary contacts type                  | Mechanically linked 1 NO + 1 NC IEC 60947-5-1<br>Mirror contact 1 NC IEC 60947-4-1                                                                                                                                                                                                                                                                                                                                                       |
| Signalling circuit frequency             | 25...400 Hz                                                                                                                                                                                                                                                                                                                                                                                                                              |
| Minimum switching voltage                | 17 V signalling circuit                                                                                                                                                                                                                                                                                                                                                                                                                  |
| Minimum switching current                | 5 mA signalling circuit                                                                                                                                                                                                                                                                                                                                                                                                                  |
| Insulation resistance                    | > 10 MOhm signalling circuit                                                                                                                                                                                                                                                                                                                                                                                                             |
| Non-overlap time                         | 1.5 Ms on de-energisation between NC and NO contact<br>1.5 ms on energisation between NC and NO contact                                                                                                                                                                                                                                                                                                                                  |
| Mounting Support                         | Plate<br>Rail                                                                                                                                                                                                                                                                                                                                                                                                                            |

## Environment

|                                                       |                                                                                                                                                                                    |
|-------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Standards                                             | CSA C22.2 No 14<br>EN 60947-4-1<br>EN 60947-5-1<br>IEC 60947-4-1<br>IEC 60947-5-1<br>UL 508<br>IEC 60335-1                                                                         |
| Product Certifications                                | LROS (Lloyds register of shipping)<br>RINA<br>DNV<br>GOST<br>BV<br>CSA<br>CCC<br>GL<br>UL<br>UKCA                                                                                  |
| IP degree of protection                               | IP20 front face IEC 60529                                                                                                                                                          |
| Protective treatment                                  | THIEC 60068-2-30                                                                                                                                                                   |
| Climatic withstand                                    | IACS E10 exposure to damp heat<br>IEC 60947-1 Annex Q category D exposure to damp heat                                                                                             |
| Permissible ambient air temperature around the device | -40...140 °F (-40...60 °C)<br>140...158 °F (60...70 °C) with derating                                                                                                              |
| Operating altitude                                    | 0...9842.52 ft (0...3000 m)                                                                                                                                                        |
| Fire resistance                                       | 1562 °F (850 °C) IEC 60695-2-1                                                                                                                                                     |
| Flame retardance                                      | V1 conforming to UL 94                                                                                                                                                             |
| Mechanical robustness                                 | Vibrations contactor open 2 Gn, 5...300 Hz)<br>Vibrations contactor closed 4 Gn, 5...300 Hz)<br>Shocks contactor open 10 Gn for 11 ms)<br>Shocks contactor closed 15 Gn for 11 ms) |
| Height                                                | 3.90 in (99 mm)                                                                                                                                                                    |
| Width                                                 | 1.77 in (45 mm)                                                                                                                                                                    |
| Depth                                                 | 3.39 in (86 mm)                                                                                                                                                                    |
| Net Weight                                            | 0.73 lb(US) (0.33 kg)                                                                                                                                                              |

## Ordering and shipping details

|                   |                                    |
|-------------------|------------------------------------|
| Category          | 22354-CTR, TESYS D, OPEN, 9-38A AC |
| Discount Schedule | I12                                |
| GTIN              | 3389110803785                      |
| Returnability     | No                                 |
| Country of origin | ID                                 |

## Packing Units

|                              |                         |
|------------------------------|-------------------------|
| Unit Type of Package 1       | PCE                     |
| Number of Units in Package 1 | 1                       |
| Package 1 Height             | 2.17 in (5.5 cm)        |
| Package 1 Width              | 4.13 in (10.5 cm)       |
| Package 1 Length             | 4.72 in (12 cm)         |
| Package 1 Weight             | 15.41 oz (437 g)        |
| Unit Type of Package 2       | S02                     |
| Number of Units in Package 2 | 15                      |
| Package 2 Height             | 5.91 in (15 cm)         |
| Package 2 Width              | 11.81 in (30 cm)        |
| Package 2 Length             | 15.75 in (40 cm)        |
| Package 2 Weight             | 15.71 lb(US) (7.126 kg) |
| Unit Type of Package 3       | P06                     |
| Number of Units in Package 3 | 240                     |
| Package 3 Height             | 29.53 in (75 cm)        |
| Package 3 Width              | 23.62 in (60 cm)        |

|                  |                          |
|------------------|--------------------------|
| Package 3 Length | 31.50 in (80 cm)         |
| Package 3 Weight | 274.48 lb(US) (124.5 kg) |

## Offer Sustainability

|                            |                                                                                                                                                                                                                                                           |
|----------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                                                                                                                                                                     |
| California proposition 65  | WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                         |
| REACH free of SVHC         | Yes                                                                                                                                                                                                                                                       |
| EU RoHS Directive          | Compliant <a href="#">EU RoHS Declaration</a>                                                                                                                                                                                                             |
| Toxic heavy metal free     | Yes                                                                                                                                                                                                                                                       |
| Mercury free               | Yes                                                                                                                                                                                                                                                       |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                                                                                                                                                                                                    |
| RoHS exemption information | <a href="#">Yes</a>                                                                                                                                                                                                                                       |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                                                                                                                                                                             |
| Circularity Profile        | <a href="#">End Of Life Information</a>                                                                                                                                                                                                                   |
| WEEE                       | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.                                                                                                                              |
| PVC free                   | Yes                                                                                                                                                                                                                                                       |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|