

# Product data sheet

Specifications



Control relay, TeSys Deca,  
3NO+2NC, <=690V, 12V DC  
standard coil, screw clamp terminals

CAD32JD

## Main

|                           |                     |
|---------------------------|---------------------|
| Range                     | TeSys<br>TeSys Deca |
| Product name              | TeSys CAD           |
| Product or component type | Control relay       |
| Device short name         | CAD                 |
| Contactor application     | Control circuit     |

## Complementary

|                                             |                                                                                                                                                                                                                                                                                                                                                                                                                                    |
|---------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Utilisation category                        | AC-14<br>AC-15<br>DC-13                                                                                                                                                                                                                                                                                                                                                                                                            |
| Pole contact composition                    | 3 NO + 2 NC                                                                                                                                                                                                                                                                                                                                                                                                                        |
| [Ue] rated operational voltage              | <= 690 V AC 25...400 Hz                                                                                                                                                                                                                                                                                                                                                                                                            |
| Control circuit type                        | DC standard                                                                                                                                                                                                                                                                                                                                                                                                                        |
| [Uc] control circuit voltage                | 12 V DC                                                                                                                                                                                                                                                                                                                                                                                                                            |
| [Uimp] rated impulse withstand voltage      | 6 kV conforming to IEC 60947                                                                                                                                                                                                                                                                                                                                                                                                       |
| [Ith] conventional free air thermal current | 10 A (at 60 °C)                                                                                                                                                                                                                                                                                                                                                                                                                    |
| Irms rated making capacity                  | 140 A AC conforming to IEC 60947-5-1<br>250 A DC conforming to IEC 60947-5-1                                                                                                                                                                                                                                                                                                                                                       |
| [Icw] rated short-time withstand current    | 100 A - 1 s<br>120 A - 500 ms<br>140 A - 100 ms                                                                                                                                                                                                                                                                                                                                                                                    |
| Associated fuse rating                      | 10 A gG conforming to IEC 60947-5-1                                                                                                                                                                                                                                                                                                                                                                                                |
| [Ui] rated insulation voltage               | 600 V UL certified<br>600 V CSA certified<br>690 V conforming to IEC 60947-5-1                                                                                                                                                                                                                                                                                                                                                     |
| Mounting support                            | Plate<br>Rail                                                                                                                                                                                                                                                                                                                                                                                                                      |
| Connections - terminals                     | Screw clamp terminals 1 cable(s) 1...4 mm²flexible without cable end<br>Screw clamp terminals 2 cable(s) 1...4 mm²flexible without cable end<br>Screw clamp terminals 1 cable(s) 1...4 mm²flexible with cable end<br>Screw clamp terminals 2 cable(s) 1...2.5 mm²flexible with cable end<br>Screw clamp terminals 1 cable(s) 1...4 mm²solid without cable end<br>Screw clamp terminals 2 cable(s) 1...4 mm²solid without cable end |
| Tightening torque                           | 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2<br>1.7 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm<br>1.7 N.m - on screw clamp terminals - with screwdriver pozidriv No 2                                                                                                                                                                                                                     |
| Control circuit voltage limits              | 0.1...0.25 Uc (-40...70 °C):drop-out DC<br>0.7...1.25 Uc (-40...60 °C):operational DC<br>1...1.25 Uc (60...70 °C):operational DC                                                                                                                                                                                                                                                                                                   |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                                |                                                                                                                                                                                                                                                                                                                      |
|--------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Operating time                 | 53...72 ms coil energisation and NO closing<br>16...24 ms coil de-energisation and NO opening<br>47...63 ms coil energisation and NC opening<br>15...25 ms coil de-energisation and NC closing                                                                                                                       |
| Mechanical durability          | 30 Mcycles                                                                                                                                                                                                                                                                                                           |
| Maximum operating rate         | 180 cyc/mn                                                                                                                                                                                                                                                                                                           |
| Time constant                  | 28 ms                                                                                                                                                                                                                                                                                                                |
| Inrush power in W              | 5.4 W (at 20 °C)                                                                                                                                                                                                                                                                                                     |
| Hold-in power consumption in W | 5.4 W at 20 °C                                                                                                                                                                                                                                                                                                       |
| Minimum switching voltage      | 17 V                                                                                                                                                                                                                                                                                                                 |
| Minimum switching current      | 5 mA                                                                                                                                                                                                                                                                                                                 |
| Non-overlap time               | 1.5 ms on energisation between NC and NO contact<br>1.5 ms on de-energisation between NC and NO contact                                                                                                                                                                                                              |
| Insulation resistance          | > 10 MOhm                                                                                                                                                                                                                                                                                                            |
| Mechanical robustness          | Shocks control relay open: 10 Gn for 11 ms conforming to IEC 60068-2-27<br>Shocks control relay closed: 15 Gn for 11 ms conforming to IEC 60068-2-27<br>Vibrations control relay open: 2 Gn, 5...300 Hz conforming to IEC 60068-2-6<br>Vibrations control relay closed: 4 Gn, 5...300 Hz conforming to IEC 60068-2-6 |
| Height                         | 77 mm                                                                                                                                                                                                                                                                                                                |
| Width                          | 45 mm                                                                                                                                                                                                                                                                                                                |
| Depth                          | 93 mm                                                                                                                                                                                                                                                                                                                |
| Product weight                 | 0.58 kg                                                                                                                                                                                                                                                                                                              |

## Environment

|                                       |                                                                                             |
|---------------------------------------|---------------------------------------------------------------------------------------------|
| Standards                             | EN/IEC 60947-5-1<br>GB/T 14048.5<br>UL 60947-5-1<br>CSA C22.2 No 60947-5-1<br>JIS C8201-5-1 |
| Product certifications                | CB<br>CCC<br>UL<br>CSA<br>EAC<br>CE<br>UKCA                                                 |
| IP degree of protection               | IP2X front face conforming to VDE 0106                                                      |
| Protective treatment                  | TH conforming to IEC 60068                                                                  |
| Ambient air temperature for operation | -40...60 °C<br>60...70 °C with derating                                                     |
| Ambient air temperature for storage   | -60...80 °C                                                                                 |
| Operating altitude                    | 0...3000 m                                                                                  |

## Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Height             | 4.900 cm  |
| Package 1 Width              | 11.100 cm |
| Package 1 Length             | 8.900 cm  |
| Package 1 Weight             | 529.000 g |

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 2       | S02       |
| Number of Units in Package 2 | 15        |
| Package 2 Height             | 15.000 cm |
| Package 2 Width              | 30.000 cm |
| Package 2 Length             | 40.000 cm |
| Package 2 Weight             | 8.302 kg  |
| Unit Type of Package 3       | P06       |
| Number of Units in Package 3 | 120       |
| Package 3 Height             | 45.000 cm |
| Package 3 Width              | 60.000 cm |
| Package 3 Length             | 80.000 cm |
| Package 3 Weight             | 75.260 kg |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

| Environmental footprint          |                                               |
|----------------------------------|-----------------------------------------------|
| Total lifecycle Carbon footprint | 38                                            |
| Environmental Disclosure         | <a href="#">Product Environmental Profile</a> |

Use Better

| Materials and Substances               |                                                                                                                                                                                                                                                           |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Packaging made with recycled cardboard | Yes                                                                                                                                                                                                                                                       |
| Packaging without single use plastic   | No                                                                                                                                                                                                                                                        |
| <a href="#">EU RoHS Directive</a>      | Compliant with Exemptions                                                                                                                                                                                                                                 |
| SCIP Number                            | B67ac941-f42f-4afd-894a-0b6f9cefde62                                                                                                                                                                                                                      |
| REACH Regulation                       | <a href="#">REACH Declaration</a>                                                                                                                                                                                                                         |
| California proposition 65              | WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |

Use Again

| Repack and remanufacture        |                                                                                                                                                                                                                 |
|---------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| End of life manual availability | <a href="#">End of Life Information</a>                                                                                                                                                                         |
| Take-back                       | No                                                                                                                                                                                                              |
| WEEE Label                      |  The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |

Image of product / Alternate images

Alternative

---



