

# Product data sheet

Specifications



Illuminated selector switch,  
Harmony XB4, metal, green handle,  
30mm, universal LED, 3 positions,  
1NO + 1NC, 110...120V AC

XB4FK133G5

**Product availability:** Non-Stock - Not normally stocked in distribution facility

**Important message:** A change in appearance may be noted on the product but does not affect its use in terms of function and safety. This makes it compatible with our Universal LED blocks

## Main

|                               |                                                                                                                                          |
|-------------------------------|------------------------------------------------------------------------------------------------------------------------------------------|
| Range of Product              | Harmony XB4                                                                                                                              |
| Product or Component Type     | Illuminated selector switch                                                                                                              |
| Device short name             | XB4F                                                                                                                                     |
| Bezel material                | Chromium plated metal                                                                                                                    |
| Fixing collar material        | Zamak                                                                                                                                    |
| Head type                     | Built-in-flush                                                                                                                           |
| Mounting diameter             | 1.2 in (30.5 mm)                                                                                                                         |
| Sale per indivisible quantity | 1                                                                                                                                        |
| Shape of signaling unit head  | Round                                                                                                                                    |
| Type of operator              | stay put                                                                                                                                 |
| Operator profile              | Green standard handle                                                                                                                    |
| Operator position information | 3 positions +/- 45°                                                                                                                      |
| Contacts type and composition | 1 NO + 1 NC                                                                                                                              |
| Contact operation             | Slow-break                                                                                                                               |
| Connections - terminals       | Screw clamp terminals, <= 2 x 1.5 mm² with cable end IEC 60947-1<br>Screw clamp terminals, >= 1 x 0.22 mm² without cable end IEC 60947-1 |
| Light source                  | Universal LED                                                                                                                            |
| Bulb base                     | Integral LED                                                                                                                             |
| [Us] rated supply voltage     | 110...120 V AC 50/60 Hz                                                                                                                  |

## Complementary

|                                    |                                              |
|------------------------------------|----------------------------------------------|
| Height                             | 2.09 in (53 mm)                              |
| Width                              | 1.4 in (36.6 mm)                             |
| Depth                              | 2.7 in (69.5 mm)                             |
| Terminals description ISO n°1      | (13-14)NO<br>(21-22)NC                       |
| Product Weight                     | 0.333 lb(US) (0.151 kg)                      |
| Resistance to high pressure washer | 1015.3 psi (7000000 Pa) 131 °F (55 °C) 0.1 m |
| Device mounting                    | Built-in 1.21 in (30.75 mm) +/- 0.25 mm      |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                                             |                                                                                                                                                                                                                                                                                                                                                                                       |
|---------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Fixing mode                                 | By screws 7.08 lbf.in (0.8 N.m) 0.8...1.2 Nm)                                                                                                                                                                                                                                                                                                                                         |
| Contacts usage                              | Standard contacts                                                                                                                                                                                                                                                                                                                                                                     |
| Positive opening                            | With NC contact IEC 60947-5-1 appendix K                                                                                                                                                                                                                                                                                                                                              |
| Operating torque                            | 1.24 lbf.in (0.14 N.m) NO changing electrical state                                                                                                                                                                                                                                                                                                                                   |
| Mechanical durability                       | 500000 cycles                                                                                                                                                                                                                                                                                                                                                                         |
| Tightening torque                           | 7.08...10.6 lbf.in (0.8...1.2 N.m) IEC 60947-1                                                                                                                                                                                                                                                                                                                                        |
| Shape of screw head                         | Cross Philips no 1<br>Cross pozidriv No 1<br>Slotted flat Ø 4 mm<br>Slotted flat Ø 5.5 mm                                                                                                                                                                                                                                                                                             |
| Contacts material                           | Silver alloy (Ag/Ni)                                                                                                                                                                                                                                                                                                                                                                  |
| Short-circuit protection                    | 10 A cartridge fuse gG IEC 60947-5-1                                                                                                                                                                                                                                                                                                                                                  |
| [Ith] conventional free air thermal current | 10 A IEC 60947-5-1                                                                                                                                                                                                                                                                                                                                                                    |
| [Ui] rated insulation voltage               | 600 V 3)IEC 60947-1                                                                                                                                                                                                                                                                                                                                                                   |
| [Uimp] rated impulse withstand voltage      | 6 kV IEC 60947-1                                                                                                                                                                                                                                                                                                                                                                      |
| [Ie] rated operational current              | 3 A 240 V, AC-15, A600 IEC 60947-5-1<br>6 A 120 V, AC-15, A600 IEC 60947-5-1<br>0.1 A 600 V, DC-13, Q600 IEC 60947-5-1<br>0.27 A 250 V, DC-13, Q600 IEC 60947-5-1<br>0.55 A 125 V, DC-13, Q600 IEC 60947-5-1<br>1.2 A 600 V, AC-15, A600 IEC 60947-5-1                                                                                                                                |
| Electrical durability                       | 1000000 cycles, AC-15, 2 A 230 V 3600 cyc/h 0.5 EN 60947-5-1 appendix C<br>1000000 cycles, AC-15, 3 A 120 V 3600 cyc/h 0.5 EN 60947-5-1 appendix C<br>1000000 cycles, AC-15, 4 A 24 V 3600 cyc/h 0.5 EN 60947-5-1 appendix C<br>1000000 cycles, DC-13, 0.2 A 110 V 3600 cyc/h 0.5 EN 60947-5-1 appendix C<br>1000000 cycles, DC-13, 0.5 A 24 V 3600 cyc/h 0.5 EN 60947-5-1 appendix C |
| Electrical reliability                      | $\Lambda < 10\exp(-6)$ 5 V 1 mA in clean environment IEC 60947-5-4<br>$\Lambda < 10\exp(-8)$ 17 V 5 mA in clean environment IEC 60947-5-4                                                                                                                                                                                                                                             |
| Signalling type                             | Steady                                                                                                                                                                                                                                                                                                                                                                                |
| Supply voltage limits                       | 100...132 V AC                                                                                                                                                                                                                                                                                                                                                                        |
| Current Consumption                         | 14 mA                                                                                                                                                                                                                                                                                                                                                                                 |
| Service life                                | 100000 h at rated voltage and 25 °C                                                                                                                                                                                                                                                                                                                                                   |
| Surge withstand                             | 1 kV IEC 61000-4-5                                                                                                                                                                                                                                                                                                                                                                    |
| Device presentation                         | Complete product                                                                                                                                                                                                                                                                                                                                                                      |

## Environment

|                                       |                                                                                                                                                  |
|---------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------|
| Protective treatment                  | TH                                                                                                                                               |
| Ambient Air Temperature for Storage   | -40...158 °F (-40...70 °C)                                                                                                                       |
| Ambient Air Temperature for Operation | -40...158 °F (-40...70 °C)                                                                                                                       |
| Electrical shock protection class     | Class I conforming to IEC 60536                                                                                                                  |
| IP degree of protection               | IP66 IEC 60529<br>IP67 IEC 60529<br>IP69 IEC 60529<br>IP69K ISO 20653<br>Type 13 UL 50 E<br>Type 12 UL 50 E<br>Type 4 UL 50 E<br>Type 4X UL 50 E |
| IK degree of protection               | IK04 conforming to IEC 50102                                                                                                                     |

|                                       |                                                                                                                                                                           |
|---------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Standards                             | CSA C22.2 No 14<br>IEC 60947-5-1<br>IEC 60947-5-4<br>UL 508<br>IEC 60947-1<br>JIS C8201-5-1<br>CE<br>JIS C8201-1                                                          |
| Product Certifications                | UL Listed<br>CSA<br>CCC<br>EAC                                                                                                                                            |
| Vibration resistance                  | 5 gn (f= 10...500 Hz) conforming to IEC 60068-2-6<br>2 mm peak to peak (f= 2...10 Hz) conforming to IEC 60068-2-6                                                         |
| Shock resistance                      | 30 gn 18 ms) half sine wave acceleration IEC 60068-2-27<br>50 gn 11 ms) half sine wave acceleration IEC 60068-2-27<br>25 gn 6 ms) 1000 shocks on each axis IEC 60068-2-27 |
| Resistance to fast transients         | 2 kV IEC 61000-4-4                                                                                                                                                        |
| Resistance to electromagnetic fields  | 9.1 V/m (10 V/m) IEC 61000-4-3                                                                                                                                            |
| Resistance to electrostatic discharge | 6 kV on contact (on metal parts) IEC 61000-4-2<br>8 kV in free air (in insulating parts) IEC 61000-4-2                                                                    |
| Electromagnetic emission              | Class B IEC 55011                                                                                                                                                         |

## Ordering and shipping details

|                   |               |
|-------------------|---------------|
| Category          | US10CS222468  |
| Discount Schedule | 0CS2          |
| GTIN              | 3606489580384 |
| Returnability     | Yes           |
| Country of origin | FR            |

## Packing Units

|                        |                      |
|------------------------|----------------------|
| Unit Type of Package 1 | PCE                  |
| Nbr. of units in pkg.  | 1                    |
| Package 1 Height       | 3.39 in (8.600 cm)   |
| Package 1 Width        | 1.69 in (4.300 cm)   |
| Package 1 Length       | 2.05 in (5.200 cm)   |
| Package weight(Lbs)    | 5.326 oz (151.000 g) |

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

| Environmental footprint                        |    |
|------------------------------------------------|----|
| Carbon footprint (kg CO2 eq, Total Life cycle) | 49 |

Use Better


| Materials and Substances               |                                                                                                                                                                                                                                                                                             |
|----------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Packaging made with recycled cardboard | No                                                                                                                                                                                                                                                                                          |
| Packaging without single use plastic   | No                                                                                                                                                                                                                                                                                          |
| <a href="#">EU RoHS Directive</a>      | Pro-active compliance (Product out of EU RoHS legal scope)                                                                                                                                                                                                                                  |
| SCIP Number                            | 51477834-6557-463b-9186-97e1bf9e303d                                                                                                                                                                                                                                                        |
| California proposition 65              | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |

Use Again

| Repack and remanufacture |                                                                                                                                                                                                                  |
|--------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Take-back                | No                                                                                                                                                                                                               |
| WEEE Label               |  The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Dimensions Drawings

Dimensions




e : clamping thickness: 1 to 6 mm / 0.04 to 0.24 in.  
(1) : Additional row of contacts

Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

Connection by Screw Clamp Terminals or Plug-in Connectors




- (1) : Diameter on finished panel or support  
(2) : Ø30.75 mm recommended ( $\text{Ø}30.5 \begin{smallmatrix} +0.5 \\ 0 \end{smallmatrix}$ ) / Ø1.21 in. recommended ( $\text{Ø}1.20 \text{ in. } \begin{smallmatrix} +0.0196 \\ 0 \end{smallmatrix}$ )

| Connections                                 | a in mm | a in in. | b in mm | b in in. |
|---------------------------------------------|---------|----------|---------|----------|
| By connectors                               | 50      | 1.97     | 40      | 1.57     |
| By connectors and with legend holder ZBZF32 | 50      | 1.97     | 40      | 1.57     |
| By connectors and with legend holder ZBZF33 | 60      | 2.36     | 40      | 1.57     |


Technical Illustration

Dimensions



Offer Marketing Illustration

Product benefits / Features





Offer Marketing Illustration

Product benefits / Features

---

### Features

Harmony XB4



Quick and easy assembly and disassembly



Various types of connection: screw clamp, connector, Faston connector, spring terminal, or printed circuit board



Excellent mechanical connection with operator head



Large set of accessories to customize your panels



Robustness to withstand harsh environments



Image of product / Alternate images

Alternative

---

