






THE INFORMATION CONTAINED HEREIN IS CONSIDERED "PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE COPIED, REPRODUCED OR DISCLOSED WITHOUT THE WRITTEN APPROVAL OF BEL FUSE INC.

RoHS



NOTES:

Material:

1. Housing Material : Glass Filled Polyester UL94V-0.
2. Contact Mateial : Phosphor Bronze t=0.35mm.
3. Plating : Contact Area- Selective 50u" Gold Plating.
4. Shield : Copper Alloy 0.20mm Thickness Plating Ni .
5. LED : Option.

Feature:

1. RJ45 10/100/1000 Base-Tx Transformer Jack With Transformer /Impedance Resistor/High Voltage Capacitor.
2. Designed To Meet IEEE 802.3ab Requirement.
3. Designed For 1000 Base Transmission over UTP-5 Cable.
4. Operation Temperature Range: 0°C To+70°C.



Mechanical:

1. Operating Life : 750 Cycles Min.
2. Pcb Retention Pre-Solder : 1 Lb Min.

Environmental:

1. Storage : -40°C To+85°C.

Mates With Modular Plug Conforming To Fcc PART 68, Subpart F.



SUGGESTED CUSTOMER BOARD LAYOUT

P01-1CC0-01

PART NUMBER

DRAWN 15Mar2024
TOWER YU / FRANK LIU

CHECKED 15Mar2024
BILL LIU

APPROVED 15Mar2024
TONY YUAN

TITLE

Gigabit MagJack[®]
(WITHT LED)
PATENTED

DRAWING NO.


P01-1CC0

FILE NAME

P01-1CC0_2.DWG

UNLESS OTHERWISE
NOTED, TOL:

X.	±0.38
.X	±0.38
.XX	±0.25
.XXX	±0.13



SIZE:	A4
UNIT:	mm
SCALE:	N/A
PAGE:	1/3
REV.:	2



a bel group

This document is electronically generated. This is a controlled copy if used internally

Please read our datasheet & drawing disclaimer [here](#).


THE INFORMATION CONTAINED HEREIN IS CONSIDERED "PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE COPIED, REPRODUCED OR DISCLOSED WITHOUT THE WRITTEN APPROVAL OF BEL FUSE INC.

RoHS



Schematic

PHY SIDE



Electrical Specification @ 25°C

PARAMETER	SPECIFICATIONS	
URNS RATIO	1.00 ± 2%	
POLARITY	PER SCHEMATIC	
INSERTION LOSS (DATA CHANNELS)	100 KHz-125MHz	
	-1.2 dB MAX	
RETURN LOSS (Z OUT=100 OHM ±1%)	0.5-40 MHz	40 MHz-100 MHz
	-18 dB MIN	-12+20LOG(f/80MHz)dB
CROSS TALK LOSS	1-100 MHz	
	-30 dB MIN	
COMMON MODE REJECTION RATIO	1-100 MHz	
	-30 dB MIN	
INDUCTANCE (OCL)	350 uH MIN @ 100 KHz, 100 mV, 8mA DC BIAS	
HIPOT-OUTPUT ISOLATION	2250 VDC MIN @ 60 SECONDS	

DRAWN	15Mar2024
TOWER YU / FRANK LIU	
CHECKED	15Mar2024
BILL LIU	
APPROVED	15Mar2024
TONY YUAN	

TITLE
Gigabit MagJack ®
(WITHT LED)
PATENTED

DRAWING NO.	P01-1CC0
FILE NAME	P01-1CC0_2.DWG

UNLESS OTHERWISE NOTED, TOL:			
X.		SIZE:	A4
.X		UNIT:	mm
.XX		SCALE:	N/A
.XXX		PAGE: 2/3	REV.: 2



THE INFORMATION CONTAINED HEREIN IS CONSIDERED "PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE COPIED, REPRODUCED OR DISCLOSED WITHOUT THE WRITTEN APPROVAL OF BEL FUSE INC.

RoHS




CHANGE HISTORY						
ISSUE	DATE	DESCRIPTIN OF CHANGE	REASON	DRAWN	APPROVAL	ECN#
1	15MAR2024	—	INITIAL RELEASE	TOWER YU	TONY YUAN	—
2	01APR2024	Page 1: change 10.54 to 10.80; change 21.16 to 21.46	PRODUCT IMPROVE	TOWER YU	TONY YUAN	—

DRAWN	15Mar2024
TOWER YU / FRANK LIU	
CHECKED	15Mar2024
BILL LIU	
APPROVED	15Mar2024
TONY YUAN	

TITLE	Gigabit MagJack [®] (WITHT LED) PATENTED
--------------	---

DRAWING NO.	P01-1CC0
FILE NAME	P01-1CC0_2.DWG

UNLESS OTHERWISE NOTED, TOL:			
X.		SIZE:	A4
.X		UNIT:	mm
.XX		SCALE:	N/A
.XXX		PAGE: 3/3	REV.: 2



bel
a bel group

MAGNETIC SOLUTIONS