



Main

Range of Product	Altivar
Accessory / separate part category	Mounting and fixing accessory
Accessory / Separate Part Type	Mounting kit
Product compatibility	Variable speed drive ATV900 250 kW, 380...480 V Variable speed drive ATV900 315 kW, 380...480 V ATV61HC25N4 with braking unit ATV61HC25N4D with braking unit ATV61HC25Y with braking unit ATV61HC31N4 with braking unit ATV61HC31N4D with braking unit ATV61HC31Y with braking unit ATV61HC40Y with braking unit ATV71HC20N4 with braking unit ATV71HC20N4D with braking unit ATV71HC20Y with braking unit ATV71HC25N4 with braking unit ATV71HC25N4D with braking unit ATV71HC25Y with braking unit ATV71HC28N4 with braking unit ATV71HC28N4D with braking unit ATV71HC31Y with braking unit
Accessory / separate part destination	Variable speed drive with braking unit
Range Compatibility	Altivar&Nbsp;Process ATV900 Altivar 61 Altivar 71
Product Specific Application	For mounting the drive power section outside the enclosure

Complementary

Kit composition	1 cutting and drilling template 1 fan support 1 user manual 1 metal frame of the right size for drive rating Corner pieces Fixing accessories seals
Net Weight	10.36 lb(US) (4.7 kg)

Environment

Environmental characteristic	Dust and damp proof
------------------------------	---------------------

Ordering and shipping details

Category	22135-ATV61-71 ACCESSORIES
Discount Schedule	CP4C
GTIN	3389119202046
Returnability	No
Country of origin	CN

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.94 in (10.0 cm)
Package 1 Width	11.81 in (30.0 cm)
Package 1 Length	43.31 in (110.0 cm)
Package 1 Weight	11.68 lb(US) (5.3 kg)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------