



DATE	DESCRIPTION	REV.
7.18.14	CHANGE AS OER ECN 14-066 SPLIT C/M DRAWING TO 'C' & 'M'	A
8.02.19	CHANGE AS PER ECN 19-063 B1 WAS 12.40mm	B
2.25.25	CHANGE AS PER PCN 25-010 ADDED PACKAGING DETAILS.	C


FRONT SHELL









INSERTED BODY



REAR SHELL



ASSEMBLED PLUG



PLUG SPECIFICATIONS:

SHELL: MAT'L- STEEL

FINISH- NICKEL PLATE

INSULATION: MAT'L- THERMOPLASTIC, UL 94V-0
(COLOR- BLUE)

CONTACT: MAT'L- PHOSPHOR BRONZE
ON SOLDER AREA

FINISH- TIN PLATE, OVER NICKEL
ON CONTACT AREA

FINISH- GOLD FLASH OVER NICKEL

ELECTRICAL CHARACTERISTICS:

RATED VOLTAGE: 30V (RMS)

CONTACT CURRENT RATING: 1 Amp DC MAX.

CONTACT RESISTANCE: 15mΩ min.

DIELECTRIC WITHSTANDING VOLTAGE: 750V AC FOR 1 MINUTE

MECHANICAL CHARACTERISTICS:

OPERATING TEMPERATURE: -13°F (-25°C) TO 176°F (+80°C)

DURABILITY: 1500 CYCLES MIN.

PACKAGING DETAILS: 100 PIECES PER BAG.

KEYSTONE ELECTRONICS CORP.				
www.keystelco.com • NEW HYDE PARK, NY 11040 • Tel (516) 328-7500				
PART NAME				
USB 3.0 TYPE A PLUG KIT				
MATERIAL				
AS NOTED				
FINISH		DRN BY		
AS NOTED		NT		
TOLERANCES		DATE		
INCH	[MM]	4.07.10		
DECIMAL	± .010 [± 0.25]	SCALE		
ANGULAR	± 1°	APPD	1.5X	
UNLESS OTHERWISE SPECIFIED		CODE	DWG. NO.	
		C	947	

THIS DOCUMENT IS THE PROPERTY OF
KEYSTONE ELECTRONICS CORP. AND
SHALL NOT BE REPRODUCED, DISTRIBUTED
OR USED AS A BASIS FOR MANUFACTURE
WITHOUT PRIOR WRITTEN PERMISSION
FROM KEYSTONE ELECTRONICS CORP.