

Product data sheet

Specifications



Full voltage nonversing starter,
TeSys Deca, 3P, Type 12/3R, 9A,
120VAC coil, unfused

LE1D093A72OG70

Product availability: Stock - Normally stocked in distribution facility

Main

Product or Component Type	Full voltage starter
Range of Product	Instakits
Starter Type	Non reversing

Complementary

Control Circuit Voltage	120 V AC 50/60 Hz
Current Rating	9 A
Horsepower Rating	0.3 hp 120 V AC, 1 phase 1 hp 240 V AC, 1 phase 2 hp 208 V AC, 3 phase 2 hp 230 V AC, 3 phase 5 hp 460 V AC, 3 phase 7.5 hp 575 V AC, 3 phase
Maximum Voltage Rating	600 V AC
Auxiliary Contacts	1 NO + 1 NC
Location of connection	Line

Environment

Product Certifications	IEC UL CSA
Enclosure Type	NEMA 12 steel

Ordering and shipping details

Category	US10I1122313
Discount Schedule	0I11
GTIN	785901466048
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	10.70 in (27.178 cm)
Package 1 Width	9.40 in (23.876 cm)
Package 1 Length	14.60 in (37.084 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package weight(Lbs)	10.900 lb(US) (4.944 kg)
---------------------	--------------------------

Contractual warranty

Warranty	18 months
----------	-----------

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant
California proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to www.P65Warnings.ca.gov
PVC free	Yes

Use Again

Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.