

GVSBPSU80K120H

Maintenance Bypass Panel, single unit,
80-120kW 400V wallmount, for Galaxy VS and
Easy UPS 3S/3M



Overview

Presentation	Maintenance bypass panel for complete isolation of the UPS during service operations.
Lead time	Usually Ships within 2 Weeks

Physical

Color	White
Height	31.50 in (80 cm)
Width	23.62 in (60 cm)
Depth	11.02 in (28 cm)
Net Weight	88.18 lb(US) (40 kg)
Mounting Location	Front
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Ambient Air Temperature for Storage	-13...131 °F (-25...55 °C)

Ordering and shipping details

GTIN	731304344490
Package weight(Lbs)	132.28 lb(US) (60 kg)

Packing Units

Package 1 Height	47.24 in (120 cm)
Package 1 width	31.50 in (80 cm)
Package 1 Length	21.26 in (54 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Optimized Energy Efficiency	Energy efficient product
Take-back	Take-back program available