

Product data sheet

Specifications



Auxiliary contact block,Easy TeSys GP2E,1NO+1NC

GPEFC11

Product availability: Stock - Normally stocked in distribution facility

Main

Range	Easy TeSys
Device short name	GPEFC
Product or Component Type	Auxiliary contact block
Mounting Location	Front side
Pole contact composition	1 NO + 1 NC
Connections - terminals	Screw clamp terminals1 0.002...0.004 in² (1...2.5 mm²) - solid Screw clamp terminals2 0.002...0.004 in² (1...2.5 mm²) - solid Screw clamp terminals1 0.001...0.004 in² (0.75...2.5 mm²) - flexible without cable end Screw clamp terminals2 0.001...0.004 in² (0.75...2.5 mm²) - flexible without cable end Screw clamp terminals1 0.001...0.002 in² (0.75...1.5 mm²) - flexible with cable end
Quantity per Set	Set of 10

Complementary

[Ui] rated insulation voltage	300 V UL 60947-4-1 300 V cUL 250 V IEC 60947-1
[Ue] rated operational voltage	24...240 V AC 24...60 V DC
[Ith] conventional free air thermal current	2.5 A
Mechanical durability	100000 cycles
Minimum switching current	5 mA
Minimum switching voltage	17 V
Protection type	GG fuse 10 A GB2CB06 circuit breaker 10 A
Rated operational power in VA	120 VA 110...120 V AC-15 100000 cycles 120 VA 230...240 V AC-15 100000 cycles 48 VA 24 V AC-15 100000 cycles 60 VA 48 V AC-15 100000 cycles
Rated operational power in W	15 W 48 V DC-13 100000 cycles 24 W 24 V DC-13 100000 cycles 9 W 60 V DC-13 100000 cycles
Tightening torque	12.4 lbf.in (1.4 N.m) screw clamp terminals
Height	0.4 in (11 mm) 0.6 in (15.5 mm)
Width	1.8 in (45 mm) 1.8 in (45 mm)
Depth	1.1 in (29 mm) 1.6 in (41 mm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Net Weight	0.04 lb(US) (0.02 kg)
	0.057 lb(US) (0.026 kg)
color	Dark grey

Environment

Environmental characteristic	Normal environment
------------------------------	--------------------

Ordering and shipping details

Category	US10I1322364
Discount Schedule	0I13
GTIN	3606481063496
Returnability	Yes
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	0.50 in (1.27 cm)
Package 1 Width	1.30 in (3.3 cm)
Package 1 Length	1.80 in (4.57 cm)
Package weight(Lbs)	0.04 lb(US) (0.02 kg)
Unit Type of Package 2	S02
Number of Units in Package 2	220
Package 2 Height	5.91 in (15 cm)
Package 2 Width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Package 2 Weight	10.752 lb(US) (4.877 kg)

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Carbon footprint (kg CO2 eq, Total Life cycle)	1
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Compliant
REACH Regulation	REACH Declaration
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Again

Repack and remanufacture	
Circularity Profile	End of Life Information
Take-back	No

Image of product / Alternate images

Alternative



