

BATTERY DRIVE, FTP-60D Series

2" HIGH SPEED THERMAL PRINTER

FTP-62DMCL101#02-R/111#02-R

Easy Loading Method

■ OVERVIEW

The 2-inch (58mm), FTP-62DMCL series is an ultra compact, low voltage thermal printer mechanism with a removable platen for easy paper loading and maintenance.

The FTP-62D MCL series can be used for a variety of low voltage applications, such as portable terminals, POS, banking terminals, and measurement and medical equipment.



FTP-62D series

■ HIGHLIGHTS

- **Easy loading type**
Our unique removable platen mechanism improves paper loading and maintenance, providing a better customer experience
- **Ultra compact**
The compact design (19mm x 69.5mm x 46mm) allows you to reduce the overall footprint of your design
- **High speed printing**
Print at 100mm/s (at 9.5VDC) maximum
Print at 75mm/s (at 7.2 VDC) maximum
- **High resolution printing**
8 dots/mm of resolution printing is possible
- **Straight paper path**
- **RoHS compliant**

FTP-62DMCL101#02-R/111#02-R

■ PART NUMBERS

Item		Part number
Printers		FTP-62DMCL101#02-R (FPC length 38mm) without platen detect switch FTP-62DMCL111#02-R (FPC length 65mm) without platen detect switch
LSI for driving		FTP-62DCU001-R
Interface boards	USB/RS-232C	FTP-62DDSL001-R
Interface cables	USB	FTP-62GY301-R
Power cable (head, motor, logic) & RS232C interface cable		FTP-62DY001-12-R
Platen replacement		FTP-62DMP0221-R

■ SPECIFICATIONS

Item	Specifications
Part number	FTP-62DMCL101#02-R/111#02-R
Printing method	Thermal-line dot method
Dot structure	384 dots/line
Dot pitch (Horizontal)	0.125 mm (8 dots/mm)—Dot density
Dot pitch (Vertical)	0.125 mm (8 dots/mm)—Line feed pitch
Effective printing area	48 mm
Number of columns	ANK 32 columns/line (maximum 12x 24 dot font)
Paper width	58 mm ⁺⁰ ₋₁
Paper thickness	60 to 85 μ m (some paper in this range may not be used because of paper characteristics)
Printing Speed	Maximum 100mm/sec. (800 dot line/sec.) at 9.5V*1 Maximum 80mm/sec. (640 dot line/sec.) at 8.5VDC *2
Character types	Alphanumeric, katakana: 159 types International and special characters: 195 types
Character, dimensions (H×W), number of columns	12 × 24 dots, (1.5 × 3.0mm), 32 columns: ANK 8 × 16 dots, (1.0 × 2.0 mm), 48 columns: ANK 8 × 6 dots, 48 columns: International 12 × 24 dots, (1.5 × 3.0 mm), 32 columns: International

Notes:

*1: Head voltage 9.5V, ambient temperature 25°C, concurrent applied dots 64 dots maximum, applied energy S.L.T. =1.25ms/line, E0Maz=0.235mJ/dot maximum, use PD150R (Oji Paper)

*2 Head voltage 8.5V, ambient temperature 25°C, concurrent applied dots 64 dots maximum, applied energy S.L.T. =1.56ms/line, E0Maz=0.27mJ/dot maximum, use PD150R (Oji Paper)

FTP-62DMCL101#02-R/111#02-R

■ SPECIFICATIONS

Item		Specification
		FTP-62DMCL101#02-R/111#02-R
Interface		Conforms to RS232C / USB
Operating Voltage	For print head	4.2 VDC to 9.5 V, approx. 2.3A at 25°C, rav=176Ω, concurrently electrified with 64 dots
	For motor	4.2 to 9.5VDC, 1A maximum
	For logic	3.3VDC ±10% or 5VDC±10%, 0.1 A maximum
Dimensions	Printer mechanism	69.5 x 46 x 19mm (WxDxH)
	Interface board	33 x 24mm
Weight	Printer mechanism	Approximately 31g
	Interface board	Approximately 5g
Head life		Pulse resistance: 100 million pulses/dot (under our standard conditions). Abrasion resistance: paper traveling distance 50km (print ratio: 12.5 % or less)
Operating environment	Operating temperature*	0°C to +50°C
	Operating humidity	20 to 85% RH (no condensation)
	Storage temperature	-20°C to +60°C (paper not included)
	Storage humidity	5 to 95% RH (no condensation)
Detection function	Head temperature detection	Detected by thermistor
	Paper out/mark detection	Detected by photo-interrupter
Recommended thermal sensitive paper		High sensitive paper: TF50KS-E4 (Nippon Paper)
		Standard paper TK60KS-E (Nippon Paper) PD150R (Oji Paper)
		Medium life storage paper TK60KS-F1 (Nippon Paper) PD170R (Oji Paper) P220VBB-1 (Mitsubishi Paper)
		Long life storage paper PD160R-N (Oji Paper)

*+5°C to +40°C printing density assurance range (-25 to 70°C capability)

FTP-62DMCL101#02-R/111#02-R


■ FUNCTION

Item	Item
1. Test print function	8. Mark detection function
2. Paper out detection	9. MCU operation abnormality detection
3. Paper near end detection	10. Power ON/OFF sequence protection
4. Thermal head temperature abnormality detection	11. Motor over-current protection
5. Blow-out fuse detection	12. Hardware timer
6. Head voltage abnormality detection	
7. Motor power saving function	

■ DIMENSIONS

1. Printer mechanism: 2- inch

FTP-62DMCL101*/111**



Unit: mm

Note: 1. Dimensions are nominal value (tolerance ± 0.5 unless otherwise specified).
2. Dimension listed in () is for reference

FTP-62DMCL101#02-R/111#02-R

■ PRINTER CONNECTOR (FLEXIBLE PT BOARD) PIN ARRAYS

Thermal head, control circuit side connector: 54104-4031 Molex or equivalent product

No.	Symbol	I/O	Signal Name
1	N.C.	-	No connection
2	N.C	-	
3	COM	I	Head drive power
4	COM	I	
5	COM	I	
6	COM	I	
7	SI	I	Data in
8	CLK	I	Clock
9	GND	-	Head ground
10	GND	-	
11	GND	-	
12	GND	-	
13	STB6	I	Strobe 6
14	STB5	I	Strobe 5
15	STB4	I	Strobe 4
16	Vdd	I	Logic power
17	TM	O	Thermistor
18	TM	O	
19	STB3	I	Strobe 3
20	STB2	I	Strobe 2
21	STB1	I	Strobe 1
22	GND	-	Head ground
23	GND	-	
24	GND	-	
25	GND	-	
26	/LAT	I	/ Data latch
27	SI	O	Data out
28	COM	I	Head drive power
29	COM	I	
30	COM	I	
31	COM	I	
32	N.C.	-	No connection
33	PHK	-	Cathode for photo interrupter
34	VSEN	I	Paper sensor power
35	PHE	O	Emitter for photo interruptor
36	N.C.	-	No connection
37	MT A	I	Excitation signal A
38	MT /A	I	Excitation signal /A
39	MT B	I	Excitation signal B
40	MT /B	I	Excitation signal /B

Do not plug or unplug the FPC when power is on.

FTP-62DMCL101#02-R/111#02-R

Contact

MEIKO ELECTRONIC COMPONENTS CO., LTD.

935, Nosakada, Oaza, Iiyama-shi,
Nagano, 389-2233, Japan
Tel: (81-3) 0269-62-1155

Copyright

All trademarks or registered trademarks are the property of their respective owners. Meiko Electronic Components Co., Ltd. does not warrant that the content of datasheet is error free. In a continuing effort to improve our products Meiko Electronic Components Co., Ltd. reserves the right to change specifications/datasheets without prior notice.

Copyright ©2026 Meiko Electronic Components Co.,Ltd. All rights reserved. Revised June 1, 2026.
