

## AUTOMOTIVE RELAY FOR EV/PHV ON-BOARD CHARGER

### 1 POLE – 40A

## FTR-K5 Series

RoHS Compliant

#### ■ FEATURES

- 1 pole 40A, 1a contact
- 32A 250VAC switching which corresponds 6.6kW standard charger
- 40A continuous power supply
- Vibration resistance and shock resistance meet automotive relay specification standards
- Operable at up to +105°C ambient temperature
- High insulation
  - Between coil and contact creepage distance 8.8mm  
(Conform to IEC61810-1 277V enhanced insulation)
  - Between coil and contact withstand voltage 5000 VAC
- Selectable from flux free and plastic sealed
- Plastic parts: UL flammability 94V-0
- Through hole



#### ■ APPLICATIONS

EV/PHV on-board charger (standard charger AC line), Standard charger, Vehicle to Home (V2H), Package air conditioner (PAC)

#### ■ PART NUMBERS

[Example] FTR-K5 A A 005 Y  
 (a) (b) (c) (d) (e)

(a)	Relay type	FTR-K5	: FTR-K5 series
(b)	Contact configuration	A	: 1a (1 form A)
(c)	Power consumption / Enclosure	A	: 900mW / Plastic sealed
		K	: 900mW / Flux free
(d)	Coil voltage	Coil code	: Refer to COIL DATA
(e)	Contact material	Y	: Silver alloy

Note: The designation name is stamped on the top of the relay case as follows:

Example: Ordering part number; FTR-K5AA005Y

Stamped on relay case: K5AA005Y

## ■ SPECIFICATIONS

Item		Specifications		Remarks / Conditions
		Plastic sealed	Flux free	
Contact Data	Configuration	1a (1 form A)		
	Material	Silver alloy		
	Construction	Single contact		
	Contact rating	32A 250VAC		Resistive
	Drop voltage (Initial)	Max. 0.32V		At 32A
	Resistance	Max. 10mΩ		At 32A
	Max. carrying current	40A (at 105°C, cable size 8mm <sup>2</sup> )		At nominal voltage
Coil	Min. switching load*	1A, 6VDC		
	Rated power consumption	900mW		At 20°C
	Operate power consumption	440mW		At 20°C
Time	Operating temperature range	-40°C to 105°C		No frost
	Operate	Max. 20ms (without bounce)		At 20°C, nominal voltage
	Release	Max. 10ms (without bounce, without diode)		At 20°C, nominal voltage
Life	Mechanical	1,000,000 operations		
	Electrical	25,000 operations		Making 5A, carrying 32A, breaking 5A, 250VAC, resistive
		200,000 operations		Inrush 60A, 250VAC, interrupt 10mA, at 250VAC
		1,000 operations	30,000 operations	Making 32A, breaking 32A, 250VAC, resistive
Insulation	Insulation resistance	Min. 1,000 MΩ		500 VDC
	Dielectric withstanding voltage	Open contacts	1,000VAC (50/60Hz), 1 minute	
		Coil-contact	5,000VAC (50/60Hz), 1 minute	
Others	Vibration resistance	Misoperation	5 to 200 Hz, 45 m/s <sup>2</sup> constant acceleration	Sense time 1ms, contact ON/OFF
		Endurance	5 to 200 Hz, 45 m/s <sup>2</sup> constant acceleration	Up/down 4 hours, left/right/front/back each 2 hours, contact ON/OFF
	Shock resistance	Misoperation	100 m/s <sup>2</sup> (11 ms)	Sense time 1ms, contact ON/OFF
		Endurance	1000 m/s <sup>2</sup> (6 ms)	Contact ON/OFF total 36 times
	Dimensions / weight		18.0 x 30.5 x 29.7 mm / Approx. 39g	

Note: Electrical characteristics mentioned above are the values at JIS standard condition (temperature 15 to 35°C, relative humidity 25 to 75%, atmospheric pressure 86k to 106kPa) unless otherwise specified.

Note: Care shall be taken on the heat generated on PC board when maximum carrying current exceed 10A.

\*: Minimum switching loads mentioned above are reference values. Please perform the confirmation test with actual load before production since reference values may vary according to switching frequencies, environmental conditions and expected reliability levels.

## ■ COIL DATA

Coil Code	Rated Coil Voltage (VDC)	Coil Resistance $\pm 10\%$ ( $\Omega$ )	Must Operate Voltage* (VDC)	Must Release Voltage* (VDC)	Nominal Power (mW)
005	5	28	3.5	0.25	Approx. 900
006	6	40	4.2	0.3	
012	12	160	8.4	0.6	
024	24	640	16.8	1.2	


Note: All values in the table are valid at 20°C and zero contact current unless otherwise specified.

Note: Please use at rated coil voltage. Please refer to characteristic data and set up adequate voltage in case of use at over voltage.


\*: Specified operate values are valid for pulse wave voltage.

## ■ DIMENSIONS


## ● Dimensions



## ● Schematics(BOTTOM VIEW)




Two terminals of #3 shall be connected on the board and soldered respectively to guarantee carrying current performance. Ditto for #4.




- Dimensions of the terminals do not include thickness of pre-solder.
- Dimensions do not include tolerances.

## ● PC Board Mounting Hole Layout (BOTTOM VIEW)



( ): Reference  
Unit: mm

■ **COIL DATA** (Characteristic data is not guaranteed value but measured values of samples from production line.)



## Cautions

- \* All values mentioned in this datasheet are provided under ideal conditions. Please perform the confirmation test before actual use.
- \* Reflow soldering is prohibited.
- \* Do not use relays in the atmosphere with sulfide gas, chloride gas or nitric oxide. Contact resistance may increase.
- \* Do not use silicon or silicon-containing product or materials near relays. It may cause contact failure.

## General Information

### 1. RoHS Compliance

- All relays produced by FCL Components are compliant with RoHS directive 2011/65/EU, including commission delegated directive 2015/863.

### 2. Recommended Lead Free Solder Condition

- Lead free solder plating on relay terminals is Sn-3.0Ag-0.5Cu, unless otherwise specified. This material has been verified to be compatible with PbSn assembly process.
- Recommended solder for assembly: Sn-3.0Ag-0.5Cu.

#### Flow Solder Condition

Pre-heating: Maximum 120°C with 90 sec.

Soldering: Dip within 5 sec. at  $255^{\circ}\text{C} \pm 5^{\circ}\text{C}$  solder bath

Relay must be cooled by air immediately after soldering.

#### Solder by Soldering Iron

Soldering Iron: 30 – 60W

Temperature: Maximum 340 – 360°C

Duration: Maximum 3 sec.

We highly recommend that you confirm your actual solder conditions

### 3. Moisture Sensitivity

- Moisture Sensitivity Level standard is not applicable to electromechanical relays, unless otherwise indicated.

### 4. Tin Whiskers

- Dipped SnAgCu solder is known as presenting a low risk to tin whisker development. No considerable length whisker was found by our in house test.

# To be discontinued in March, 2026

## Contact

### Japan

FCL COMPONENTS LIMITED  
Shinagawa Seaside Park Tower  
12-4, Higashi-shinagawa 4-chome,  
Tokyo 140 0002, Japan  
Tel: +81-3-3450-1682  
Email: fcl-contact@cs.fcl-components.com

### North and South America

FCL COMPONENTS AMERICA, INC.  
2055 Gateway Place Suite 480,  
San Jose, CA 95110 USA  
Tel: +1-408-745-4900  
Email: fcai.components@fcl-components.com

### Europe

FCL COMPONENTS EUROPE B.V.  
Diamantlaan 25  
2132 WV Hoofddorp, Netherlands  
Tel: +31-23-556-0910  
Email: info.fceu@cs.fcl-components.com

### Asia Pacific

FCL COMPONENTS ASIA PTE LTD.  
No. 20 Harbour Drive, #07-01B  
Singapore 117612  
Tel: +65-6375-8560  
Email: fcsl@fcl-components.com

### China

FCL COMPONENTS (SHANGHAI) CO., LTD.  
Unit 1105, Central Park - Jing An,  
No.329 Heng Feng Road, Shanghai 200070,  
China  
Tel: +86-21-3253 0998  
Email: fcsh@fcl-components.com

**Web:** [www.fcl-components.com/en/](http://www.fcl-components.com/en/)

© 2024 FCL Components Limited. All rights reserved. All trademarks or registered trademarks are the property of their respective owners.

FCL Products are intended for general use, including without limitation, in personal, household and office environments, in buildings and for ordinary use in the industry. FCL Products are not intended to be used in applications where extremely high safety is required ("High Safety Required Applications"), such as, but not limited to, applications in nuclear facilities, in aircraft automatic flight control, in air traffic control, in mass transit system control, in missile launch system, in weapon systems, in medical equipment for life support or any application involving a direct serious risk of physical injury or death.

Please do not use FCL Products without securing the sufficient safety and reliability required for the High Safety Required Applications. In addition, FCL shall not be liable against the customer and/or any third party for any claims or damages arising in connection with the use of FCL Products in the High Safety Required Applications.

FCL warrants that its Products, if properly used and services, will conform to their specification and will be free from defects in material and workmanship for twelve months from delivery.

The implied warranties of merchantability and fitness for a particular purpose and all other warranties, representations and conditions, express or implied by statute, trade usage or otherwise, except as set forth in this warranty, are excluded and shall not apply to the Products delivered.

The contents, data and information in this datasheet are provided by FCL Components Limited as a service only to its user and only for general information purposes. The use of the contents, data and information provided in this datasheet is at the users' own risk.

FCL has assembled this datasheet with care and will endeavor to keep the contents, data and information correct, accurate, comprehensive, complete and up to date.

FCL Components Limited and affiliated companies do however not accept any responsibility or liability on their behalf, nor on behalf of its employees, for any loss or damage, direct, indirect or consequential, with respect to this datasheet, its contents, data, and information and related graphics and the correctness, reliability, accuracy, comprehensiveness, usefulness, availability and completeness thereof. Nor do FCL Components Limited and affiliated companies accept on their behalf, nor on behalf of its employees, any responsibility or liability with respect to these datasheets, its contents, data, information and related graphics and the correctness, reliability, accuracy, comprehensiveness, usefulness, availability and completeness thereof. Rev. February 1, 2024.