


SERIES: MDP65 | DESCRIPTION: 65 W AC-DC POWER SUPPLY

FEATURES

- New efficient GaN power technology design
- Efficiency up to 92%
- Form factor 1 x 3 x 1.26 in
- Output power up to 65 W
- High power density 17.20 W/in³
- Operating temperature - 20°C to 70°C
- 2 x MOPP (suitable for medical BF type applications)



MODEL	Connection	Output Voltage	Output Current ³	Output Power	Ripple ²
		[VDC]	max. [A]		
MDP65-1205 MDP65-1305	PCB mountable Header	5	5	65	5
MDP65-1212 MDP65-1312	PCB mountable Header	12	5.42	65	2
MDP65-1215 MDP65-1315	PCB mountable Header	15	4.33	65	2
MDP65-1224 MDP65-1324	PCB mountable Header	24	2.71	65	1
MDP65-1248 MDP65-1348	PCB mountable Header	48	1.35	65	1
MDP65-1256 MDP65-1356	PCB mountable Header	56	1.16	65	1

Notes:

All specifications are measured at nominal input voltage, 25°C, unless otherwise specified.

² Output Voltage ripple will be greater than 10 % during burst-mode operation (at operation below 10% of rated load).

Ripple is peak to peak with 20 MHz bandwidth and 10 µF (Electrolytic capacitor) in parallel with a 0.1 µF capacitor at rated line voltage and load ranges.

³ Derating is required.

PART NUMBER KEY

MDP65 - 1X VV - YYYY

Type / Product Series

MDP65 = High Density Power 65 W Series

Connector Type

12 = PCB Mounting

13 = Header Connector

Minor Output Variations / Circuit

Any alpha, numeric or alphanumeric character or blank

Output Voltage

05 = 5 V 12 = 12 V 15 = 15 V
24 = 24 V 48 = 48 V 56 = 56 V

INPUT

Parameter	Conditions	Min	Typ	Max	Units
Input voltage	Derate linearly from 100% at 115 VAC to 80% at 90 VAC	90		264	VAC
Input frequency		47		63	Hz
Input current				1.2	A
Inrush current				75	A
Leakage current				100	μA
No load input power				0.5	W

OUTPUT ⁴

Parameter	Conditions	Min	Typ	Max	Units
Output power	At 230 VAC			65	W
Efficiency	At 230 VAC	85		92	%
Hold-up time ⁵			10		ms
Line regulation		-1		1	%
Load regulation		-1		1	%
Rise time			55		ms
No load input power				0.5	W
Transient response	Max excursion 5%; 50% step load change at 0.1 A/μs slew rate, 50% duty cycle, 50 Hz. Recovery time 5.		5		ms
Switching frequency			65		kHz
Start up delay	At 115/230 VAC, full load			1	s
Over / undershoot	Turn On / Off			10	%

Notes:

⁴ Specifications are for nominal input voltage 230 VAC, 25°C unless otherwise stated.

⁵ Not for parallel operation.

PROTECTIONS

Parameter	Conditions	Min	Typ	Max	Units
Over current protection	Hiccup mode; auto recovery	103		140	%
Over voltage protection	Hiccup mode; auto recovery	110		140	%
Short circuit protection	Hiccup mode; auto recovery				
Over temperature protection	Hiccup mode; auto recovery				

SAFETY & COMPLIANCE

Parameter	Compliant	Min	Typ	Max	Units
Approval agency	Nemko, UL				
Safety standards	IEC 60601-1, EN 60601-1 ANSI/AAMI ES 60601-1 & C-UL (equivalent to CAN/CSA-C22.2 No.60601-1)				
Safety file numbers	CB Certificate No.: NO133967 Nemko Certificate No.: P25228152 UL Certificate No.: UL-US-2589064-0, UL-CA-2565085-0				
Equipment protection class	Class II				
Isolation voltage	Input to Output (2x MOPP)		4000		VAC
MTBF	Telcordia -SR332-issue 3		800		kH

ENVIROMENTAL

Parameter	Conditions	Min	Typ	Max	Units
Operating temperature	-20°C to 0°C start-up is guaranteed with spec. deviation	-20		+70	°C
Storage temperature		-40		+85	°C
Humidity	Relative	5		95	%
Altitude	Operating, RH, non-condensing			16000	ft
	Non-operating, non-condensing			40000	ft

EMC

Parameter	Conditions	Class / Level / Criterion
Conducted emissions ⁶	EN 55011, CISPR22-B, FCC PART15-B	Class A
Radiated emissions	EN 55011	Class A
Harmonic current	EN 61000-3-2	Class A
Fluctuation & flicker	EN 61000-3-3	Compliance
ESD immunity	EN 61000-4-2	Level 4, Criteria A
Radiated field immunity	EN 61000-4-3	Level 3, Criteria A
Electrical fast transient	EN 61000-4-4	Level 3, Criteria A
Surge immunity	EN 61000-4-5	Level 3, Criteria A
Conducted immunity	EN 61000-4-6	Level 3, Criteria A
Magnetic field immunity	EN 61000-4-8	Level 4, Criteria A
Voltage dips & interruptions	EN 61000-4-11	Criteria A & B

Notes:

⁶ An external EMI/EMC filter is recommended to connect with the PSU to meet desired EMC/EMI regulations.

MECHANICAL

Parameter	Conditions	Min	Typ	Max	Units
Dimensions			25.4 x 32 x 76.2		mm
			1.00 x 1.26 x 3.00		in
Weight			60		g


CONNECTORS / PIN DESCRIPTION

Connector	Pin #	Function	Connector Manufacturer's PN
AC input connector (J1) (Header)	Pin 1	AC Line	TE Connectivity: 640445-3 Mating: 640250-3; Pins: 3-640707-1
	Pin 2	Not fitted	
	Pin 3	AC Neutral	
AC input connector (J1) (PCB mount)	Pin 1	AC Line	Greenconn: GPJA104-0301A652C1ZA or equivalent
	Pin 2	Not fitted	
	Pin 3	AC Neutral	
DC output connector (J2) (Header)	Pin 1, 2	V1 +VE	TE Connectivity: 640445-4 Mating: 640250-4; Pins: 3-640707-1
	Pin 3, 4	V1 -VE	
DC output connector (J2) (PCB mount)	Pin 1, 2	V1 +VE	Greenconn: GPJA104-04-01A050C1ZA or equivalent
	Pin 3, 4	V1 -VE	

MECHANICAL DRAWING


MDP65-12XX SERIES (PCB Mount)

Units: mm [in]

General tolerance: ± 1.0 mm [0.04 in]** Tolerance: ± 0.2 mm [0.008]


MDP65-13XX SERIES (Header)

Units: mm [in]


General tolerance: ± 1.0 mm [0.04]

DERATING CURVES


**Output Power Derating
w.r.t. Input Voltage**



**Output Power Derating
w.r.t. Temperature (5 V)**



**Output Power Derating
w.r.t. Temperature (12 to 56 V)**



Load 65 W up to 30°C; derate above 30°C @ 1.25% per °C

REVISION HISTORY

Rev.	Description	Date
1	Initial release.	Feb/12/2025
A	Safety cert. file numbers added. Official product release.	Oct/29/2025
B	EMEA phone no. updated, redundant row for 56 V part number removed.	Dec/11/2025

NUCLEAR AND MEDICAL APPLICATIONS - Products are not designed or intended for use as critical components in life support systems, equipment used in hazardous environments, or nuclear control systems.

TECHNICAL REVISIONS - The appearance of products, including safety agency certifications pictured on labels, may change depending on the date manufactured. Specifications are subject to change without notice.



Bel Fuse Inc.
300 Executive Drive, Suite 300
West Orange, NJ 07052
United States
© 2025 Bel Fuse Inc.

Asia-Pacific
+86 755 298 85888

EMEA
+353 61 531 820

North America
+1 866 513 2839
powersupport@belf.com