

NOTES:

TAPE AND REEL SPECIFICATIONS:

1. TAPE:

MAT'L - ALL CONDUCTIVE POLYSTYRENE CARRIER
ANSI/EIA-481 STANDARD
.945 [24.0] WIDE; .473 [12.00] PITCH

2. REEL:

13.0 [330.2] DIA. 1500 PIECES OF
PART NO. 3050 PER REEL.

KEYSTONE ELECTRONICS CORP.

www.keyelco.com • ASTORIA, N.Y. 11105-2017 • Tel (718) 956-8900

PART NAME

SM RETAINER ON TAPE

MATERIAL

AS NOTED

FINISH

AS NOTED

DRN BY

NT

DATE

12.30.10

APP'D

LN

SCALE

X

TOLERANCES

INCH

[MM]

DECIMAL

± .015

[± 0.38]

ANGULAR

± 1°

UNLESS OTHERWISE SPECIFIED

CODE

DWG NO.

3050TR


DATE

DESCRIPTION

REV.

C

MOUNTING PAD LAYOUT





THIS DOCUMENT IS THE PROPERTY OF
KEYSTONE ELECTRONICS CORP. AND
SHALL NOT BE REPRODUCED, DISTRIBUTED
OR USED AS A BASIS FOR MANUFACTURE
WITHOUT PRIOR WRITTEN PERMISSION
FROM KEYSTONE ELECTRONICS CORP.

ACTUAL SIZE



POLARITY STAMP AS SHOWN



KEYSTONE ELECTRONICS CORP.

www.keyelco.com • NEW HYDE PARK, NY 11040 • Tel (516) 328-7500

PART NAME

10mm SM COIN CELL CLIP

MATERIAL

.006 [0.15] TH'K PHOSPHOR BRONZE

FINISH

MATTE TIN PLATE

DRN BY

NT

DATE 9.17.10

APP'D

LN

SCALE 4X

2.29.24 NO CHANGES TO PART

C

3.31.21 POLARITY STAMP WAS CUT THRU MA'L
CHANGE AS PER ECN 21-032

B

12.27.16 CHANGE AS PER ECN 16-115

A

DATE

DESCRIPTION

REV.

TOLERANCES INCH [MM]

DECIMAL ± .010 [± 0.25]

ANGULAR ± 1°

UNLESS OTHERWISE SPECIFIED

CODE

C

DWG NO.

3050