



DATE	DESCRIPTION	REV.
2.25.10	CHANGE AS PER ECN 10-017	A
6.01.11	CHANGE AS PER ECN 11-077	B
11.05.12	CHANGE AS PER ECN 12-155	C
2.20.13	CHANGE AS PER ECN 13-019 ADD PIN NUMERATION	D
10.31.19	CHANGE AS PER ECN 19-082	E
2.25.25	CHANGE AS PER PCN 25-009. ADDED PACKAGING DETAILS.	F

Supplied Unassembled




Notes:

Materiall:

- Shell: Steel, Nickel Plate.
- Insulator: PBT, UL 94-V0 (Color Black)
- Contacts: Phosphor Bronze
- Finish:
- Contact Area: Gold Plate over Nickel Plate
- on Solder Tail: Tin Plate over Nickel Plate

Electrical Specifications

- Rated Voltage: 30V AC (rms)
- Contact Current Rating: 1.5 Amp
- Contact Resistance: 30 milliohms Max.
- Dielectric Withstanding: 100V AC
- Operating Temperature: -30°C to 85°C
- Packaging Details: 100 Pieces Per Bag.



ACTUAL SIZE

THIS DOCUMENT IS THE PROPERTY OF KEYSTONE ELECTRONICS CORP. AND SHALL NOT BE REPRODUCED, DISTRIBUTED OR USED AS A BASIS FOR MANUFACTURE WITHOUT PRIOR WRITTEN PERMISSION FROM KEYSTONE ELECTRONICS CORP.

www.keyleco.com • NEW HYDE PARK, NY 11040 • Tel (516) 328-7500				
PART NAME				
MICRO USB PLUG				
MATERIAL				
AS NOTED				
FINISH		DRN BY		
AS NOTED		NT		
		DATE		
		10.31.19		
		SCALE		
		2.5X		
TOLERANCES		INCH		
DECIMAL		± .010 [± 0.25]		
ANGULAR		± 1°		
UNLESS OTHERWISE SPECIFIED		CODE		
		C		
		DWG. NO.		
		941		

941