

MALLORY Mallory Sonalet Products, Inc.

Part #: **JTC120-RG-CDL**

Sales Outline Drawing

Revisio

A

Specifications:


| | | | | |
|------------------------|----------------------|--|--|--|
| Stack Number: | 1 | 2 | | |
| LED Color: | RED | GREEN | | |
| LED Operation: | Continuous | Continuous | | |
| Connection Wires: | Red and Brown | Green and Brown | | |
| LED Current Draw: | <210 mA | <190 mA | | |
| Rated Voltage: | | 120 VAC | | |
| Operating Voltage: | | 90-120 VAC | | |
| Sound Level Category: | Loud | Loud | Loud | Loud |
| Mode of Operation: | Continuous | Medium Pulse (5PPS) | Double Pulse (0.5PPS) | Continuous for 5 sec then 0.1s beep until reset |
| Connection: | Black and Gray Wires | Black and Gray Wires; Orange wire connected to Green/Yellow wire | Black and Gray Wires; Purple wire connected to Green/Yellow wire | Black and Gray wires; Orange and Purple wires connected to Green/Yellow wire |
| Sound Current Draw: | 40mA Max. | 40mA Max. | 40mA Max. | 40mA Max. |
| Loudness @ 1m: | | 80-85 dB(A) Typ. | | |
| Frequency: | | 2000 ± 500 Hz | | |
| Total Max Current: | | <440mA with all LED's and sound unit working | | |
| Operating Temperature: | | -25° ~ +60°C | | |
| Lens Color: | | Transparent - matching LED stack color | | |
| Material: | | Lexan CFR7431 | | |
| Mounting Method: | | Direct Mount using 1/2" NPT Stainless Steel Pipe and Nut | | |
| Weight Typical (g): | | 320 | | |
| NEMA 12: | | Approved | | |
| Options: | | Please contact factory. | | |

Dimensions: Inches (mm)

cUL Recognized

ROHS Compliant

PATENT NUMBER(S) 10309594 D898600



LED OPERATION: |CONNECT STACK COLOR WIRE TO POWER AND BROWN WIRE TO POWER.

SOUND OPERATION: |CONNECT GRAY AND BLACK WIRES TO POWER FOR CONTINUOUS SOUND.

FOR MEDIUM PULSE, CONNECT GRAY & BLACK TO POWER AND ORANGE WIRE TO GREEN/YELLOW WIRE.

FOR DOUBLE PULSE, CONNECT GRAY & BLACK TO POWER AND PURPLE WIRE TO GREEN/YELLOW WIRE.

FOR CONT/BEEP, CONNECT GRAY & BLACK TO POWER AND ORANGE & PURPLE TO GREEN/YELLOW WIRE.