

MALLORY Mallory Sonalet Products, Inc.

Part #: **JTC120-R-CDL**

Sales Outline Drawing

Revisio

A


Specifications:

Stack Number:	1			
LED Color:	RED			
LED Operation:	Continuous			
Connection Wires:	Red and Brown			
LED Current Draw:	<210 mA			
Rated Voltage:	120 VAC			
Operating Voltage:	90-120 VAC			
Sound Level Category:	Loud	Loud	Loud	Loud
Mode of Operation:	Continuous	Medium Pulse (5PPS)	Double Pulse (0.5PPS)	Continuous for 5 sec then 0.1s beep until reset
Connection:	Black and Gray Wires	Black and Gray Wires; Orange wire connected to Green/Yellow wire	Black and Gray Wires; Purple wire connected to Green/Yellow wire	Black and Gray wires; Orange and Purple wires connected to Green/Yellow wire
Sound Current Draw:	40mA Max.	40mA Max.	40mA Max.	40mA Max.
Loudness @ 1m:		80-85 dB(A) Typ.		
Frequency:		2000 ± 500 Hz		
Total Max Current:		<250mA with all LED's and sound unit working		
Operating Temperature:		-25° ~ +60°C		
Lens Color:		Transparent - matching LED stack color		
Material:		Lexan CFR7431		
Mounting Method:		Direct Mount using 1/2" NPT Stainless Steel Pipe and Nut		
Weight Typical (g):		275		
NEMA 12:		Approved		
Options:		Please contact factory.		

Dimensions: Inches (mm)

cUL Recognized

ROHS Compliant



LED OPERATION: |CONNECT STACK COLOR WIRE TO POWER AND BROWN WIRE TO POWER.

SOUND OPERATION: |CONNECT GRAY AND BLACK WIRES TO POWER FOR CONTINUOUS SOUND.

FOR MEDIUM PULSE, CONNECT GRAY & BLACK TO POWER AND ORANGE WIRE TO GREEN/YELLOW WIRE.

FOR DOUBLE PULSE, CONNECT GRAY & BLACK TO POWER AND PURPLE WIRE TO GREEN/YELLOW WIRE.

FOR CONT/BEEP, CONNECT GRAY & BLACK TO POWER AND ORANGE & PURPLE TO GREEN/YELLOW WIRE.