

## 12V DC, 90-Amp Replacement Battery for HCRK and HCRK-INT Medical-Grade Mobile Power Retrofit Kits, TAA

MODEL NUMBER: **BP12V82**



### Description

12V DC, 90-Amp Replacement Battery for HCRK and HCRK-INT Medical-Grade Mobile Power Retrofit Kits. Sealed lead acid, maintenance-free, spill/leak proof, AGM battery, simple plug-in connection with included cable – Included in the HCRK and HCRK-INT. This is the replacement battery for the HCRK and HCRK-INT battery.

### Features

- 12V DC
- 90-Amp
- Simple plug-in connection with included cable
- Sealed, maintenance-free

### Specifications

| OVERVIEW                        |                            |
|---------------------------------|----------------------------|
| UPC Code                        | 037332134042               |
| Accessory Type                  | Battery                    |
| Accessory Class                 | Power Inverter Accessories |
| INPUT                           |                            |
| Voltage Compatibility (VDC)     | 12                         |
| PHYSICAL                        |                            |
| Shipping Dimensions (hwd / in.) | 13.30 x 14.80 x 21.20      |

### Highlights

- 12V DC, 90-Amp Replacement Battery for HCRK and HCRK-INT Medical-Grade Mobile Power Retrofit Kits
- Sealed, Maintenance-Free

### Package Includes

- BP12V82 12V DC Battery
- Connection cable



*Powering Business Worldwide*

TRIPP LITE  
SERIES

|                                     |                                  |
|-------------------------------------|----------------------------------|
| Shipping Dimensions (hwd / cm)      | 33.78 x 37.59 x 53.85            |
| Shipping Weight (lbs.)              | 73.00                            |
| Shipping Weight (kg)                | 33.11                            |
| Unit Dimensions (hwd / in.)         | 7.000 x 8.500 x 14.500           |
| Unit Dimensions (hwd / cm)          | 17.78 x 21.59 x 36.83            |
| Unit Weight (lbs.)                  | 61.5                             |
| Unit Weight (kg)                    | 27.90                            |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                                  |
| Product Compliance                  | RoHS; Trade Agreements Act (TAA) |
| <b>WARRANTY &amp; SUPPORT</b>       |                                  |
| Product Warranty Period (Worldwide) | 6-month limited warranty         |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.