



Sales Outline Drawing

Revision B

May not be suitable for all Medical and Aerospace applications.**Contact Mallory Sonaalert to discuss your application.****NO CIRCUITRY**

Resonant Frequency (Hz)	4000 \pm 500
Operating Voltage (Vp-p/max)	25
Rated Voltage (Vp-p)	5.0
Current Consumption (mA/max)	1.5 at Rated Voltage
Sound Pressure Level (dB/min)	80 at 10cm at Rated voltage
Capacitance (pF)	13,000 \pm 30% at 120Hz
Operating Temperature (°C)	-20 ~ +100
Storage Temperature (°C)	-30 ~ +110
Housing	PBT1200
Lead Pins	Tin Plated Brass
Weight (Grams)	0.67
Condition by wave soldering (°C)	245 \pm 5 / 3 \pm 0.5 sec
Condition by hand soldering (°C)	350 \pm 20 / within 5 sec
Options	For other options contact factory

PS: Vp-p = 1/2duty, square wave

RoHS Compliant

Dimensions: (units: mm)