

## 600VA 325W Standby UPS - 10 NEMA 5-15R Outlets, 120V, 50/60 Hz, USB, 5-15P Plug, Desktop/Wall Mount

MODEL NUMBER: **INTERNET600U**



Compact desktop UPS with silent alarm provides battery backup support for your home/office network system or digital signage components.

### Features

#### 600VA/325W/120V Battery Backup for PCs, Home Theater and Digital Signage

The standby INTERNET600U UPS system provides reliable battery backup and AC power protection against blackouts, brownouts, overvoltages, surges and line noise that can damage valuable electronics or destroy data. The 10-outlet 120V battery backup is ideal protection for your home office, media center or commerce components, including computers, routers, printers, NAS drives, HDTVs, Blu-ray players, game consoles, media players, DVRs and audio receivers.

#### Allows Time to Back Up Critical Files During a Blackout

Backup support allows you to work through short power failures and gives you enough time to safely save files and shut down your system in case of a prolonged blackout. Backup time varies according to load, but the INTERNET600U should keep an energy-efficient desktop computer with small LCD monitor powered as long as 16 minutes. During normal operation, incoming utility power keeps the replaceable internal battery fully charged, so backup power will always be available.

#### 10 NEMA 5-15R Outlets Protect Your Connected Components

Five 5-15R outlets provide battery backup and surge protection for your computer, monitor and other crucial components. The other five 5-15R outlets provide surge suppression only for printers, speakers and other desktop equipment regarded as non-essential during a blackout. A high >98% line mode efficiency rating reduces BTU emissions, energy consumption and, ultimately, your energy costs.

#### 316 Joules Fight Back Against Unexpected Power Surges

A 316-joule surge suppression rating protects connected components from the harmful effects of power surges. Dual network data line surge suppression jacks protect a wired peripheral from dangerous surges on a single 10/100Base-T or dial-up network connection.

#### HID-Compliant USB Port Allows for Automatic Saves and Shutdowns

This USB port connects the INTERNET600U to a computer running free downloadable PowerAlert® software to enable safe unattended file saves and system shutdown in case of a prolonged power failure.

#### Combats Electromagnetic Interference That Can Harm Equipment

Various electromagnetic and radio sources found in virtually every home and business can cause disruptive interference on the AC line. Known as EMI (electromagnetic interference) and RFI (radio frequency interference), this line noise is a common cause of performance problems and can lead to incremental hardware damage, data corruption and audio/video transmission problems. The INTERNET600U incorporates technology that filters out disruptive line noise so that it won't affect your equipment.

#### Home-Friendly Alarm and Diagnostic LED Keep You Informed 24/7

The UPS remains silent in both line and battery backup modes. The alarm sounds only to warn you of a low battery or fault condition. A front-panel green LED indicates operating mode and fault status.

### Highlights

- Protects equipment against blackouts, brownouts, overvoltages, surges and line noise
- Keeps AC power running during blackouts to allow time for file saves and safe shutdown
- 10 NEMA 5-15R outlets power and protect PC, home theater or digital signage equipment
- Home-friendly alarm remains silent in backup mode, sounding only when imperative
- High >98% efficiency with low BTU ratings saves electricity and lowers your energy costs

### Applications

- Protect your PC and other sensitive electronics against power surges, line noise, brownouts, overvoltages and blackouts
- Operate essential equipment during short-term power outages using battery backup power
- Shut down desktop PCs and other equipment without data loss during long-term power outages
- Extend runtime for DVRs, wireless routers and other low-power home network equipment

### Package Includes

- INTERNET600U 600VA 325W 120V Standby UPS with 10 Outlets
- USB cable
- Owner's manual

**Compact Housing Compatible with Easy Desktop or Wall-Mount Installation**

The space-saving ABS housing fits on a desktop, shelf or anywhere else convenient to your workstation or home theater. Keyhole mounting tabs on the rear allow easy wall-mount installation. The five-foot power cord with NEMA 5-15P plug connects to any compatible AC outlet.

## Specifications

OVERVIEW	
UPC Code	037332211033
UPS Type	Standby
INPUT	
Input Phase	Single-Phase
Rated input current (Maximum Load)	6A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
Input Circuit Breakers	7A
UPS Input Cord Length (ft.)	5
UPS Input Cord Length (m)	1.5
Recommended Electrical Service	15A 120V
Maximum Input Amps	6
OUTPUT	
Output Capacity (VA)	600
Output Capacity (kVA)	0.6
Output Capacity (Watts)	325
Output Capacity (kW)	0.325
Nominal Voltage Details	120v nominal output in battery mode
Frequency Compatibility	50 / 60 Hz
Output Voltage Regulation (Line Mode)	120V ( $\pm 20\%$ )
Output Voltage Regulation (Battery Mode)	120V ( $\pm 10\%$ )
UPS Output Receptacles (Surge Suppression Only)	5 UPS outlets, 5 surge-only outlets
Output AC Waveform (AC Mode)	Pure sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
Nominal Output Voltage(s) Supported	110V; 115V; 120V
Output Receptacles	(10) 5-15R



Powering Business Worldwide

TRIPP LITE  
SERIES

Individually Controllable Load Banks	No
<b>BATTERY</b>	
Battery Type	Valve Regulated Lead Acid (VRLA)
Runtime Full Load (min.)	1 min. (325W)
Runtime Half Load (min.)	4.5 min. (163W)
Expandable Runtime	No
DC System Voltage (VDC)	12
Battery Recharge Rate (Included Batteries)	6.5 hours (10% to 90%)
Battery Access	Battery access door
Internal UPS Replacement Battery Cartridge	IMPORTANT BATTERY REPLACEMENT INFORMATION > If your INTERNET600U has no battery access door, please contact a local electronics repair technician to source and install a matching replacement battery; If your INTERNET600U UPS does have a battery replacement door and the original battery inside has a rating of 12V 3.6AH, please order Tripp Lite &nbsp;<a class="productLink" href="//triplite.eaton.com/UPS-Replacement-Battery-Cartridge-for-Select-Tripp-Lite-AVR550U-AVRX550U-UPS-Systems-12V~RBC36H">RBC36H</a>&nbsp; replacement battery.
Battery Replacement Description	Replaceable internal batteries (see manual)
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	Switch controls power off/on status
Audible Alarm	Alarm reports low-battery, fault, overload and replace battery conditions
LED Indicators	1 Status LED reports operating mode and fault status
<b>SURGE / NOISE SUPPRESSION</b>	
UPS Dataline Suppression	1 line TEL/DSL or Ethernet
EMI / RFI AC Noise Suppression	Yes
AC Suppression Joule Rating	316
AC Suppression Response Time	Instantaneous
<b>PHYSICAL</b>	
Primary Form Factor	Desktop
Installation Form Factors Supported with Included Accessories	Tower; Ultra-compact desktop; Wallmount
Primary UPS Depth (mm)	185
Primary UPS Height (mm)	105
Primary UPS Width (mm)	110
Shipping Dimensions (hwd / in.)	7.36 x 5.67 x 10.86
Shipping Dimensions (hwd / cm)	18.69 x 14.40 x 27.58
Shipping Weight (lbs.)	4.40
Shipping Weight (kg)	2.00



Powering Business Worldwide

TRIPP LITE  
SERIES

UPS Housing Material	ABS
UPS Power Module Dimensions (hwd, cm)	10.49 x 11.00 x 18.49
UPS Power Module Dimensions (hwd, in.)	4.13 x 4.33 x 7.28
UPS Power Module Weight (kg)	1.80
UPS Power Module Weight (lbs.)	3.96
Unit Weight (lbs.)	3.960
Unit Weight (kg)	1.80
Mounting Details	Wallmount installation supported using keyhole mounting tabs
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 113°F (-15° to 45°C )
Relative Humidity	0-90% non-condensing
AC Mode BTU / Hr. (Full Load)	13.1
AC Mode Efficiency Rating (100% Load)	>98%
Operating Elevation	0-10000 ft. (0-3000 m)
<b>COMMUNICATIONS</b>	
PowerAlert Software	For local monitoring via the UPS's built-in USB port, download PowerAlert software at <a href="https://tripplite.eaton.com/products/power-alert">https://tripplite.eaton.com/products/power-alert</a>
Communications Cable	USB interface cable included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network Management Card Description	Network management not supported
Communications Interface	USB (HID enabled)
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	6 milliseconds typical (10 milliseconds max)
Low Voltage Transfer to Battery Power (Setpoint)	95
High Voltage Transfer to Battery Power (Setpoint)	145
<b>FEATURES &amp; SPECIFICATIONS</b>	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Surge/noise protection
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS



Powering Business Worldwide

TRIPP LITE  
SERIES

APPLICATIONS	
UPS Applications	Computer/Peripherals; Retail/Point of Sale; Hospitality
STANDARDS & COMPLIANCE	
Product Certifications	RETIE (Colombia); CSA (Canada); NOM (Mexico); UL 1778
Product Compliance	RoHS; FCC Part 15 Class B (USA)
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	3-year limited warranty
Product Warranty Period (Latin America)	3-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	3-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.