

## Isolator Series 120V 1000W UL 60601-1 Medical-Grade Isolation Transformer with 4 Hospital-Grade Outlets, TAA

MODEL NUMBER: **IS1000HG**



### Highlights

- Complete line isolation and noise filtering
- Hospital-grade plug and receptacles
- Lowers cumulative leakage current of connected equipment to under 100 microamps
- Floating AC output prevents noise coupling
- TAA-compliant

### Package Includes

- IS1000HG Isolation Transformer
- Instruction manual with warranty information

### Description

Isolator Series UL 60601-1 Listed Medical-Grade Isolation Transformers offer line isolation and continuous noise filtering. An internal low-impedance isolation transformer component offers 100% isolation from the input AC line. Full UL 60601-1 medical-grade listing with hospital-grade plug and outlet receptacles makes Isolator medical-grade transformers ideal for protecting sensitive electronic equipment in patient-care areas. Faraday shield reduces the cumulative leakage current of the Isolator and connected equipment to levels less than 100 microamps. Removes EMI/RFI noise, utility switching transients and harmonics generated by other on-site loads. Reduces impact of utility-related surge conditions. Transformer filtering provides continuous common-mode noise rejection with no wearable parts. Reduces 6000V IEEE587 Category A & B ring wave and combination wave test surges to only 0.5V common mode. Includes four widely spaced NEMA 5-15R hospital-grade output receptacles, 10-ft. (3.05 m) power cord, hospital-grade input plug, circuit breaker overload protection, lighted power switch and rugged all-metal housing. Ships ready for placement in any industrial, medical, office or network environment. PLUG/OUTLETS: Input - NEMA 5-15P Hospital Grade; Output - 4 NEMA 5-15R Hospital Grade ELECTRICAL: 120V AC, 60 Hz, 8.3A (requires NEMA 5-15R wall receptacle).

### Features

- Offers line isolation and continuous noise filtering
- Internal low-impedance isolation transformer with Faraday shield offers 100% isolation from the input AC line
- Full UL 60601-1 medical-grade listing with hospital-grade plug and outlet receptacles for the protection of sensitive electronic equipment in patient-care areas
- Reduces cumulative leakage current of the Isolator and connected equipment to levels less than 100 microamps
- Floating AC output prevents noise coupling from noisy hospital ground circuits and meets agency requirements
- Inexpensive alternative to dedicated circuits and site electrical upgrades
- Removes EMI/RFI noise, utility switching transients, load-generated harmonics and ground loops
- Transformer filtering offers continuous common-mode noise rejection with no wearable parts
- Reduces 6000V IEEE587 Cat A & B ring wave and combination wave test surges to only 0.5V common mode
- Includes 4 widely spaced NEMA 5-15R hospital-grade output receptacles, 10-ft. (3.05 m) power cord, hospital-grade input plug, circuit breaker overload protection, lighted power switch and rugged all-metal

unit housing

- Ships ready for upright tower placement in any industrial, medical, office or network environment

## Specifications

OVERVIEW	
UPC Code	037332116215
Efficiency	96%
Let-through Voltage (Combination Wave)	L-N: 250V L-G: 250V N-G: 0.5V
Let-through Voltage (Ring Wave)	L-N: 20V L-G: 20V N-G: 0.5V
Nominal Voltage / Frequency	120V / 60Hz
VA / Watt Capacity	1000
Transformer Type	Medical Grade, Low Impedance transformer-based line isolation transformer
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Input Plug Type	NEMA 5-15P-HG
Total Harmonic Distortion	Less than 1%
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
OUTPUT	
Nominal Output Voltage(s) Supported	120V
Output Receptacles	(4) 5-15R-HG
Output Amp Capacity	8.8
ISOLATION	
Leakage Current	Less than 100 microamps
SURGE / NOISE SUPPRESSION	
Noise Suppression Rating	35-65 dB
PHYSICAL	
Cooling Method	Convection
Form Factors Supported	Tower
Shipping Dimensions (hwd / in.)	10.40 x 10.70 x 12.80
Shipping Dimensions (hwd / cm)	26.42 x 27.18 x 32.51



*Powering Business Worldwide*

TRIPP LITE  
SERIES

Shipping Weight (lbs.)	37.70
Shipping Weight (kg)	17.10
Unit Dimensions (hwd / in.)	7.250 x 7.250 x 10.500
Unit Dimensions (hwd / cm)	19.66 x 18.42 x 26.67
<b>FEATURES &amp; SPECIFICATIONS</b>	
Over Current Protection	1 x Thermal, 2 pole, 10 amp
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	UL 60601-1
Product Compliance	RoHS; Trade Agreements Act (TAA)
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.