

KVM Extender with VGA and USB Connections, Up to 330 ft.

MODEL NUMBER: **B013-330-USB**



Extends keyboard, mouse and monitor up to 330 ft. from your computer via Cat5 UTP cabling.

Features

Extends Console up to 330 ft. from Computer, KVM or Server

This KVM extender lets you control a computer, server or KVM switch from up to 330 feet (100 meters) away. Just connect the included transmitter and receiver with a Cat5 UTP cable (sold separately). Console ports on both the transmitter and receiver allow local or remote control of the connected device. Plus, the receiver doubles as a two-port KVM, allowing the connection of a local computer.

Recommended for Small to Medium-Sized Businesses (SMBs)

Being able to extend VGA video and USB signals up to 330 feet is ideal in commercial office spaces where the computers are not close to your workstation, as well as SMB applications needed KVM switches without requiring an IP network for long-distance control. The B013-330-USB supports VGA video resolutions up to 1920 x 1200.

Pure Hardware Solution Is Easy to Install and Operate

The B013-330-USB supports all major operating systems, including Windows and macOS. All necessary cables are included as a convenient off-the-shelf package, making the KVM Extender simple to maintain. As a pure hardware solution, you don't have to worry about software/network conflicts. This KVM Extender is compatible with any computers using VGA and USB connections.

Specifications

OVERVIEW	
UPC Code	037332288875
Console	No
Accessory Type	Extender Kit
Technology	USB 2.0 (High Speed)
Accessory Class	KVM Switch Accessories

Highlights

- Extends VGA video + USB keyboard/mouse from your computer up to 330 ft.
- Console ports on each end allow for local or remote control of connected computer
- Receiver doubles as 2-port KVM, allowing for connection of a local computer
- Supports VGA video resolutions up to 1920 x 1200, including 1080p
- Easy to install and operate with all necessary cables included

Package Includes

- Transmitter
- Receiver
- (2) USB KVM combo cables
- USB-A to USB-B upgrade cable (M/M)
- (2) External power supplies (Input: 100–240V, 50/60 Hz, 0.6A; Output: 5V 2A) with 6 ft. (1.8 m) cord
- (8) International plug adapters
- Quick Start Guide

VIDEO	
Number of Monitors Supported	1
Video Ports	HD15 (FEMALE)
Max Supported Video Resolution	1920 x 1200 @60Hz
Max. Distance (Between any 2 Units)	330FT (100M)
Max Number of Ports (Entire Chain)	2
Transmitter Video Input	VGA
HDR Support	No
3D Video Supported	No
EDID Support	Yes
INPUT	
AC Power Adapter Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/16 Schuko; NEMA 1-15P North America
AC Power Adapter Input Specs (V / Hz / A)	100-240V / 50/60Hz / 0.6A
AC Power Adapter Output Specs (V / A)	DC 5V/2A
AC Power Adapter Cord Length (ft.)	6
AC Power Adapter Cord Length (m)	1.8
Nominal Input Voltage(s) Supported	100V AC; 240V AC
Maximum Input Amps	1
Voltage Compatibility (VAC)	100-240
Input Frequency	50/60 Hz
Redundancy - Dual Power Inputs	No
Bus Powered	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
POWER	
Power Source Type	AC Adapter with detachable power cord
AC Plug Type	AS/NZS 3112; BS1363; CEE 7/16 Schuko; NEMA 1-15P
Power Over Cable (PoC) Support	Yes
AC Adapter	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/16 Schuko; NEMA 1-15P North America
DC Barrel Plug	OD: 3.5 x 1.35 x 7.5mm, Positive Pin, Negative Sleeve
CONNECTIONS	
Number of Ports	2



Powering Business Worldwide

TRIPP LITE
SERIES

Computer/Server Ports	(2) HD15 (FEMALE)
Firmware Upgrade Port	(x2) USB-B
PC/Server Connections	USB; VGA
Side A - Connector 1	(2) HD15 (FEMALE); RJ45 (MALE); (2) USB A (FEMALE); (1) USB B (FEMALE)
Side B - Connector 1	(2) HD15 (FEMALE); RJ45 (MALE); (2) USB A (FEMALE); (1) USB B (FEMALE)
Included Cable (Side A) - Connector 1	(1) USB A (FEMALE)
Included Cable (Side B) - Connector 2	(1) USB B (FEMALE)
Included KVM Cable (Equipment Side) - Connector 1	(1) HD15 (FEMALE)
Included KVM Cable (Equipment Side) - Connector 2	(1) HD15 (FEMALE), (1) USB A (FEMALE), (1) PS/2
Computer Keyboard and Mouse Interface	USB
Computer Monitor Interface	HD15; VGA
Console Keyboard and Mouse Interface	PS/2; USB
Console Monitor Interface	HD15; VGA
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	Receiver- 1X (Red) Power; 3X (Green) Link RX & TX; Transmitter- 1X (Red) Power; 3X (Green) Link, Video & Control
PHYSICAL	
Color	Black
Material of Construction	Metal
Rackmountable	No
Receiver Unit Dimensions (hwd / in.)	1.02 x 5.15 x 2.55
Receiver Unit Weight (lbs.)	0.639
Shipping Dimensions (hwd / in.)	7.95 x 5.47 x 6.92
Shipping Weight (lbs.)	3.21
Transmitter Unit Dimensions (hwd / in.)	1.02 x 5.15 x 2.55
Transmitter Unit Weight (lbs.)	0.639
Unit Dimensions (hwd / in.)	1.020 x 5.150 x 2.550
Unit Packaging Type	Box
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)



Powering Business Worldwide

TRIPP LITE
SERIES

Relative Humidity	0-90% non-condensing
COMMUNICATIONS	
Hotkey	YES
Port Control	Push Buttons, Hotkeys, OSD
IP Remote Access	No
Transmission Distance	330 ft.
EDID Compatible	Yes
IR Remote Extension Support	No
Consumer Electronics Control (CEC) Supported	No
Latency	Zero
USB Extension Support	Yes
FEATURES & SPECIFICATIONS	
USB Specification	USB 1.1 (up to 12 Mbps)
NIAP-Certified Secure	No
Number of Users	1
Autoscan (Y,N)	N
On-Screen Display (OSD)	Yes
Port Selection	Hotkey; OSD; Pushbutton
Driver Required	No
Recommended Category Cable	Cat5,Cat5e
REMOTE ACCESS	
Modem Port	No
STANDARDS & COMPLIANCE	
External Power Supply Certifications	CE; FCC; GS; NOM; TUV; UKCA; UL; WEEE; cUL
Product Certifications	CAN/CSA-C22.2 No. 62368-1 (Canada); EN 55032; EN 55035; IEC 62368-1; NOM (Mexico); TUVus; UL 62368-1
Product Compliance	CE (Europe); FCC Part 15 Class B (USA); REACH; RoHS; UKCA; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty



Powering Business Worldwide

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

TRIPP LITE
SERIES

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.