

12V DC, 54-Amp Replacement Battery for HCRK-54 Medical-Grade Mobile Power Retrofit Kit, TAA

MODEL NUMBER: **BP12V54**



Highlights

- 12V DC, 54-Amp Replacement Battery for HCRK-54 Medical-Grade Mobile Power Retrofit Kit
- Sealed, Maintenance-Free

Package Includes

- BP12V54 12V DC Battery
- Connection cable

Description

12V DC, 54-Amp Replacement Battery for HCRK-54 Medical-Grade Mobile Power Retrofit Kit. Sealed lead acid, maintenance-free, spill/leak proof, AGM battery, simple plug-in connection with included cable – Included in the HCRK-54. This is the replacement battery for the HCRK-54 battery.

Features

- 12V DC
- 54-Amp
- Simple plug-in connection with included cable
- Sealed, maintenance-free

Specifications

OVERVIEW	
UPC Code	037332142450
Accessory Type	Battery
Accessory Class	Power Inverter Accessories
INPUT	
Voltage Compatibility (VDC)	12
PHYSICAL	
Shipping Dimensions (hwd / in.)	9.70 x 12.50 x 11.70
Shipping Dimensions (hwd / cm)	24.64 x 31.75 x 29.72
Shipping Weight (lbs.)	47.44



Powering Business Worldwide

TRIPP LITE
SERIES

Shipping Weight (kg)	21.52
Unit Dimensions (hwd / in.)	6.500 x 8.750 x 10.000
Unit Dimensions (hwd / cm)	16.51 x 22.23 x 25.4
Unit Weight (lbs.)	44
Unit Weight (kg)	19.96
STANDARDS & COMPLIANCE	
Product Compliance	RoHS; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	6-month limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.