

Heavy-Duty Fixed Security TV Wall Mount for 45-70" TVs & Monitors - Flat Screen, Portrait Mode

MODEL NUMBER: DWFPSC4570M



Security wall mount with combination lock mounts your 45–70 in. flat-panel television or monitor to the wall in portrait mode.

Features

Portrait Wall Mount Hangs Your Flat-Panel TV or Monitor on the Wall Recommended for classrooms, conference rooms, hotels, bars, restaurants or anywhere else you may want to show off a television or monitor in portrait mode, this heavy-duty anti-theft TV wall mount is hidden out of sight behind the display for a sleek, professional appearance. It fits most flat-panel displays from 45 to 70 inches and up to 110 lbs (49.9 kgs). Mounting hardware is included.

Durable All-Metal Construction Provides Convenient Cable Access The fixed TV wall mount is constructed from heavy-duty steel with a powder-coated black finish that resists scratches. Rear openings with smooth edges enable easy access to cables. A built-in bubble level helps ensure your display is evenly mounted. The DWFPSC4570M is designed for portrait viewing, making it ideal for menus, schedules and announcements.

Designed to Keep Your Display Safe and Secure This security wall mount was conceived with your television or monitor's safety in mind, especially if the display is located in a public area with unguarded traffic, such as a library, classroom or hotel lobby. It comes with a solid steel security bar that slides through the mounting brackets and is secured into place with an included four-position combination lock.

Complies with VESA Standards VESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing industry-wide standards for products like flat-panel TVs and monitors. To comply with these standards, most manufacturers use a series of universal mounting hole patterns, measured in millimeters, on the backs of the products. Measure the vertical and horizontal distances between the holes on the back of your display or refer to your display's owner's manual to find its VESA pattern. This monitor wall mount conforms to VESA-compliant displays with any of the following standard mounting hole patterns: 200 x 200, 300 x 300, 400 x 200, 400 x 400 and 600 x 400.

Highlights

- Accepts most popular flat-screen displays from 45 to 70 in. up to 110 lbs (49.9 kgs)
- Displays in portrait mode for easy reading of menus, schedules, announcements, etc.
- Solid steel security bar and included combo lock deters tampering and theft
- Open architecture and built-in level enable easy cable access and accurate leveling
- Complies with VESA standards to ensure compatibility with your display

Applications

- Avoid theft by mounting a flat-screen monitor or TV to this secure mounting bracket with a solid steel security bar and lock
- Ideal for conference rooms, restaurants, hotels, classrooms, lobbies or anywhere else digital signage is needed

Package Includes

- (2) Vertical wall plates
- (2) Horizontal wall plates
- (2) Adapter brackets
- Security bar
- (8) M5 x 8 screws
- (4) M5 x 14 screws
- (4) M6 x 14 screws
- (4) M6 x 30 screws
- (4) M8 x 20 screws
- (4) M8 x 30 screws
- (4) Washers
- (8) Small spacers
- (8) Large spacers
- (6) Anchor bolts
- (6) Concrete anchors
- (6) D6 washers
- Bubble level
- Combination lock
- Owner's manual

Specifications

OVERVIEW	
UPC Code	037332238535
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Material of Construction	Steel
VESA Pattern (mm)	200x200; 200x400; 300x300; 300x400; 400x300; 400x400; 400x600
Motion	Fixed
Mounting Location	Wall
Distance from Wall (in.)	2.3
Distance from Wall (cm)	6
Distance from Wall (mm)	58
Minimum Screen Size (in.)	45
Minimum Screen Size (cm)	114.3
Maximum Screen Size (in.)	70
Maximum Screen Size (cm)	177.8
Maximum Weight Capacity (lbs.)	110
Maximum Weight Capacity (kg)	50
Number of Displays	1
Shipping Dimensions (hwd / in.)	3.80 x 5.80 x 27.60
Shipping Dimensions (hwd / cm)	9.65 x 14.73 x 70.10
Shipping Weight (lbs.)	11.30
Shipping Weight (kg)	5.13
Unit Dimensions (hwd / in.)	20.500 x 26.800 x 2.300
Unit Weight (lbs.)	9.9
Unit Weight (kg)	4.49
Assembly Required	Yes
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Cord Management	No
Tools Necessary	Yes
Security Lock	Yes



Powering Business Worldwide

TRIPP LITE
SERIES

STANDARDS & COMPLIANCE

Product Compliance	RoHS; RoHS3; REACH
--------------------	--------------------

WARRANTY & SUPPORT

Product Warranty Period (Worldwide)	5-year limited warranty
-------------------------------------	-------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.