

Single-Phase Metered Input Rack PDU G4, 100-240V, 24 Outlets, 16A, 3.8kW, C20/L6-20 Input, 10 ft. Cord, 0U Vertical

MODEL NUMBER: **EVMIL620A**



Metered input PDU with enhanced cybersecurity is ideal for data center managers seeking to streamline PDU procurement and management.

Features

Single-Phase Metered Input PDU Ideal for Data Center Managers with Large-Scale Distributed IT

The EVMIL620A Rack PDU G4 is ideal for streamlining PDU procurement and deployment within a rack in an enterprise data center, colocation data center or distributed IT infrastructure. Equipped to meet even the most diverse data center rack power needs, the EVMIL620A delivers versatile, enterprise-quality power distribution.

Market-Leading Cybersecurity Ensures Your Data Is Kept Safe

Chain-of-trust encryption, a user-configurable firewall and secure firmware boot capability prevent the EVMIL620A PDU from being a cyberattack vulnerability point on a network. An embedded, hot-swappable Gigabit Network Module (GNM) offers enhanced management and cybersecurity, including zero-trust architecture and zero-touch provisioning. The EVMIL620A is compatible with select Eaton Brightlayer Data Centers suite software solutions that enable extensive automation to shorten response times to power issues and ensure timely updates for stronger cybersecurity.

Metering to Optimize Utilization and Prevent Down Time

High accuracy metering for voltage, current, power and energy. Use this data for capacity planning, alarming or reporting energy consumption. Set alarm thresholds to prevent overload and prevent costly down time. Power data is available on the local LCD display or over the network using Web, SNMP, CLI or RestAPI.

24 Outlets Give You Plenty of Power Options

The EVMIL620A features 12 C13 outlets, which accept C14 connectors, and 12 high-retention C39 combo outlets, which accept both C14 and C20 connectors, adding flexibility to deployments and reducing the quantity of PDUs you will need to purchase and install. The outlets are evenly distributed into color-coded load banks, each with its own circuit breaker, to improve load balancing and organize connections in a crowded rack.

Convenient Box-to-Rack Installation

This EVMIL620A rack PDU (rPDU) features toolless mounting buttons that allow front- or side-facing rack installation, depending on your rack's layout and your power needs. The 10-foot power cord has an attached C20 input and an L6-20 input adapter is included for versatility. Low-profile circuit breakers are flush with the lightweight aluminum chassis, and the narrow two-inch width saves space within the rack for

Highlights

- Embedded Gigabit Network Module offers market-leading cybersecurity
- 24 outlets include 12 C13 and 12 flexible C39, which accepts C14 and C20 plugs
- Compatible with Eaton Tripp Lite P-Lock Power Cords to simplify deployment and enhance reliability
- Color-coded load banks with individual breakers keep connections organized
- Toolless mounting buttons allow 0U vertical installation in your rack

Package Includes

EVMIL620A Single-Phase Metered Input Rack PDU G4



Powering Business Worldwide

revenue-generating equipment. You can cascade up to 40 EVMIL620A models with each model maintaining its own individual IP address from a single network connection point.

Specifications

| OVERVIEW | |
|--------------------------------------|---|
| UPC Code | 786689801410 |
| PDU Type | Metered |
| INPUT | |
| Input Phase | Single-Phase |
| PDU Input Voltage | 100-240V |
| Nominal Input Voltage(s) Supported | 100V AC; 120V AC; 200V AC; 208V AC; 230V AC; 240V AC |
| Recommended Electrical Service | Single-phase 200-240V service |
| Maximum Input Amps | 20 |
| Input Connection Type | IEC-320 C20; NEMA L6-20P |
| PDU Plug Type | IEC-320 C20; NEMA L6-20P |
| Voltage Compatibility (VAC) | 1-Phase; 200-240 |
| Input Cord Length (ft.) | 10 |
| Input Cord Length (m) | 3.05 |
| OUTPUT | |
| Output Capacity (kVA) | 3.8 |
| Output Capacity (Watts) | 3800 |
| Output Capacity (kW) | 3.8 |
| Output Capacity Details | 3.8kW (120-240V) total capacity; 16A max per output phase |
| Frequency Compatibility | 50 / 60 Hz |
| Output Receptacle Details | (10) C13; (10) C39 combo outlets compatible with P-Lock Power Cords |
| Nominal Output Voltage(s) Supported | 100V; 110V; 115V; 120V; 200V; 208V; 220V; 230V; 240V |
| Output Receptacles | (12) C13; (12) C39 |
| CONNECTIONS | |
| Ethernet Interface | Yes |
| Serial Interface | Yes |
| Daisy-chainable / Cascadable | Yes |
| Daisy-chainable / Cascadable Details | Cascade up to 40 PDUs |



Powering Business Worldwide

| USER INTERFACE, ALERTS & CONTROLS | |
|--------------------------------------|---|
| Front Panel LCD Display | LCD pixel display with outlet-level readings and automatic shut-off to save energy. Set IP address, rotate display, control outlets, view alarms and read current, voltage, power and energy. |
| Current Measurement Accuracy (Amps) | +/-1% |
| Voltage Measurement Accuracy (Volts) | +/-1% |
| Power Measurement Accuracy (Watts) | +/-1% |
| SURGE / NOISE SUPPRESSION | |
| Automatic Shut-Off | No |
| PHYSICAL | |
| Material of Construction | Aluminum |
| Rack Height | 0U |
| Form Factors Supported | Vertical |
| Housing Color | Black |
| PDU Form Factor | Vertical (0U) |
| Shipping Dimensions (hwd / in.) | 46.30 x 7.72 x 5.40 |
| Shipping Dimensions (hwd / cm) | 117.60 x 19.61 x 13.72 |
| Shipping Weight (lbs.) | 9.70 |
| Shipping Weight (kg) | 4.40 |
| Unit Dimensions (hwd / in.) | 39.400 x 2.000 x 2.080 |
| Unit Dimensions (hwd / cm) | 100.07 x 5.08 x 5.28 |
| Unit Weight (lbs.) | 4.9 |
| Unit Weight (kg) | 2.22 |
| Mounting Details | Factory-installed shoulder-style aluminum mounting buttons. 61.25" center-to-center Alternative flush-style mounting buttons also included with PDU. |
| ENVIRONMENTAL | |
| Operating Temperature Range | 32° to 140°F (0° to 60°C) |
| Storage Temperature Range | -13° to 149°F (-25° to 65°C) |
| Relative Humidity | 5% to 95% non-condensing |
| Operating Elevation | 0-10000 ft. (0-3000 m) |
| Storage Elevation (ft.) | 0-50000 ft. (0-15240 m) |
| COMMUNICATIONS | |
| Network Monitoring Port | Serial/Ethernet ports for environmental monitoring and daisy-chain connections |
| SNMP Compatibility | Yes |



Powering Business Worldwide

| | |
|---|--|
| Network Compatibility | 10 Mbps; 100 Mbps (Fast Ethernet); 1 Gbps (Gigabit); 1000 Mbps |
| Network Speed Details | 10 Mbps; 100 Mbps (Fast Ethernet); 1 Gbps (Gigabit); 1000 Mbps |
| Network Management Card Description | Eaton Gigabit Network Module G4 |
| FEATURES & SPECIFICATIONS | |
| High Availability PDU Features | Advanced cybersecurity |
| STANDARDS & COMPLIANCE | |
| Product Certifications | ICES (Canada); UL 62368-1; cTUVus |
| Product Compliance | FCC Part 15 Class A (USA); RoHS |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | 3-year limited warranty |
| Product Warranty Period (U.S. & Canada) | 3-year limited warranty |

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.