

## Monitor Riser for Desk, 15 x 9 in. - Height Adjustable, Storage Drawer, Metal, Black

MODEL NUMBER: **MR159D**



Computer monitor stand lifts your monitor by increments up to a maximum of 5.5 in. above your desktop surface to help ease eye and neck strain.

### Features

#### Maintenance-Free Computer Monitor Stand Raises Your Screen for Comfortable Viewing

This desk monitor riser allows you some flexibility in placing your monitor for maximum comfort. The legs adjust to heights of 3.9 inches (99 millimeters), 4.7 inches (119 millimeters) and 5.5 inches (140 millimeters), so you can view your monitor while lessening strain on your eyes and neck. Lifting your monitor also frees up valuable space on your desk, table or counter at home, school or office.

#### Rugged Metal Construction Supports Up to 44 Pounds

The rectangular metal platform measures 14.6 x 9.3 inches (370 x 235 millimeters) and supports monitors, laptops, printers, small televisions and other devices weighing up to 44 pounds (20 kilograms). The platform is ventilated to allow proper airflow and help keep your monitor cool. A built-in storage drawer keeps necessary office supplies at your fingertips.

#### Sets Up Quickly and Easily in Just a Few Seconds

This monitor stand riser assembles in moments with no tools or permanent mounting required. Rubber feet attached to the legs secure the riser in place on a smooth surface.

## Specifications

OVERVIEW	
UPC Code	037332283887
Device Compatibility	Monitor/HDTV
PHYSICAL	
Color	Black
Material of Construction	Metal
Mounting Location	Desktop

### Highlights

- Computer monitor riser adjusts to heights of 3.9 in., 4.7 in. and 5.5 in.
- Eases eye and neck strain while clearing valuable space on your desk or table
- Rectangular metal platform supports monitor or other devices up to 44 lb.
- Ventilated surface allows proper airflow to help keep your monitor cool
- Riser and storage drawer assemble in just a few seconds with no tools required

### Package Includes

- MR159D Monitor Riser with storage drawer
- (4) Legs with rubber feet
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

Maximum Weight Capacity (lbs.)	44
Maximum Weight Capacity (kg)	20
Number of Displays	1
Shipping Dimensions (hwd / in.)	16.20 x 9.60 x 1.80
Shipping Dimensions (hwd / cm)	41.15 x 24.38 x 4.57
Shipping Weight (lbs.)	2.40
Shipping Weight (kg)	1.09
Unit Dimensions (hwd / in.)	5.510 x 14.570 x 9.250
Unit Dimensions (hwd / cm)	11 x 47 x 28
Unit Weight (lbs.)	2.11
Unit Weight (kg)	0.96
Assembly Required	Yes
<b>FEATURES &amp; SPECIFICATIONS</b>	
Antimicrobial	No
Cord Management	No
Tools Necessary	No
Security Lock	No
Height Adjustable	Yes
Outdoor Use	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS3
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.