

PDU Power Cord, C13 to P-Lock C14 - North America and Europe Rated, 10A, 250V, 18AWG, 6 ft. (1.83m), Black

MODEL NUMBER: P004-E06



Locking C13/C14 power cord provides a secure connection between a server, switch or other critical data center device and P-Lock compatible PDU.

Features

P-Lock C14-to-C13 Power Cable Connects Computers, Printers, Servers and Other Equipment This IEC-320-C14 to IEC-320-C13 cable is designed for small data center, office workstation and other lower-amp applications. The C14 male to C13 female cord can be used to power a computer, server or monitor; attach a server or drive to a UPS system or PDU; or extend an existing connection up to 6-ft. (1.83 m). **P-Lock Connector Reduces Risk of Costly Downtime** Plug the P004-E06's P-Lock C14 connector into a compatible PDU, such as Eaton's line of PDUs with P-Lock C13 and C39 outlets, for a secure connection that reduces the risk of accidental disconnections in a crowded rack enclosure or cabinet. Locking tabs on either side of the connector click into place for a secure connection.

Specifications

OVERVIEW	
UPC Code	037332292957
Product Type	PDU Power Cord
Device Compatibility	Computer; Monitor/HDTV; Printer; Server; UPS; PDU
Country/Region	Global
INPUT	
Maximum Input Amps	10
Voltage Compatibility (VAC)	100-250
CONNECTIONS	

Highlights

- Provides power to a computer, server or other device frequently connected to a PDU in a data center rack or cabinet
- P-Lock C14 connector forms a secure connection with a compatible PDU, including Eaton PDUs with C39 outlets
- Locking tabs prevents accidental disconnects which cause costly downtime in a crowded rack enclosure
- Compliant with UL and VDE standards for international application use

Package Includes

- P004-E06 P-Lock C14 Male to C13 Female Power Cable, 6-ft. (1.83 m), Black



Powering Business Worldwide

TRIPP LITE
SERIES

Side A - Connector 1	IEC-320-C14
Side B - Connector 1	IEC-320-C13
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	H05VV-F; SJT; VW-1
Power Cord Jacket Type	SJT + H05VV-F
Cable Outer Diameter (OD)	7.0mm
Number of Conductors	3
Wire Gauge (AWG)	18
Wire Gauge (OD - mm ²)	1.0
Cable Length (ft.)	6
Cable Length (m)	1.83
Shipping Dimensions (hwd / in.)	10.00 x 7.99 x 0.50
Shipping Weight (lbs.)	0.82
Shipping Weight (kg)	0.37
Unit Dimensions (hwd / in.)	10.000 x 7.990 x 0.500
ENVIRONMENTAL	
Operating Temperature Range	23° to 158°F (-5° to 70°C)
Storage Temperature Range	14° to 140°F (-10° to 60°C)
Relative Humidity	35 TO 85% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	Yes
Locking Plug	Yes
Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	CE (Europe); REACH; RoHS3; UKCA; WEEE
WARRANTY & SUPPORT	



Powering Business Worldwide

TRIPP LITE
SERIES

Product Warranty Period (Worldwide)	Lifetime limited warranty
-------------------------------------	---------------------------

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.