

## Duplex Multimode 62.5/125 Fiber Patch Cable (SC/ST), 15M (50 ft.)

MODEL NUMBER: **N304-15M**



### Highlights

- Premium PVC 62.5/125 $\mu$ m multimode patch cables
- Attenuation loss meets or exceeds the latest industry standards

### System Requirements

- Any fiber optic hardware or NIC card requiring multimode duplex cable with SC/ST connectors

### Package Includes

- 15-meter ( 50ft ) duplex MMF cable ST/SC 62.5/125 fiber

### Description

This multimode duplex fiber optic SC/ST Ethernet cable is manufactured from 62.5/125 zipcord fiber. The cable has ST to SC connectors, a PVC jacket and is FDDI and OFNR rated. Duplex multimode fiber is most commonly used in LAN applications.

### Features

- Manufactured from 62.5/125 duplex (zipcord) fiber
- PVC jacket
- Length: 15-meters ( 50ft ) Connectors: 2 ST to 2 SC connectors
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze
- Fiber made from glass (not a polymer)
- Color coded shrouds identify transmit and receive
- Fiber optic distributed data interface (FDDI) rated
- OFNR (riser rated)

## Specifications

OVERVIEW	
UPC Code	037332122568
Technology	Multimode
Optical Mode	OM1
CONNECTIONS	
Side A - Connector 1	SC DUPLEX (MALE)



Powering Business Worldwide

TRIPP LITE  
SERIES

Side B - Connector 1	ST DUPLEX (MALE)
Endface Polish	PC
<b>PHYSICAL</b>	
Cable Jacket Color	Orange
Connector Color	White; Black
Cable Jacket Material	LSZH
Cable Jacket Rating	OFNR
Clad Diameter (microns)	125
Core Diameter (microns)	62.5
Number of Fibers	2
Cable Length (ft.)	49.2
Cable Length (m)	15.00
Cable Length (in.)	590.6
Minimum Bend Radius	20 mm (Dynamic); 10 mm (Static)
Shipping Dimensions (hwd / in.)	10.00 x 8.00 x 0.75
Shipping Dimensions (hwd / cm)	25.40 x 20.32 x 1.90
Shipping Weight (lbs.)	0.41
Shipping Weight (kg)	0.19
Fiber Cable Length	15M (49.2 ft)
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	-4° to 140°F (-20° to 60°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	5% to 85% RH, Non-Condensing
Storage Humidity Range	35% to 65% RH, Non-Condensing
<b>COMMUNICATIONS</b>	
Network Compatibility	1 Gbps (Gigabit); 10 Gbps
Attenuation @ 850NM	3.0 dB/km
Insertion Loss	0.20 dB
<b>FEATURES &amp; SPECIFICATIONS</b>	
Push/Pull Tabs	No
Breakout	No
Trunk	No
<b>STANDARDS &amp; COMPLIANCE</b>	



*Powering Business Worldwide*

TRIPP LITE  
SERIES

Product Compliance	RoHS; REACH
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard

Cleveland, OH 44122

United States

<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.