

Hospital-Grade Power Cord, NEMA 5-15P to C13 - Green Dot, 13A, 125V, 16 AWG, 15 ft. (4.57 m), Clear Plugs

MODEL NUMBER: **P006-015-HG13CL**



Connects your PC, mobile cart or other hospital equipment with a C14 inlet to a grounded hospital-grade AC outlet.

Features

Hospital-Grade Power Cable is a Safe Solution for Medical Facilities This hospital-grade IEC power cord is designed for computers, mobile carts, printers, scanners, monitors and other compatible hospital equipment with a three-pin C14 inlet. It features a C13 end for connecting to a device and a NEMA 5-15P-HG plug for connecting to a hospital-grade AC power source located outside patient-care vicinities. The 15-ft. (4.57 m) length allows you great flexibility in placing equipment with respect to the power outlet.

Designed and Tested to Strict Hospital-Grade Standards Both fully molded ends are clear, so you can inspect their internal connections at a glance. This hospital-grade power cord is tested to ANSI/UL 62 and 817 standards, as well as CAN/CSA C22.2 no. 21 and 49 standards, ensuring it's a dependable power solution for hospital environments.

Specifications

| OVERVIEW | |
|-----------------------------|--|
| UPC Code | 037332193308 |
| Device Compatibility | Mobile Cart; Computer; Printer; Monitor/HDTV; Server; UPS; PDU |
| Country/Region | North America |
| INPUT | CONNECTIONS |
| Maximum Input Amps | 13 |
| Voltage Compatibility (VAC) | 125 |
| CONNECTIONS | |

Highlights

- Fully molded clear plugs allow visual inspection of internal construction to ensure safety
- Recommended for connecting devices to power outlets outside patient-care vicinities
- 15-ft. (4.57 m) length allows great flexibility in placing devices in relationship to AC outlet
- Hospital-grade power cord replaces or upgrades power cord provided by manufacturer
- NEMA 5-15P-HG plug connects to AC power; C13 plug connects to device's C14 inlet

Applications

- Connect devices like PCs, mobile carts, monitors and printers to a power outlet up to 15-ft. (4.57 m) away in a hospital environment outside patient-care vicinities
- Extend an existing power connection up to 15-ft. (4.57 m) to more easily place a device or reach a power source
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P006-015-HG13CL Hospital-Grade Power Cord, NEMA 5-15P to C13, 15-ft. (4.57 m), Clear Plugs



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|--------------------------------------|-----------------------------|
| Side A - Connector 1 | NEMA 5-15P-HG |
| Side B - Connector 1 | IEC-320-C13 |
| PHYSICAL | |
| Plug Color | Clear |
| Cable Jacket Color | Black |
| Cable Jacket Material | PVC |
| Cable Jacket Rating | FT2 |
| Power Cord Jacket Type | SJT |
| Cable Outer Diameter (OD) | 9mm |
| Number of Conductors | 3 |
| Wire Gauge (AWG) | 16 |
| Wire Gauge (OD - mm ²) | 1.31 |
| Cable Length (ft.) | 15 |
| Cable Length (m) | 4.57 |
| Shipping Dimensions (hwd / in.) | 10.60 x 14.90 x 0.50 |
| Shipping Dimensions (hwd / cm) | 26.92 x 37.85 x 1.27 |
| Shipping Weight (lbs.) | 1.19 |
| Shipping Weight (kg) | 0.54 |
| ENVIRONMENTAL | |
| Operating Temperature Range | -4° to 140°F (-20° to 60°C) |
| Storage Temperature Range | -4° to 140°F (-20° to 60°C) |
| Operating Humidity Range | 20% to 80% RH |
| Storage Humidity Range | 20% to 80% RH |
| FEATURES & SPECIFICATIONS | |
| Antibacterial | No |
| Angled Plug | No |
| High Voltage | No |
| Locking Plug | No |
| Coiled Power Cord | No |
| STANDARDS & COMPLIANCE | |
| Product Certifications | cUL Listed; UL Listed |
| Product Compliance | RoHS |
| WARRANTY & SUPPORT | |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|-------------------------------------|---------------------------|
| Product Warranty Period (Worldwide) | Lifetime limited warranty |
|-------------------------------------|---------------------------|

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.