

Hospital-Grade Power Cord, NEMA 5-20P to C19 - Heavy-Duty, Green Dot, 20A, 125V, 12 AWG, 6 ft. (1.83 m), Gray

MODEL NUMBER: **P049-006-GY-HG**



Connects a server, transformer, or other high-current medical device with a C20 power inlet to a grounded 5-20R hospital-grade outlet.

Features

Hospital-Grade Power Cord is a Safe Solution for Medical Facilities This hospital-grade cord features 12 AWG wire suitable for high power connections, making it a reliable solution for devices that require a higher-rated, heavier-gauge cable. The C19 end connects to a server, isolation transformer, power strip or other compatible hospital component. The NEMA 5-20P-HG green-dot plug connects to a hospital-grade AC power source located outside patient-care vicinities. The 6-ft. (1.83 m) length allows you flexibility in placing equipment with respect to the power outlet.

Designed and Tested to Strict Hospital-Grade Standards This hospital power cord is tested to ANSI/UL 62 and 817 standards, as well as CAN/CSA C22.2 no. 21 and 49 standards, ensuring it's a dependable power solution for hospital environments.

Color-Coded to Avoid Misidentification That Can Cause Costly Downtime This hospital-grade power cord features a gray SJT jacket and fully molded gray ends. The color-coding allows easy, fast identification in a crowded surge protector and helps prevent the cable from becoming inadvertently disconnected.

Specifications

| OVERVIEW | |
|----------------------|--|
| UPC Code | 037332224910 |
| Device Compatibility | Mobile Cart; Computer; Printer; Monitor/HDTV; Server; UPS; PDU |
| Country/Region | North America |
| INPUT | |
| Maximum Input Amps | 20 |

Highlights

- Recommended for connecting devices to power outlets outside patient-care vicinities
- 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
- Hospital-grade power cord replaces or upgrades power cord provided by manufacturer
- Thick 12 AWG wire gauge manages high power levels required for larger equipment
- Color-coded gray for fast, easy identification in a crowded PDU, UPS or surge protector

Applications

- Connect devices like servers, transformers and power strips to an AC outlet up to 6-ft. (1.83 m) away in a hospital environment outside patient-care vicinities
- Extend an existing power connection up to 6-ft. (1.83 m) to more easily place a device or reach a power source
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P049-006-GY-HG Hospital-Grade Power Cord, NEMA 5-20P to C19, 6-ft. (1.83 m), Gray



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|--------------------------------------|-------------------------------------|
| Voltage Compatibility (VAC) | 125 |
| CONNECTIONS | |
| Side A - Connector 1 | NEMA 5-20P-HG |
| Side B - Connector 1 | IEC-320-C19 |
| PHYSICAL | |
| Plug Color | Gray |
| Cable Jacket Color | Gray |
| Cable Jacket Material | PVC |
| Cable Jacket Rating | VW-1 |
| Power Cord Jacket Type | SJT |
| Cable Outer Diameter (OD) | 1mm |
| Number of Conductors | 3 |
| Wire Gauge (AWG) | 12 |
| Wire Gauge (OD - mm ²) | 3.31 |
| Cable Length (ft.) | 6 |
| Cable Length (m) | 1.83 |
| Shipping Dimensions (hwd / in.) | 1.00 x 9.00 x 13.00 |
| Shipping Dimensions (hwd / cm) | 2.54 x 22.86 x 33.02 |
| Shipping Weight (lbs.) | 1.10 |
| Shipping Weight (kg) | 0.50 |
| ENVIRONMENTAL | |
| Operating Temperature Range | -4° to 221°F (-20° to 105°C) |
| Storage Temperature Range | -4° to 221°F (-20° to 105°C) |
| Operating Humidity Range | 0% to 65% RH |
| Storage Humidity Range | 0% to 65% RH |
| FEATURES & SPECIFICATIONS | |
| Antibacterial | No |
| Angled Plug | No |
| High Voltage | Yes |
| Locking Plug | No |
| Coiled Power Cord | No |
| STANDARDS & COMPLIANCE | |
| Product Certifications | CSA (Canada); cUL Listed; UL Listed |



Powering Business Worldwide

TRIPP LITE
SERIES

| | |
|-------------------------------------|---------------------------|
| Product Compliance | RoHS; REACH |
| WARRANTY & SUPPORT | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard

Cleveland, OH 44122

United States

<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks
are the property of their respective owners.