

## DisplayPort to DVI Adapter Video Converter, Black (M/F), 1 ft. (0.31 m)

MODEL NUMBER: P134-001-GC



DP to DVI converter connects a DVI monitor to the DisplayPort output on your notebook, desktop PC or Chromebook Pixel.

### Features

**DP to DVI Converter Connects a DisplayPort Source to Your Existing DVI Display** This DisplayPort to DVI converter connects a DVI monitor or projector to the DisplayPort (DP) output on your notebook computer, desktop PC, Chromebook Pixel or other compatible device. It features a male DP connector and a female dual-link DVI-I connector, allowing you to continue using your existing DVI display and DVI cable to transmit video signals without the expense of a new DP display.

**Transmits Outstanding 1080p Video for High-Definition Presentations** Ideal for classrooms, lecture halls and anywhere else you may give a presentation, this DisplayPort to DVI converter supports DVI-D single-link computer video resolutions up to 1920 x 1200 (at 60 Hz) and high-definition resolutions up to 1080p. It also complies with HDCP 2.2 and DisplayPort 1.1 standards. Molded gold-plated connectors and contacts provide maximum conductivity and minimum data loss to guarantee a clear transmission free of interference. The P134-001-GC is a passive adapter and requires that the connected computer has a DP++ (DisplayPort ++ ) port, which allows DVI signals to be passed through. Check the documentation for your DisplayPort source for compatibility.

**Ready to Use Right Out of the Package** The plug-and-play adapter requires no software, drivers or external power, so you can connect it to your devices right away. Only one foot in length, the P134-001-GC is recommended for stowing in your laptop bag and carrying to school, the office or the latest trade show.

## Specifications

| OVERVIEW     |                  |
|--------------|------------------|
| UPC Code     | 037332238047     |
| Product Type | Video Adapter    |
| Technology   | DVI; DisplayPort |
| VIDEO        |                  |

### Highlights

- Continue using your current DVI display without the expense of a new DP monitor
- Delivers HD picture quality at resolutions up to 1920 x 1200 (1080p) @ 60 Hz
- Compact unit fits easily into briefcase or laptop bag for instant use anywhere
- Plug-and-play operation with no software required for easy, immediate installation
- Ideal for high-definition video presentations and digital signage on a DVI display
- This product is a passive adapter and requires that the connected computer has a DP++ (DisplayPort ++ ) dual-mode port

### Applications

- Display 1080p video on an existing DVI monitor without the expense of buying a new DisplayPort monitor
- Give a video presentation in a classroom, conference room or trade show booth

### System Requirements

- Source device with DisplayPort output and DisplayPort++ support
- Display device with DVI input

### Package Includes

- P134-001-GC DisplayPort to DVI Cable Adapter - M/F, Black, 1 ft.



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                 |                                                       |
|---------------------------------|-------------------------------------------------------|
| Max Supported Video Resolution  | 1920 x 1200 (1080p)                                   |
| Max Supported Color Depth       | 48-bit (w/ Dual-Link)                                 |
| 3D Video Supported              | Yes                                                   |
| <b>INPUT</b>                    |                                                       |
| Bus Powered                     | Yes                                                   |
| <b>CONNECTIONS</b>              |                                                       |
| Side A - Connector 1            | DISPLAYPORT (MALE)                                    |
| Side B - Connector 1            | DVI-I DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK) |
| Connector Plating               | Gold                                                  |
| Contact Plating                 | Gold                                                  |
| <b>PHYSICAL</b>                 |                                                       |
| Color                           | Black                                                 |
| Material of Construction        | PVC, ABS                                              |
| Cable Jacket Material           | PVC                                                   |
| Cable Jacket Rating             | VW-1                                                  |
| Cable Outer Diameter (OD)       | 7.0mm                                                 |
| Cable Length (ft.)              | 1                                                     |
| Cable Length (m)                | 0.30                                                  |
| Cable Length (in.)              | 12                                                    |
| Ferrite Core                    | No                                                    |
| Cable Length (cm)               | 30.48                                                 |
| Minimum Bend Radius             | 70mm                                                  |
| Shipping Dimensions (hwd / in.) | 9.00 x 7.00 x 0.50                                    |
| Shipping Weight (kg)            | 0.06                                                  |
| Unit Weight (lbs.)              | 0.13                                                  |
| Unit Weight (kg)                | 0.06                                                  |
| <b>ENVIRONMENTAL</b>            |                                                       |
| Operating Temperature Range     | 32° to 104°F (0° to 40°C)                             |
| Storage Temperature Range       | 5° to 122°F (-15° to 50°C)                            |
| Relative Humidity               | 0-85% non-condensing                                  |
| <b>COMMUNICATIONS</b>           |                                                       |
| EDID Compatible                 | Yes                                                   |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                              |                                                 |
|----------------------------------------------|-------------------------------------------------|
| Consumer Electronics Control (CEC) Supported | Yes                                             |
| <b>FEATURES &amp; SPECIFICATIONS</b>         |                                                 |
| Displayport Specification                    | 1.1                                             |
| HDCP Specification                           | 2.2                                             |
| Driver Required                              | No                                              |
| <b>STANDARDS &amp; COMPLIANCE</b>            |                                                 |
| Product Compliance                           | CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE |
| <b>WARRANTY &amp; SUPPORT</b>                |                                                 |
| Product Warranty Period (Worldwide)          | 3-year limited warranty                         |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.