

VGA Monitor Cable, 640x480 (HD15 M/M), 6 ft. (1.83 m)

MODEL NUMBER: **P512-006**



Highlights

- Superior molded cables with foil-shielding for maximum EMI/RFI protection

System Requirements

- Monitor with removable HD15 cable and resolutions up to 640x480.

Package Includes

- 6-ft. (1.83 m) VGA Monitor Cable HD15M to HD15M Gold Connectors

Description

This VGA monitor replacement cable is designed for use with a monitor that has a removable cable with HD15 connectors. This six-foot (1.8 meters) cable has gold-plated connectors and gold-plated copper contacts to ensure excellent conductivity. Shielded for maximum EMI/RFI protection. The HD15 male and HD15 male connectors are molded and have integral strain relief to ensure they last a long time.

For use with monitors with resolutions up to 640 x 480 (VGA Std). For higher resolution monitors, please use P502-006.

Features

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Gold plated connectors and gold plated copper contacts ensure excellent conductivity
- HD15 male to HD15 male molded connectors

Specifications

OVERVIEW	
UPC Code	037332012364
Product Type	Passive Cable
Technology	VGA/SVGA
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	HD15 (MALE)
Side B - Connector 1	HD15 (MALE)
Latching or Gripping Connector	No



Powering Business Worldwide

TRIPP LITE
SERIES

PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	8.50 x 6.90 x 0.50
Shipping Dimensions (hwd / cm)	21.59 x 17.53 x 1.27
Shipping Weight (lbs.)	0.33
Shipping Weight (kg)	0.15
FEATURES & SPECIFICATIONS	
IP68 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.