

DVI Dual Link Extension Cable, Digital TMDS Monitor Cable (DVI-D M/F), 6 ft. (1.83 m)

MODEL NUMBER: **P562-006**



Features

- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- Dual Link digital signaling for transmission speeds to 9.9Gbps
- 2560x1600 @ 60Hz Resolution Support
- Gold plated contacts ensure excellent conductivity
- Meets DVI DDWG Standard
- For use with Digital CRT displays, Flat Panel Displays, HDTV and Projectors

Specifications

OVERVIEW	
UPC Code	037332120649
Product Type	Passive Cable
Technology	DVI
Cable Type	Passive
CONNECTIONS	
Side A - Connector 1	DVI-D DUAL LINK (MALE)
Side B - Connector 1	DVI-D DUAL LINK (FEMALE)
Latching or Gripping Connector	No
PHYSICAL	
Color	Black

Highlights

- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 2560 x 1600 @ 60Hz
- High Speed Digital Transmission to 9.9Gbps

System Requirements

- Monitor with DVI, and CPU with a DVI video card. Video card must support Dual Link in order to obtain resolutions up to 2560 x 1600

Package Includes

- DVI Dual Link Extension TMDS cable - DVI-D, M/F, 6-ft.



Powering Business Worldwide

TRIPP LITE
SERIES

Cable Jacket Color	Black
Cable Length (ft.)	6
Cable Length (m)	1.83
Cable Length (in.)	72
Shipping Dimensions (hwd / in.)	10.00 x 8.00 x 0.50
Shipping Dimensions (hwd / cm)	25.40 x 20.32 x 1.27
Shipping Weight (lbs.)	0.70
Shipping Weight (kg)	0.32
FEATURES & SPECIFICATIONS	
IP68 Rated	No
IP20 Rated	No
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.