


3.7kW Single-Phase Local Metered PDU, 208/230V (8 C13 & 2 C19), C20 / L6-20P Adapter, 12 ft. (3.66 m) Cord, 1U Rack-Mount, TAA

MODEL NUMBER: PDUMH20HV



Highlights

- Local metered single phase 16A 208/230V PDU
- 1U horizontal rackmount; Digital current meter
- C20 input with L6-20P plug adapter; 12 ft. (3.7 m) line cord
- 10 total outlets (8 C13, 2 C19); Compatible with Eaton Tripp Lite power cords
- Reversible housing; 6.5 in. / 16.5 cm depth
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- Rackmount PDU
- C19 to L6-20P plug adapter
- Rack mounting brackets

Features

- 16/20A single phase 208/230V Local Metered Power Distribution Unit / rack PDU (rPDU) (Agency de-rated to 16A continuous)
- Built-in 2 digit visual meter continuously reports PDU load level in amps
- C20 inlet with C20 input cable and L6-20P adapter; 12-ft. (3.66 m) line cord
- 1U horizontal rackmount format installs in one rack space
- 10 total outlets (8 C13 / 2 C19)
- Mounting flanges support installation in 2 and 4 post racks, with additional support for wall-mount and under-counter installation formats
- Mounting ears are reversible for front or rear facing rackmount installation
- Optional PDUSIDEBRKT enables 0U vertical rackmount in compatible racks
Back panel grounding lug
- Federal Trade Agreements Act / TAA Compliant for GSA Schedule purchases

Specifications

OVERVIEW	
UPC Code	037332159014
PDU Type	Local Metered
INPUT	
Input Phase	Single-Phase
PDU Input Voltage	208; 230
Recommended Electrical Service	Single-phase 16/20A 230/208V service



Powering Business Worldwide

TRIPP LITE
SERIES

Maximum Input Amps	16
Maximum Input Amps Details	Agency de-rated to 16A continuous
Input Connection Type	C20 inlet
PDU Plug Type	NEMA L6-20P; IEC-320 C20
Input Cord Details	Includes 12 ft. / 3.6m C19 to C20 power cable and L6-20P plug adapter
Input Cord Length (ft.)	12
Input Cord Length (m)	3.66
OUTPUT	
Output Capacity Details	3.68kW (230V), 3.33kW (208V) / 16A total capacity; 16A max per C19 outlet; 12A (10A CE) max per C13 outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacle Details	Compatible with Eaton Tripp Lite Power Cords
Output Receptacles	(8) C13; (2) C19
Output Nominal Voltage	208/230V
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Digital display reports total PDU output current in amps
SURGE / NOISE SUPPRESSION	
Automatic Shut-Off	No
PHYSICAL	
Material of Construction	Metal
Rack Height	1U
Form Factors Supported	1U rackmount. Includes mounting accessories for 2-4 post racks
Minimum Required Rack Depth (cm)	24.13
Minimum Required Rack Depth (inches)	9.5
PDU Form Factor	Horizontal (1U)
Shipping Dimensions (hwd / in.)	2.20 x 11.60 x 20.40
Shipping Dimensions (hwd / cm)	5.59 x 29.46 x 51.82
Shipping Weight (lbs.)	7.50
Shipping Weight (kg)	3.40
Unit Dimensions (hwd / in.)	1.750 x 17.500 x 6.500
Unit Dimensions (hwd / cm)	2,87 x 44,4 x 16,5
Unit Weight (lbs.)	6.80
Unit Weight (kg)	3.08



Powering Business Worldwide

TRIPP LITE
SERIES

ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-22° to 122°F (-30° to 50°C)
Relative Humidity	5% to 95% non-condensing
Operating Elevation	0-10000 ft. (0-3000 m)
FEATURES & SPECIFICATIONS	
Grounding	Rear grounding lug
STANDARDS & COMPLIANCE	
Product Certifications	IEC 62368-1; RETIE (Colombia); GOST (Russia); NOM (Mexico)
Product Compliance	RoHS; CE (Europe); EAC (Belarus, Kazakhstan, Russia); FCC Part 15 Class A (USA); UKCA; Trade Agreements Act (TAA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.