

3.7kW Single-Phase Local Metered PDU, 208/230V Outlets (6-C19 & 32-C13) C20/L6-20P Cable 10 ft. (3.05 m) Cord, 0U Vertical

MODEL NUMBER: **PDUMV20HV**



Features

- 16/20A single phase 230/208V Local Metered Power Distribution Unit / rack PDU (rPDU) (Agency derated to 16A continuous)
- Two-digit lighted meter reports combined total output current in amps
- 10ft / 3m detachable input cable with NEMA L6-20P plug
- C20 inlet accepts a variety of 16A international cordsets
- 0U 63.75in / 162cm vertical rackmount format installs using no rack spaces
- 38 total outlets (6 C19, 32 C13)
- Included plug-lock inserts ensure components remain connected and powered
- Toolless installation supported in button-mount compatible equipment racks
- Bolt-down installation brackets support installation in other racks and additional surfaces

Specifications

OVERVIEW	
UPC Code	037332139344
PDU Type	Local Metered
INPUT	
Input Phase	Single-Phase
PDU Input Voltage	208; 230
Recommended Electrical Service	Single-phase 16/20A 230/208V service
Maximum Input Amps	16

Highlights

- Local metered single phase 16A 208/230V 0U 63.75in / 162cm vertical rackmount PDU
- Two-digit meter reports output current in amps
- 10ft / 3m detachable input cable with NEMA L6-20P plug
- C20 inlet accepts a variety of 16A international cordsets
- 38 output receptacles (6 C19, 32 C13); Compatible with Eaton Tripp Lite power cords
- Ready for immediate toolless 0U installation

Package Includes

- PDUMV20HV 63.75 inch basic PDU
- Plug-lock inserts (6 C20, 32 C13)
- Spare installation buttons, 2.9 mm/4.6 mm
- 10-ft. (3.05 m) detachable C19-to-L620P input cordset
- Mounting hardware
- Owner's Manual



Powering Business Worldwide

TRIPP LITE
SERIES

Maximum Input Amps Details	Agency de-rated to 16A continuous
Input Connection Type	L6-20P detachable cordset, C20 inlet available
PDU Plug Type	NEMA L6-20P; IEC-320 C20
Input Cord Length (ft.)	10
Input Cord Length (m)	3.05
OUTPUT	
Output Capacity Details	3.68kW (230V), 3.33kW (208V) / 16A total capacity; 16A max per C19 outlet; 12A (10A CE) max per C13 outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacle Details	Compatible with Eaton Tripp Lite Power Cords
Output Receptacles	(32) C13; (6) C19
Output Nominal Voltage	208/230V
USER INTERFACE, ALERTS & CONTROLS	
Front Panel LCD Display	Digital meter reports PDU output current in amps
SURGE / NOISE SUPPRESSION	
Automatic Shut-Off	No
PHYSICAL	
Material of Construction	Aluminum
Rack Height	0U
Form Factors Supported	0u vertical installation in equipment racks, plus under-counter and wallmount
PDU Form Factor	Vertical (0U)
Shipping Dimensions (hwd / in.)	5.00 x 3.50 x 65.50
Shipping Dimensions (hwd / cm)	12.70 x 8.89 x 166.37
Shipping Weight (lbs.)	9.50
Shipping Weight (kg)	4.31
Unit Dimensions (hwd / in.)	3.750 x 2.250 x 63.750
Unit Dimensions (hwd / cm)	162 x 5.7 x 9.5
Unit Weight (lbs.)	5.20
Unit Weight (kg)	2.36
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	-22° to 122°F (-30° to 50°C)
Relative Humidity	0-95% non-condensing
Operating Elevation	0-10000 ft. (0-3000 m)



Powering Business Worldwide

TRIPP LITE
SERIES

STANDARDS & COMPLIANCE

Product Certifications	IEC 62368-1; RETIE (Colombia); GOST (Russia); NOM (Mexico)
Product Compliance	RoHS; CE (Europe); EAC (Belarus, Kazakhstan, Russia); UKCA

WARRANTY & SUPPORT

Product Warranty Period (Worldwide)	2-year limited warranty
-------------------------------------	-------------------------

1000 Eaton Boulevard

Cleveland, OH 44122

United States

<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks
are the property of their respective owners.