


Important Note

Guaranteed compatibility when used with recommended cabling. Designed specifically for use with N370-Series cables.

40/100Gb Fiber Breakout Cassette with Built-In MTP Cables, 40Gb to 4 x 10Gb, 100Gb to 4 x 25Gb, (x3) 8-Fiber Singlemode MTP/MPO to (x12) LC Duplex 9/125

MODEL NUMBER: N482-3M8L12S-B



Installs in select Tripp Lite fiber chassis to connect 12 LC duplex fiber cables with three 8-fiber MTP/MPO connections in high-density network applications.

Description

The N482-3M8L12S-B 9/125 Fiber Breakout Cassette works in tandem with a N482-01U or N482-02U chassis (sold separately) to connect 12 LC duplex fiber cables with three 8-fiber MTP/MPO connections in high-density network applications. The cassette features three built-in 2-meter 8-fiber MTP cables. Color-coded yellow singlemode cables are easily distinguished from traditional aqua OM3 multimode fiber.

The cassette's modular design installs easily in the N482-01U and N482-02U chassis with no tools required. Just insert the cassette into the chassis, and screw in its retention clips to secure it. Plug LC Ethernet cables, such as N370-Series cables (sold separately), into the cassette. Up to five N482-3M8L12S-B cassettes fit in the N482-01U 1U enclosure panel, and up to 14 cassettes fit in the N482-02U 2U sleeve. Dust tabs protect unused ports from potential damage. Guaranteed compatibility when used with recommended cabling, including N370-Series cables.

The N482-3M8L12S-B complies with IEEE 802.3ae (10 GbE) and ANSI T11.2 (Fibre Channel) requirements. Supports 40 GbE internally using 9/125 singlemode fiber optic cable. Ideal for QSFP fabric switches that use eight out of 12 available MTP fibers for four-lane parallel optics to 40 GB, allowing all 12 LC duplex cassette ports to be used. Maximum insertion loss of 0.35 dB falls well under the IEEE 802.3ae maximum channel loss specification of <25 dB. This cassette also supports devices of varying speeds, including 10Gb, 25Gb, 40Gb and 100Gb network equipment.

With factory-terminated connectors that reduce time and labor, the N482-3M8L12S-B is made from only the finest materials to ensure fast installations and optimal performance.

Features

Elegant, Simple Solution for 40 Gb to 10 Gb, or 100 Gb to 25 Gb, LC Cable Connections High-density fiber cassette for use with N482-01U and N482-02U fiber enclosure panels
3 yellow built-in 2-meter 8-fiber MTP singlemode cables
Connect up to 12 LC duplex fiber cables with 3 8-fiber MTP/MPO connections
Recommended for use with QSFP fabric switches to support 4 lanes parallel to 40 GB
Supports 40 GbE internally using 9/125 singlemode fiber optic cable
Guaranteed compatibility when used with recommended cabling
Designed specifically for use with cables, such as the N370-series cables

Highlights

- For use with N482-01U or N482-02U chassis
- 3 yellow built-in 2-meter 8-fiber MTP singlemode cables
- Guaranteed compatibility when used with recommended cabling
- Designed specifically for use with N370-Series cables
- Factory-terminated connectors
- Supports 40 GbE internally using fiber optic cable
- Simple installation with no tools required

System Requirements

- QSFP switches that use 8-fiber per port to support 4 x LC 10 GB breakout
- Guaranteed compatibility when used with recommended cabling
- Designed specifically for use with N370-Series cables

Package Includes

- N482-3M8L12S-B 9/125 Fiber Breakout Cassette
- Owner's manual



Powering Business Worldwide

TRIPP LITE
SERIES

Simple Fiber Installations Save Time and Money Easy installation with no tools required Install up to 14 cassettes in N484-02U 2U chassis Install up to 5 cassettes in N484-01U 1U chassis

Easy to Modify, Upgrade or Expand Fiber Infrastructure By Adding or Swapping

Cassettes Complies with IEEE 802.3ae (10 GbE) and ANSI T11.2 (Fibre Channel) requirements 0.35 dB maximum insertion loss falls under IEEE 802.3ae maximum channel loss spec of <25 dB Supports devices of varying speeds, including 10 Gb, 25 Gb, 40 Gb and 100 Gb network equipment

Premium Construction for Optimal Performance Factory-terminated connectors reduce time and labor Dust caps protect unused ports

Specifications

OVERVIEW	
UPC Code	037332200860
Technology	Singlemode
CONNECTIONS	
Number of Ports	12
Side A - Connector 1	8F MTP/MPO (FEMALE)
Side B - Connector 1	LC DUPLEX (FEMALE)
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.00 x 13.20 x 4.40
Shipping Dimensions (hwd / cm)	5.08 x 33.53 x 11.18
Shipping Weight (lbs.)	0.50
Shipping Weight (kg)	0.23
Unit Dimensions (hwd / in.)	4.720 x 3.460 x 1.180
FEATURES & SPECIFICATIONS	
Built-in Cables	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.