

Important Note

Guaranteed compatibility with recommended cabling, including N820- and N821-Series cables.

40/100Gb Fiber Breakout Patch Panel, 40Gb to 4 x 10Gb, 100Gb to 4 x 25Gb, 15 MTP QSFP to 60 LC Duplex OM4 50/125 Multimode Ports, 1U

MODEL NUMBER: N48K-15M8L60-B



High-density 50/125 multimode breakout panel seamlessly and conveniently integrates 10G equipment with 40G networks or 25Gb equipment with 100Gb networks to meet current connectivity needs and future-proof your network in a cost-effective manner.

Description

The N48K-15M8L60-B 50/125 Breakout Fiber Patch Panel not only integrates equipment with 10G and 40G speeds, but also provides a simple, flexible path from 25Gb to 100Gb, as well as upcoming 50Gb to 200Gb speeds and beyond. The 1U chassis features five breakout cassettes. Each cassette contains 12 LC duplex ports and three built-in two-meter MTP multimode cables for a total of 15 QSFP fiber switch ports breaking out to 60 LC ports.

Base8 wiring with built-in MTP trunks maximizes rack space and link performance, while enabling simple cable deployment and optimized harness mapping. The N48K-15M8L60-B uses all 60 LC ports, meaning no dead ports as in Base12 wiring, with streamlined 1-to-1 port mapping. Eliminating the need for 12-fiber conversion modules results in a reduction of up to 50 percent in link attenuation.

Hardwired cassettes offer a 30-percent improvement in insertion loss with no separate MTP connection in the rear, resulting in longer duplex link distances. Color-coded magenta OM4 cables are easily distinguished from traditional aqua OM3 multimode fiber. Base-8 Fiber compatible with both QSFP+ 40GBASE-SR4 to SFP+ 10GBASE-SR and QSFP28 100GBASE-SR4 to SFP28 25GBASE-SR connections.

The front panel folds down to protect the LC patch cords, as well as provide wire mapping by matching each cassette's labeled MTP cables to the LC clusters. Writing space on the inside panel lets you custom-label each port. Each panel is serialized and insertion loss data is available upon request via the unit's serial number.

Features**Integrates Equipment with 10Gb and 40Gb Speeds, or 25Gb and 100Gb, to Meet Current**

Connectivity NeedsAlso future-proofs your network for eventual 50Gb and 200Gb speeds and beyondBase-8 Fiber compatible with both QSFP+ 40GBASE-SR4 to SFP+ 10GBASE-SR and QSFP28 100GBASE-SR4 to SFP28 25GBASE-SR connections.OM4 fiber for highest throughput

5 Breakout Cassettes12 LC duplex ports and 3 built-in 2-meter MTP multimode cables per cassetteTotal of 15 QSFP fiber switch ports and 60 LC ports100% fiber utilizationStreamlined 1:1 port mappingUp to

Highlights

- Total of 15 12-fiber MTP/MPO switch ports and 60 LC ports
- Base8 wiring uses all LC ports—no dead ports as in Base12
- Base-8 Fiber compatible with both QSFP+ 40GBASE-SR4 to SFP+ 10GBASE-SR and QSFP28 100GBASE-SR4 to SFP28 25GBASE-SR connections
- Hardwired cassettes for 30% improvement in insertion loss
- Easily identifiable color-coded magenta OM4 cables

System Requirements**Package Includes**

- N48K-15M8L60-B 50/125 Breakout Fiber Patch Panel

50% reduction in link attenuationColor-coded magenta cables easily distinguishable in crowded switch

Base8 Wiring No unused LC ports as in Base12 wiringSimple patch cable deploymentOptimized harness mappingHardwired cassette modules offer 30% improvement in insertion loss

Fold-Down Front Panel LC patch cables protectedProvides wire mapping by matching each cassette's labeled MTP cables to LC clustersWriting space on inside panel for custom-labeling of portsInsertion loss data available via unit's serial number

Mounts in 1U of EIA-Standard 19 in. Rack Maximizes rack space and link performance

Specifications

OVERVIEW	
UPC Code	037332200846
Product Type	Breakout
Technology	Multimode
Optical Mode	OM4
CONNECTIONS	
Side A - Connector 1	MTP/MPO (FEMALE)
Side B - Connector 1	LC DUPLEX (FEMALE)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	3.80 x 21.30 x 18.80
Shipping Dimensions (hwd / cm)	9.65 x 54.10 x 47.75
Shipping Weight (lbs.)	8.10
Shipping Weight (kg)	3.67
Panel Style	Fiber Breakout
FEATURES & SPECIFICATIONS	
All-in-One Kit	Yes
Built-in Cables	Yes
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Powering Business Worldwide

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

TRIPP LITE
SERIES

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.