


12-Outlet (10-15A & 2-20A) Vertical Power Strip, 120V, 20A, 15 ft. (4.57 m) Cord, 5-20P, 36 in.

MODEL NUMBER: PS361220



Add extra power outlets in rack-mount, workbench, office, retail displays and telecom applications, or any area that needs to power many electrical devices in close proximity to one another from a single AC wall outlet.

Description

Need to power many pieces of equipment in close proximity to one another, but don't have enough outlets to power them all? This PS361220 12-outlet vertical power strip will give you the outlets where you need them, when you need them. The PS361220 contains a 15-foot (4.6-meter) (14/3 SJT) cord, 10 standard NEMA 5-15R outlets and two commercial-use NEMA 5-20R outlets. Each outlet is spaced 2.64 inches apart (center-to-center), wide enough for many types of transformers or AC adapters without blocking adjacent outlets. Encased in a rugged all-metal housing, it comes with mounting clips for either vertical and horizontal mounting, making the PS361220 ideal for a variety of uses in rack-mount, workbench, industrial, office and telecom environments. An illuminated rocker-style power switch with a transparent guard prevents accidental turn-offs, while a 20-amp circuit breaker guards against dangerous circuit overloads. To match the decor of most professional settings, it has an extruded aluminum housing with black receptacles.

Features

Multi-Outlet 120V Power Distribution for Rack-Mount, Raceway and Workbench Applications

- 1800W, 120V, 20A, corded, multi-outlet power strip that safely connects multiple electrical devices to a single AC wall socket
- Saves the time and cost of installing new power outlets in un-powered areas
- Ideal for branch circuit power distribution to telecommunications, computers or internetworking equipment in rack enclosures, workbenches, table tops, work stations, offices, factories, repair shops, hobby shops, test stands and engineering labs

12 Convenient Outlets Power All Standard Electrical Equipment

- Features 12 outlets (10 NEMA 5-15R and 2 NEMA 5-20R) that are compatible with all standard electrical and electronic equipment
- Each outlet is 2.64 inches apart (center to center) - wide enough to fit transformers or AC adapters without blocking adjacent outlets, so you can fully utilize the power strip all the time
- An extra-long, 15-ft. (4.57 m), 14 AWG, 3-wire, SJT cord can reach wall outlets mounted in a different area or room from where it draws AC power, putting you in control of getting reliable power where you need it most

Highlights

- 12-outlet (ten 5-15R and two 5-20R) power strip with a 15-ft. (4.57 m) Cord and an industrial-grade 5-20P plug
- Rated at 1800W, 120V, featuring a 20A resettable circuit breaker to prevent circuit overloads
- Easy-to-install, vertical or horizontal mounting with included mounting clips
- Rocker-style, illuminated power switch with safety cover to prevent accidental turn offs
- RoHS-compliant and certified to meet UL 1363 standards

Package Includes

- PS361220
- Mounting hardware
- Instruction manual



Powering Business Worldwide

TRIPP LITE
SERIES

Easy-to-Install, Vertical and Horizontal Mounting Options

- Offers a convenient method of optional horizontal or vertical power distribution. Mounting clips are included.
- Its 36-in. length and strip-style, bench/cabinet, form factor fits in the most confined spaces unobtrusively
- Weighing less than 4 lbs (1.8 kgs), the PS361220 is both easy to handle and effortless to install

Built-In, Automatic Safety Features

- An illuminated, rocker-style, power switch with a transparent guard prevents accidental turn offs, while still allowing you to see whether the PS361220 is operational at a glance
- An integral, 20-amp resettable circuit breaker prevents dangerous circuit overloads that can irreversibly damage connected equipment
- The breaker automatically disconnects AC input power to the PS361220 when it detects that the equipment load is drawing too much current

Rugged, Durable Housing

- A rugged, all-metal housing is durably constructed to stand up to demanding network, laboratory or factory environments
- An attractive, extruded aluminum housing with stylish black receptacles matches the decor of most professional settings

Specifications

OVERVIEW	
UPC Code	037332186638
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	20A 120V
Input Cord Gauge Type	12 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-20P
Input Cord Length (ft.)	15
Right-Angle Plug	No
Input Cord Length (m)	4.57
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	60 Hz
Output (Watts)	1800
Output Receptacles	(10) 5-15R; (2) 5-20R
Circuit Breaker (amps)	20
Transformer Accommodation	(6) Yes



Powering Business Worldwide

TRIPP LITE
SERIES

Right-Angle Outlets	No
Outlet Spacing	2.64 in.
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted 2 position switch controls power to all outlets
Locking Switch Cover	Transparent on/off switch cover prevents accidental turn-off
PHYSICAL	
Color	Silver
Material of Construction	Aluminum
Power Cord Color	Black
Form Factors Supported	Supports vertical or horizontal mounting in rack enclosures, raceways and a variety of other applications
Housing Color	Silver
Mounting Holes or Slots	No
Outlets Measurement (Center to Center)	2.64 in.
Receptacle Color	Black
Shipping Dimensions (hwd / in.)	2.40 x 4.40 x 40.00
Shipping Dimensions (hwd / cm)	6.10 x 11.18 x 101.60
Shipping Weight (lbs.)	4.50
Shipping Weight (kg)	2.04
Unit Dimensions (hwd / in.)	1.250 x 1.500 x 36.000
Unit Dimensions (hwd / cm)	3.18 x 3.81 x 91.4
Unit Weight (lbs.)	3.79
Unit Weight (kg)	1.72
Outlet Spacing	2.64 in.
Mounting Details	Includes mounting clips
ENVIRONMENTAL	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 122°F (-10° to 50°C)
Operating Humidity Range	10% to 90% RH
Storage Humidity Range	5% to 95% RH
FEATURES & SPECIFICATIONS	
Antimicrobial	No
Built-In Circuit Breaker	Yes



Powering Business Worldwide

TRIPP LITE
SERIES

STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL 1363; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.