

**Important Note**

UL1363a, Paragraph 14.1(d) States "The SPRPT shall be permanently attached to the medical equipment by a means such that it is only removable with the use of a tool." To achieve compliance, one must use the PSCLAMP.

## Safe-IT UL 1363A Medical-Grade Power Strip for Patient-Care Vicinity, 4x Hospital-Grade Outlets, 3 ft. Coiled Cord

MODEL NUMBER: PS-410-HGOEMCC



Versatile power strip with coiled cord supplies power to movable plug-connected components mounted to IV poles, mobile carts, crash carts and mobile medical workstations in operating rooms and patient-care vicinities.

**Description**

The PS-410-HGOEMCC Medical-Grade Power Strip supplies power to movable plug-connected components mounted to a rack, table or pedestal in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas. Compliant with UL 1363A specifications, this 120V, 50/60 Hz power strip features a NEMA 5-15P-HG hospital-grade plug and four NEMA 5-15R-HG hospital-grade outlets.

The power strip is protected by an antimicrobial powder coating. Antimicrobial protection helps prevent the growth of bacteria, viruses, fungi, mold and mildew. The coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

Two built-in resettable 15A circuit breakers control power to all outlets and protect the power strip against overloads. Switchless design prevents the unit from being accidentally shut off. The coiled power cord is three feet (0.9 meters) long, and can be fully extended to 10 feet (3 m).

Mounting flanges let you install the PS-410-HGOEMCC on a wide variety of surfaces, such as IV poles, mobile carts, crash carts and mobile medical workstations. The all-metal housing ensures safety and is guaranteed to last a long time in demanding environments.

**Features**

**Power Distribution Anywhere in Any Medical Facility** Ideal for use in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas. For use on IV poles, mobile carts, crash carts and mobile workstations, when properly mounted. 120V, 50/60 Hz power strip complies with UL 1363A specifications.

**Exclusive Antimicrobial Protection** Antimicrobial coating helps resist the growth of bacteria, viruses, fungi, mold and mildew. Coating meets the requirements of JIS Z 2801:2000, an international standard for evaluating efficacy in antimicrobial products.

**Highlights**

- Antimicrobial protection helps prevent the growth of bacteria, viruses, fungi, mold and mildew
- Approved for use in patient-care vicinities when properly mounted
- Complies with UL 1363A and NFPA 99 specifications
- 3 ft. (0.9 m) coiled cord with NEMA 5-15P-HG hospital-grade plug extends to 10 ft.
- Features 4 NEMA 5-15R-HG hospital-grade outlets

**Package Includes**

- PS-410-HGOEMCC UL 1363A Medical-Grade Power Strip with four 15A Hospital-Grade Outlets and 3-ft. (0.91 m) Coiled, Extendable Cord
- Owner's Manual with maintenance requirements



Powering Business Worldwide

TRIPP LITE  
SERIES

**Versatile Medical-Grade Solution**4 NEMA 5-15R-HG hospital-grade outlets provide consistent power3 ft. power cord is coiled so it can be extended up to 10 ft. Rugged, all-metal housing for long life in demanding environments

**Premium Safety Features**Dual, resettable built-in 15A circuit breakers protect against dangerous overloadsSwitchless design prevents accidental shut-off

**Ready to Use Right Out of the Box**Built-in mounting flanges make the PS-410-HGOEMCC easy to install on a variety of surfaces

## Specifications

OVERVIEW	
UPC Code	037332148834
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Plug Features	Coiled Hospital Grade Plug
Input Cord Gauge Type	14 gauge; SJT
Voltage Compatibility (VAC)	120
Input Plug Type	NEMA 5-15P-HG
Input Cord Length (ft.)	10
Right-Angle Plug	No
Input Cord Length (m)	3.05
Integrated Cord Clip	No
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(4) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	2 x 15amp breakers (1 line, 1 neutral)
Transformer Accommodation	(2) Yes
Outlet Orientation	Single row of 4
Right-Angle Outlets	No
USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch
PHYSICAL	



Powering Business Worldwide

TRIPP LITE  
SERIES

Color	White
Material of Construction	Metal
Power Cord Color	White
Form Factors Supported	IV poles, mobile carts, crash carts and mobile medical workstations
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	Distance between keyhole tabs = 127mm; Distance between end tabs = 207.45mm
Outlets Measurement (Center to Center)	3.05 in.
Receptacle Color	White
Shipping Dimensions (hwd / in.)	9.80 x 2.60 x 6.30
Shipping Dimensions (hwd / cm)	24.89 x 6.60 x 16.00
Shipping Weight (lbs.)	2.30
Shipping Weight (kg)	1.04
Unit Dimensions (hwd / in.)	1.730 x 2.500 x 8.540
Unit Dimensions (hwd / cm)	4.39 x 6.35 x 21.69
Unit Weight (lbs.)	2.20
Unit Weight (kg)	1.00
Mounting Details	Includes flanges
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 122°F (-10° to 50°C)
Operating Humidity Range	10% to 90% RH
Storage Humidity Range	5% to 95% RH
<b>FEATURES &amp; SPECIFICATIONS</b>	
Rotatable Outlets	No
Antimicrobial	Yes
Built-In Circuit Breaker	Yes
Antibacterial	No
Built-in Cable Management	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	UL 1363A
Product Compliance	NFPA 99: 10.2.3.6; RoHS
<b>WARRANTY &amp; SUPPORT</b>	



*Powering Business Worldwide*

TRIPP LITE  
SERIES

Product Warranty Period (Worldwide)	Lifetime limited warranty
-------------------------------------	---------------------------

1000 Eaton Boulevard

Cleveland, OH 44122

United States

<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.